



Material

Insulator: P. B. T. +30%Glass Fiber (UL94V-0)  
 Contact: Phosphor Bronze Or Brass  
 Contact plated: Gold over Nickel or Tin

Specification

Current Rating: 3A  
 Voltage Rating: 250V AC  
 Insulator Resistance: 1000M $\Omega$  Min. at 500V DC  
 Operating Temperature: -55° C ~ +105° C  
 Contact Resistance: 15m $\Omega$  Max

APPROVED:	DATE:	TITLE:			
CHECKED:	DATE:	2.54短路帽 闭口			
DRAWN:	DATE:	CLIENT P/N	跳线帽	SCALE	free
L Y F	2009-05-27	UNIT	mm	FILE NO.	Ckmtw-207-0004
TOLERANCE TABLE		REV.	$\phi$	$\nabla$	A
.0	$\pm 0.20$				
.00	$\pm 0.15$				
.000	$\pm 0.05$				

深圳市灿科盟实业有限公司  
 CkmtwCHANKEMENG INDUSTRYCO., LTD