


PCB Layout (Pattern side)

NOTE:
 Operating Force: 500 ± 50 gf
 Travel: 15 Pulses 0.3mm±0.1mm



Circuit Diagram

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑩	Dust cover	—	1	Kapton Film	Yellow	—
⑨	Spring plate	—	1	SUS	Natural	—
⑧	Contact	—	1	F.Ag/SUS	Natural	—
⑦	Knob	—	1	LCP	Black	—
⑥	Tuning Knob 2	—	1	LCP	Black	—
⑤	Terminal	—	8	Brass(0.15t)	Plating Silver	—
④	Gasket	—	1	Aluminum	Plating Stannum	—
③	Base	—	1	LCP	Black	—
②	Earth Terminal	—	1	Brass(0.15t)	Plating silver	—
①	Tuning Knob 1	—	1	LCP	Black	—

APPROVALS		DATE	TITLE:	
DRAWN	J.X.Zhong	2013/7/25	ELECTRONICS CO.,LTD	
CHECKED			MULTIFUNCTIONAL SWITCHS	

APPROVALS		PART NO.	SCALE:	PROJ.
TOLERANCES ARE	30~12.5 ± 10~30 ±0.20 5~10 ±0.15 ~5 ±0.10	K1-1203UA-01	1:1	PROJ. 1 OF 1
CHECKED				
APPROVALS				
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.
	A		NEW	
	B			