



Circuit Diagram

NOTE:  
Operating Force: 50gf—180gf Max

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑩	Terminal	—	6	H65(0.3t)	Plating silver	—
⑨	PCB	—	1	FR4	—	—
⑧	Base	—	1	PPA	Black	—
⑦	Movable pin 2	—	1	LCP	White	—
⑥	Contact	—	2	Brass(0.10t)	Plating silver	—
⑤	Movable pin 1	—	1	LCP	White	—
④	Cover 2	—	1	FR52	Black	—
③	Rocker	—	1	FR52	Black	—
②	spring	—	1	SUS	—	—
①	Cover 1	—	1	SUS	White	—

APPROVALS		DATE
DRAWN	J.X.Zhong	2013/8/6

TITLE: MULTIFUNCTIONAL SWITCHES  
ELECTRONICS CO.,LTD

APPROVALS		PART NO.	SCALE:	PROJ.
CHECKED		K1-1539SA-01	1:1	①
APPROVALS				
TOLERANCES ARE	30~12.1 ±	±0.30	ANGLE	
	10~30	±0.20		
	5~10	±0.15		
	~5	±0.10	±2'	DRAWING NO.

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			