




PCB Layout (Pattern Side)



Circuit diagram



NO.1	
PART NO	H
A	3.8
B	4.3
C	4.8
D	5
E	5.5
F	6
G	6.5
H	7
I	7.5
J	8
K	8.5
L	9

NO.2	
PART NO	vigor
1	90±.30
2	130±.30
3	180±.30
4	250±.30
5	350±.50

NO.3	
PART NO	MATERIAL/QTY
S	SUS/1PC
C	C5210/1PC
D	SUS/2PCS
F	C5210/2PCS

NO.4-NO.5	
PART NO	NOTE
01~99	SERIAL NUMBER

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
⑤	Terminal	—	3	Brass(0.30)	Plating silver	—
④	Contact	—	1	F.Ag/SUS	—	—
③	Base	—	1	PA46	Black	—
②	Cover	—	1	SUS	—	—
①	Keystroke	—	1	PA46	Black	—

APPROVALS	
DRAWN	JKUN.LU
CHECKED	—
DATE	2013/6/24

TITLE: TACT SWITCHS
ELECTRONICS CO.,LTD



ECN NO.	REV	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
—	A	—	NEW	—	—	—
TOLERANCES ARE: 30~12.1 ± ±0.30 ANGLE ±2° DRAWING NO. — SHEET 1 OF 1 10~30 ± ±0.20 UNIT: mm SCALE: 1:1 5~10 ± ±0.15 PROJ: — ~5 ± ±0.10						