Spec Sheet

Multilayer Chip Inductors (LK series)

LK21253R9K-T



Features

- Item Summary
 3.9uH±10%, 30mA, 0805/2012 (EIA/JIS)
- Lifecycle Stage
 Mass Production
- Standard packaging quantity (minimum)
 Taping Embossed 2000pcs

Products characteristics table

Inductance	3.9 uH ± 10 %
Case Size (EIA/JIS)	0805/2012
Rated Current (max)	30 mA
DC Resistance (max)	0.7 Ω
Q (min)	45
LQ Measuring Frequency	10 MHz
Self Resonant Frequency (min)	38 MHz
Operating Temp. Range	-40 to +85 ℃
RoHS2 Compliance (10 subst.)	Yes
REACH Compliance (168 subst.)	Yes
Soldering	Reflow/Wave

■ External Dimensions

Dimension L	2.0 +0.3/-0.1 mm
Dimension W	1.25 ±0.2 mm
Dimension T	1.25 ±0.2 mm
Dimension e	0.5 ±0.3 mm

2017.01.02