PTS 540 Series Ultra Low Profile SMT Top Actuated

Features/Benefits

- 3.7 x 3.7 mm footprint
- 0.35 mm thickness
- High number of cycles

Typical Applications

- MP3 accessories
- Bluetooth headset
- Remote controls



Specifications

FUNCTION: momentary action

CONTACT ARRANGEMENT: 1 make contact = SPST N.O.

TERMINALS: J type for SMT TRAVEL: 0.15 mm ± 0.1 mm

Mechanical

	Operating	Operating Life
Part Number	Force (gf)	(operations)
PTS540 JM035 SMTR LFS	160 ± 50	500,000
PTS540 JK035 SMTR LFS	230 ± 50	300,000

Packaging

Switches in reels of 10,000 pieces. Dimensions of reels according to EIA 481B External diameter 330 mm

Electrical

Environmental

OPERATING TEMPERATURE: -30°C to 85°C

Process


SOLDERING: This component is suited to the following methods: Infrared Reflow Soldering in accordance with IEC61760-1

NOTE: Specifications listed above are for switches with standard options. For information on specific and custom switches, consult Customer Service Center.

How To Order


Our easy build-a-switch concept allows you to mix and match options to create the switch you need. To order, select desired option from each category and place it in the appropriate box.

For any part number different from those listed above, please consult your local representative.





PTS 540



RECOMMENDED PCB 1 3

