



P.C.B LAYOUT(copper-sided view)



Rating:0.5A 30V DC
 Contact Resistance:100 mΩ Max.
 Operating temperature:-20℃~70℃
 Operating force:3~20N
 Operating Life:5,000cycles

Model No.	PJ-237-A
Schematic	

② Terminal	6	Phosphor bronze	Au Plating			
① Housing	1	Nylon	Black			
ITEM PART NAME	TER.NO. QTY.	MATERIAL	FINISHING	REMARK		
APPROVALS		DATE				
DRAWN JKUN.LU	2013/11/11	TITLE: PHONE JACKES				
CHECKED		ELECTRONICS CO.,LTD				
APPROVALS		PART NO.	PJ-237			
TOLERANCES ARE		SCALE: 1:1	PROJ:			
30~0.1	±0.30	ANGLE	SHEET 1 OF 1			
10~0.30	±0.20	UNIT: mm				
5~10	±0.15	DRAWING NO.				
~5	±2'					
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			