


P.C. Blyayout(copper-sided view)



L=5.5 L1=4.0	PJ-203-A	PJ-203-B
Schematic		
L=5.5 L1=4.0	PJ-203-G	
Schematic		

Rating:0.5A 30V DC
 Contact Resistance:100 mΩ Max.
 Operating temperature:-20℃~70℃
 Operating force:3-20N
 Operating Life:5,000cycles

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			

② Terminal	5	Phosphor bronze	Au Plating
① Housing	1	Nylon	Black
ITEM	PART NAME	TER.NO.	QTY.
APPROVALS		DATE	
DRAWN	J.X.Zhang	2013/11/11	
CHECKED			
APPROVALS			
TOLERANCES ARE		30~0.1	±0.30
	10~30	±0.20	ANGLE
	5~10	±0.15	UNIT: mm
	~5	±0.10	SCALE: 1:1
		±2'	DRAWING NO.
TITLE:		PHONE JACKES	
PART NO.		PJ-203	
DRAWN		PROJ.	
DATE		SHEET 1 OF 1	
ELECTRONICS CO.,LTD			