



CIRCUIT DIAGRAM

Rating:0.5A 30V DC
 Contact Resistance:100 mΩ Max.
 Operating temperature:-20℃~70℃
 Operating force:3-20N
 Operating Life:5,000cycles

P C B Layout(Top view)

②	Shunt terminal	6	Phosphor bronze	Plating Au		
①	Housing	1	PPA	Black		
ITEM	PART NAME	Serial number	QTY.	MATERIAL	FINISHING	REMARK
APPROVALS		DATE		ELECTRONICS CO.,LTD TITLE: PHONE JACKS PART NO. PJ-604		
DRAWN	xu qi feng	2014.11.25				
CHECKED						
APPROVALS				UNIT: mm	SCALE: 1:1	PROJ:
TOLERANCES ARE		30~以下: ±0.30	10~30: ±0.20	ANGLE	DRAWING NO.	SHEET 1 OF 1
		5~10: ±0.15	~ 5: ±0.10	±2'		

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			