


适用电线范围 Suitable Wires A. W. G.	额定电气规格 Electrical Ratings			公差 Tolerance	品名 Parts Name 型号 Part NO.	印刷电路板型端子台 (垂直焊针) PA001-2P
	电压	温度	电流			
26-14AWG ² 0.5-1.5MM ²	300V (UL) 250V (IEC)	75° C (UL), -30° C to T110° C (IEC)	10A (UL) 17.5A (IEC)	0. = ±0.1MM 00. = ±0.2MM 000. = ±0.3MM	材质 MATERIAL PA66 铜合金	颜色 Color 绿色 Green



介绍:
 剥线长度: 6mm (公里) / 0.24in. (吋)
 间距: 5mm
 胶壳: 尼龙66工程塑料
 线座: 铜合金, 镀锡; 方形接线孔
 螺丝: 碳钢线, 镀锌; M2. 6x5mm
 弹片: 不锈钢
 相关认证: CE, VDE, FIMKO UL CSA



DIMENSION	TOLERANCES	FRIST ANGLE PROJ			
0.0 0.00	0. = ±0.1MM 00. = ±0.2MM 000. = ±0.3MM				
		A	NEW PART	DATE	
		LTR.	REVISION RECORD	DWG. BY	CHK. BY

未经许受权不得修改和复印
 该知识产权属于技术质量部

DWG. BY	<i>Lin Liang</i>	UNIT	mm
CHK. BY	<i>William</i>	REV.	A
APP. BY	<i>wang shiyuan</i>	DWG. NO.	HIWA/OR-JZ-41-001-2

HWA 惠华苏州惠华电子科技有限公司