




NOTE:

- 1) 功能: USB2.0 TO RS232 CONVERTER
- 2) 連接器: DB 9PIN PLUG & USB A/M
- 3) CABLE: 不帶 CABLE
- 4) 電源: 不帶電源
- 5) 工作溫度: 0 至 75 °C
- 6) 儲存溫度: -65 至 150 °C
- 7) 重量: 9g
- 8) 尺寸: 附圖紙
- 9) 操作系統: 支援 Windows 8(32/64)/Windows 7(32/64)/Windows 10(32/64)/Vista(32/64)/XP(32/64)/Server 2008(32/64)/Server 2003(32/64)/ME/98/CE(V4.2及以上版本)/Linux(2.4及以上版本)/Mac OS (8、9及以上版本)
- 10) 包裝: USB2.0 TO RS232 ADAPTOR, 光碟, USB CABLE
- 11) 紙箱: 46*30*30CM SLAYER 50PC
- 12) 產品符合RoHS標準






CUSTOMER NO:

REMARK

A2	CHANGE SCREW	FYS	2015/12/26
REV. ECR	DESCRIPTION	C.N.	DATE
ELECTRONIC LTD.			
TITLE: USB2.0 TO RS232(雙色模)ADAPTOR ROHS			
TOLERANCE		CHKD.	
±0.10mm		CONF.	
±0.13mm		DIR.	
±0.15mm		APRD.	
150.01mm	1	±0.20mm	PART NO.
MATERIAL MATERIAL		ZE551A	
FINISH FINISH	1/1	UNIT MM	SIZE A4
		REV.	A2

CUSTOMER NO:	REMARK
--------------	--------






合骨袋	P1	PINOUT:	P2
1	RED	1	WHITE
2	BLACK	2	GREEN
3	BRAID	3	SHELL
4	SHELL	4	SHELL

- NOTES:
- 1) PRIMARY DIM: A, B
 - 2) SHORT AND OPEN 100% TESING INSULATION RESISTANCE:5MΩ CONTACT RESISTANCE: 5Ω HI -POT: DC 300V
 - 3) 外模為雙色模(藍色+白色); 藍色色碼為: 2955C; 白色色碼為: 1901
 - 4) 線材為藍色, 色碼為: 2955C
 - 5) 合骨袋包裝
 - 6) 長度條碼貼紙貼在合骨袋左上角, 如圖: ③
 - 7) 產品符合"ROHS"規範

A	FIRST EDITION	FYS	2014/05/12
REV. ECR	DESCRIPTION	C.N.	DATE
ELECTRONIC LTD.			
TITLE: USB2.0 A/M TO A/F BLUE CABLE 1.5M ROHS(外模: 白色+藍色)			
DIMENSIONS ARE IN MILLIMETERS		CONF.	
ANGULAR TOLERANCE: ±1.0°	TOLERANCE		
0.00 TO 30.00mm ±0.10mm	±0.10mm		
30.01 TO 80.00mm ±0.13mm	±0.13mm		
80.01 TO 150.00mm ±0.15mm	±0.15mm		
150.01mm ±0.20mm	±0.20mm		
MATERIAL FINISH	MODEL NO.	SCALE	SHEET
PINISH	ZY149	MM	1/1
		SIZE	REV.
		A4	A

CUSTOMER NO:	REMARK
--------------	--------






NOTES:

- 1) PRIMARY DIM: A, B
- 2) SHORT AND OPEN 100% TESING INSULATION RESISTANCE: 20MΩ CONTACT RESISTANCE: 5Ω HI-POT: DC 300V
- 3) 線材 & 外模均為黑色
- 4) P1 & P2 DIE NO: ZOF017, ZOF035
- 5) 複合袋包裝
- 6) 長度條碼貼紙貼在複合袋左上角, 如圖 ⑨
- 7) 產品符合"ROHS"規範

REV. ECR	FIRST EDITION	DESCRIPTION	C.N.	DATE
A		ELECTRONIC LTD.		FYYS 2015/12/31
<p>THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF CO-IMPORTER LIMITED AND SHALL NOT BE REPRODUCED COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF CO-IMPORTER LIMITED.</p> <p>UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN MILLIMETERS ANGULAR TOLERANCE: ±1°</p> <p>TITLE: DB9/F TO DB9/F BLACK CABLE 1.5M ROHS</p> <p>CHKD: _____ CON'F: _____</p> <p>DR: _____ APPD: _____</p> <p>MODEL NO: ZC291</p> <p>SCALE: / SHEET: 1/1 UNIT: MM SIZE: A4 REV: A</p>				
DB9/F		2	BROWN	3
DB9/F		3	RED	2
DB9/F		4	BLACK	1,6
DB9/F		5	YELLOW	5
DB9/F		1,6	ORANGE	4
DB9/F		7	WHITE	8
DB9/F		8	PURPLE	7
DB9/F		SHELL	DRAIN	SHELL

CUSTOMER NO:	REMARK
--------------	--------



1	DB9/M	BLACK	DB9/F
2	BROWN	1	
3	RED	2	
4	ORANGE	3	
5	YELLOW	4	
6	PINK	5	
7	WHITE	6	
8	PURPLE	7	
9	GRAY	8	
	DRAIN	9	
	SHELL	9	SHELL

- NOTES:
- 1) PRIMARY DIM: A, B
 - 2) SHORT AND OPEN 100% TESING INSULATION RESISTANCE: 20MΩ CONTACT RESISTANCE: 5Ω HI-POT: DC 300V
 - 3) 線材 & 外模均為黑色
 - 4) P1 & P2 DIE NO: ZOF017, ZOF035
 - 5) 復合袋包裝
 - 6) 長度條碼貼紙貼在復合袋左上角, 如圖 ⑩
 - 7) 產品符合"RoHS"規範

A	FIRST EDITION		FYS	2015/12/31
REV. ECR	DESCRIPTION	C.N.	DATE	
THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF CO-MPTON LIMITED AND SHALL NOT BE REPRODUCED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF CO-MPTON LIMITED.				
TITLE		ELECTRONIC LTD.		
DB9/M TO DB9/F BLACK CABLE 1.5M ROHS		CONP-		
CHKD.		APPD.		
DIMENSIONS		TOLERANCE		
0.00 TO 30.00mm	±0.10mm			
30.01 TO 80.00mm	±0.13mm			
80.01 TO 150.00mm	±0.15mm			
150.01mm	±0.20mm			
MATERIAL	MODEL NO.	ZC292		
FINISH	SCALE	SHEET	UNIT	SIZE
	/	1/1	MM	A4
				REV. A