


• E49A Series DIP 49US Crystal



This part is a miniature AT cut strip crystal units with a low profile package. It is with resistance weld.

FEATURES

- Low Cost
- Industry Standard
- Wide Frequency Range
- Excellent Aging

Electrical Specifications


Type	E49A	
Frequency Range	F0	3.2~66.000MHz
Load Capacitance	CL	10pF to Series
Frequency Tolerance	$\Delta F / F_0$	$\pm 10\text{ppm}, \pm 30\text{ppm}, \pm 50\text{ppm}(\text{At } 25^\circ\text{C})$
Equivalent Series Resistance	ESR	See Table 1
Temperature Stability	TC	$\pm 10\text{ppm}, \pm 30\text{ppm}, \pm 50\text{ppm}(\text{Refer to } 25^\circ\text{C})$
Operating Temperature Range	TOPR	-20~+70°C, -30~+85°C Option
Storage Temperature Range	TSTG	-55~+125°C
Shunt Capacitance	C0	7pF max.
Insulator Resistance	IR	500M Ω min. (At 100VDC)
Drive Level	DL	100 μ W(500 μ W max.)
Aging	Fa	$\pm 5\text{ppm max. (At } 25^\circ\text{C, First year)}$
Packing Unit		200pcs/bag

Table 1:Equivalent Series Resistance(ESR) and Mode of Vibration(Mode)

Frequency Range(MHz)	Max ESR(Ω)	Mode	Frequency Range(MHz)	Max ESR(Ω)	Mode
3.200 to 4.499	150	Fundamental/AT	9.000 to 9.999	60	Fundamental/AT
4.500 to 5.999	120	Fundamental/AT	10.000 to 12.999	50	Fundamental/AT
6.000 to 6.999	100	Fundamental/AT	13.000 to 40.000	40	Fundamental/AT
7.000 to 7.999	90	Fundamental/AT	40.000 to 66.000	80	3 rd Overtone
8.000 to 8.999	80	Fundamental/AT			

**Please contact us for inquiries regarding other Specifications

Mechanical Dimensions(mm)



TAIWAN:

HOSONIC ELECTRONIC CO., LTD.
23-1 LANE 84, CHUN YING ST. SHULIN CHEN.
TAIPEI 23804, TAIWAN
WEB SITE:<http://www.hosonic.com>

☎: 886-2-86875200
☎: 886-2-26816456
✉: hosonic.sales@hosonic.com

CHINA:

HANGZHOU HOSONIC ELECTRONIC CO., LTD.
NO.242 LIANGBO ROAD, LIANGZHU TOWN.
YUHANG DISTRICT, HANGZHOU, ZHEJIANG, CHINA
WEB SITE:<http://www.hosonic.com>

☎: 86-571-88778189
☎: 86-571-88778857
✉: hosonic.sales@hosonic.com

Specifications are subject to change without notice