




序号	变更内容	日期	版本
1			
2			



HOUSING

Part No: 3962H
 Material: Nylon 66 UL94V-0
 Insulation resistance: 1000M OHM /min
 Withstand voltage: 1000V AC/minuite
 Voltage rating: 250V AC/DC
 Temperatuer range: -25° c to +85° c

未注公差:
 X.X: ±0.50
 X.XX: ±0.25
 X.XXX: ±0.10

Circuits	Part NO	Dimension(mm)	
		A	B
2	3962H-2P	3.96	7.90
3	3962H-3P	7.92	11.80
4	3962H-4P	11.88	15.80
5	3962H-5P	15.84	19.80
6	3962H-6P	19.80	23.70
7	3962H-7P	23.76	27.70
8	3962H-8P	27.72	31.60
9	3962H-9P	31.68	35.60
10	3962H-10P	35.64	39.60
11	3962H-11P	39.60	43.60
12	3962H-12P	43.56	47.70
13	3962H-13P	47.52	51.60
14	3962H-14P	51.48	55.60
15	3962H-15P	55.44	59.60

品名:	3962H-XXP	比例	单位	图纸	图号
客户料号:		2:1	mm	1/1	S80386
制图:	刘海平		深圳市灿科盟实业有限公司 CHANKLEMENT INDUSTRY CO., LTD		
审核:					