





SPEC. A-A



SPECIFICATIONS
 Current Rating: 1A AC/DC
 Pitch Between Poles: 1.25mm
 Voltag rating: 125V AC/DC
 Contact Resistance: 20MΩ max
 Temperature Range: -25℃ TO +85℃
 Insulation Resistance: 100MΩ min
 Withstand Voltage: 500V AC/minute

MATERIAL
 Material: Nylon66 UL94V-2

| Poles | Part No. | Dimension mm | | |
|-------|-----------|--------------|-------|-------|
| | | A | B | C |
| 2 | 1251H-2P | 4.25 | 1.25 | 2.95 |
| 3 | 1251H-3P | 5.50 | 2.50 | 4.20 |
| 4 | 1251H-4P | 6.75 | 3.75 | 5.45 |
| 5 | 1251H-5P | 8.00 | 5.00 | 6.70 |
| 6 | 1251H-6P | 9.25 | 6.25 | 7.95 |
| 7 | 1251H-7P | 10.50 | 7.50 | 9.20 |
| 8 | 1251H-8P | 11.75 | 8.75 | 10.45 |
| 9 | 1251H-9P | 13.00 | 10.00 | 11.70 |
| 10 | 1251H-10P | 14.25 | 11.25 | 12.95 |
| 11 | 1251H-11P | 15.50 | 12.50 | 14.20 |
| 12 | 1251H-12P | 16.75 | 13.75 | 15.45 |
| 13 | 1251H-13P | 18.00 | 15.00 | 16.70 |
| 14 | 1251H-14P | 19.25 | 16.25 | 17.95 |
| 15 | 1251H-15P | 20.50 | 17.50 | 19.20 |
| 16 | 1251H-16P | 21.75 | 18.75 | 20.45 |

TOLERANCE TABLE

| | |
|------|-------|
| .0 | ±0.20 |
| .00 | ±0.10 |
| .000 | ±0.05 |

| | | |
|-------------|------------------|--|
| APPROVED: | DATE: | 深圳市炬科盟实业有限公司 Chantw/CHANKLEMENT INDUSTRY CO., LTD |
| CHECKED: | DATE: | |
| DRAWN: | DATE: | TITLE: |
| LYF | 2008-04-07 | 1251H-XP |
| CLIENT P/N: | / | UNIT |
| | | mm |
| | | SCALE |
| | | free |
| FILE NO. | Chantw-1251-0005 | REV. |
| | | A |