





SPEC. A-A



**SPECIFICATIONS**

Current Rating: 1A AC/DC  
 Pitch Between Poles: 1.25mm  
 Voltag rating: 125V AC/DC  
 Contact Resistance: 20MΩ max  
 Temperature Range: -25℃ TO +85℃  
 Insulation Resistance: 100MΩ min  
 Withstand Voltage: 500V AC/minute

**MATERIAL**

Material: Nylon66 UL94V-2

Poles	Part No.	Dimension mm		
		A	B	C
2	1251H-2P	4.25	1.25	2.95
3	1251H-3P	5.50	2.50	4.20
4	1251H-4P	6.75	3.75	5.45
5	1251H-5P	8.00	5.00	6.70
6	1251H-6P	9.25	6.25	7.95
7	1251H-7P	10.50	7.50	9.20
8	1251H-8P	11.75	8.75	10.45
9	1251H-9P	13.00	10.00	11.70
10	1251H-10P	14.25	11.25	12.95
11	1251H-11P	15.50	12.50	14.20
12	1251H-12P	16.75	13.75	15.45
13	1251H-13P	18.00	15.00	16.70
14	1251H-14P	19.25	16.25	17.95
15	1251H-15P	20.50	17.50	19.20
16	1251H-16P	21.75	18.75	20.45

**TOLERANCE TABLE**

.0	±0.20
.00	±0.10
.000	±0.05

<b>APPROVED:</b>	<b>DATE:</b>	<p>深圳市灿科盟实业有限公司          CHANKLEMENT INDUSTRY CO., LTD</p>
<b>CHECKED:</b>	<b>DATE:</b>	
<b>DRAWN:</b> LYF	<b>DATE:</b> 2008-04-07	<b>TITLE:</b> 1251H-XP <b>CLIENT P/N:</b> / <b>UNIT:</b> mm <b>SCALE:</b> free <b>FILE NO.:</b> Chantw-1251-0005
		<b>REV.:</b> A