



# Spring Contact SCTA\_A Series (Standard Type)

Part number	SCTA3A0103	
Dimensions (W×D)	1.4×1.4mm	
Height in use	1.0 to 1.4mm	
Travel	0.6mm	
Mounting type	Surface mounting type	
Mounting style	Standard mount	
Packing system	Taping	
Minimum order unit (pcs.)	12,000	
Operating temprature range	-30℃ to +85℃	
Rated current	3A	
Contact resistance (Initial)	Connector contacts $40m\Omega$ max.	
Stroke Frequency	500 times	

### **Dimensions**




Land Dimensions



## **Packing Specifications**






Number of packages (pcs.)	s 1 reel	12,000
	1 case / Japan	36,000
	1 case / export packing	72,000

8

Export package measurements (mm)

403×403×167

## **Soldering Conditions**



Temperature on the surface of PWB

#### Notes are common to this series/models.

- 1. This site catalog shows only outline specifications. When using the products, please obtain formal specifications for supply.
- 2. Please place purchase orders per minimum order unit (integer).