








<b>PRODUCT NO.</b>	1
<b>DISCOSTSGER</b>	RoHS compliant



**RECOMMENDED P.C.B. LAYOUT (TOP VIEW)**



Number	Part Name	Material	Finished
①	Actuator	UL94 V0	White
②	Cover	UL94 V0	Black
③	Movable	Copper Alloy	3u"Gold
④	Terminal	Brass	1u"Gold
⑤	Base	UL94 V0	Black
⑥	Terminal Contact	Brass	3u"Gold
⑦	Mylar	UL94 V0	0.05mm

TOLERANCE UNLESS OTHERWISE SPECIFIED		INSPECTION COPY	
LINER	ANGLES	PROJECTION	COPY
0 ± 0.25	0 ± 2'		BY DISC SERIES PITCH 2.54mm
.00 ± 0.15	.0 ± 1'		
.000 ± 0.10	.00 ± 0.5'	DESIGN	2012/04/12
DRAWING		PRAT NO.	DISCOSTSGER
CHECK		FILE NO.	DISCOSTSGER-A
APPRO.		SIZE	UNIT SCALE SHEET REV.
		A4	mm 2 : 1 10F 1 A

**RE** 东莞市广聚实业有限公司  
Dongguan Kingtek Industrial Co., Ltd.

PRODUCT FAMILY DISC SERIES

- NOTES :**
- 1> Specification:
- 1> Operating force: 1000gf Max
  - 2> Operating Temperature: -40° to +85°
  - 3> Storage Temperature: -40° to +85°
  - 4> Mechanical Life: 3000cycles minimum
  - 5> Electrical Life: 2000cycles 25mA 24VDC
2. PLATING:
- GOLD FLASH 1u"(min.) SOLDER TAIL, 3u" GOLD PLATING ON THE CONTACT AREA, WITH 50u" NICKEL UNDERPLATING OVERALL.
3. PART NUMBER DESCRIPTION

REV.	ECN NO.	DR	DATE