

PRODUCT NO.	DSHP01TSGER
RoHS compliant	






NOTES :1.Specification:

- 1>.Operating force:1000gf Max
- 2>.Operating Temperature: -40° to+85°
- 3>.Storage Temperature: -40° to+85°
- 4>.Electrical Life:1000cycles 25mA 24VDC
- 5>.Mechanical Life:3000cycles Operations



2. PLATING:
GOLD FLASH 1u"~2u" SOLDER TAIL,
1u"~3u" GOLD PLATING ON THE CONTACT AREA,
WITH 50u" NICKEL UNDERPLATING OVERALL.

3. PART NUMBER DESCRIPTION :

DSHP XX I S G E R
 [包装方式: T=管装 R=Reel]
 [电镀层: E=接触部1u"~3u" 焊脚部1~2u" G=接触部30u"
 焊脚部30u" F=接触部0u" 焊脚部0u"
 [G=镀全金 S=内镀金(接触部)外镀镍(焊脚部)]
 [脚型: S脚 / J脚 / A脚 / Z脚]
 [T=低推贴膜 S=低推不贴膜 L=长推]
 [产品P数: 02=2P 04=4P 06=6P 08=8P 10=10P 12=12P]



RECOMMENDED P.C.B. LAYOUT (TOP VIEW)



1	2	3	4	5	6
---	---	---	---	---	---

Number	Part Name	Material	Finished
①	Actuator	UL94 V0	White
②	Cover	UL94 V0	Black
③	Movable	Beryllium Copper	3μ Gold
④	Terminal	Brass	1μ~2μ Gold
⑤	Base	UL94 V0	Black
⑥	Terminal Contact	Brass	1μ~3μ Gold
⑦	Mylar	UL94 V0	0.05mm

TOLERANCE UNLESS OTHERWISE SPECIFIED		INSPECTION COPY	
LINER	ANGLES	PROJECTION	
0 ± 0.25	0 ± 2'		
.00 ± 0.15	.0 ± 1'		
.000± 0.10	.00± 0.5'		
DESIGN	kathy	03/20/12	
DRAWING			
CHECK			
APPRO.			
东莞市广睿实业有限公司 Dongguan Kingtek Industrial Co., Ltd. BY DSHP SERIES PITCH 1.27mm PRODUCT FAMILY DSHP SERIES PRAT NO. DSHP01TSGER FILE NO. DSHP01TSGER-A SIZE UNIT SCALE SHEET REV. A4 mm Z : 1 1OF 1 A			

1	2	3	4	5	6
---	---	---	---	---	---