



PCB Layout

**SPECIFICATION**  
 Current Rate: 3Amp  
 Insulation Resistance: 5000MΩ MIN atDC500V  
 Dielectric Strength: AC500V PER minute  
 Operation Temperature: -40°to +105°

**MATERIAL**

Insulator: Polyester, UL94V-0  
 Standard: P.B.T  
 CONTACT: Brass  
 Contact plated: Gold 0.8u Over Nickel  
 Poles: 2~40P (Double)

TOLERANCE TABLE	
.0	±0.20
.00	±0.10
.000	±0.05

APPROVED:	DATE:	深圳市灿科盟实业有限公司 KIMT W CHANKEMENG INDUSTRY CO., LTD
CHECKED:	DATE:	
DRAWN:	DATE:	TITLE:
LYP	2008-04-29	220S-2*XP H=8.5MM 蓝胶
		CLIENT P/N /
UNIT	mm	SCALE
		free
REV.		FILE NO.
		A