



Specification

Power Pins: 1AMP
 Dielectric Withstanding Voltage:
 AC 1000V/60 sec.r.m.s
 Insulation Resistance:
 1000M Min at DC500V
 Contact Resistance: 20m Max
 Durability: 100gf cycles Min
 Terminal Retention Force:
 2.27kg fper contact Min

Material

Contacts: Brass
 Insulator: P.B.T UL 94V-0 Rate
 Planted: Gold over
 Operating Temperature:
 -40°C to 105°C

未注公差 (TOLERANCE)		绘图 (DRAWN)	change	单位(SCALE)	mm	料号 (PART NO.)	
X	±2°	X		投影(PROJECT)	第一角投影	料号(DRAW NO.)	
X	±1°	X	校对 (CHECKED)	比例(ACALE)	5:1	品名	Female Header
.XX	±0.5°	.XX	核准 (APPROVED)	版本(EDITION)	2009-03-18	(NAME)	2.54mm
.XXX		.XXX		日期 (DATE)			
						175-9F04V021-E	