



# For microSD™ Memory Card (Push-push Type) SCHA Series

Part number		SCHA4B0419
Applicable media		microSD™ Memory Card
Media ejection structure		Push-push type
Mounting type		Surface mounting type
Mounting style		Standard mount
Features		With switches and fly-out protection
Stand-off		0mm
Packing system		Taping
Minimum order unit (pcs.)		2,000
Operating temperature range		-20℃ to +70℃
Voltage proof		500V AC 1minute
Insulation resistance (Initial)		1,000MΩ min.
Contact resistance (Initial)	Connector contacts	100mΩ max.
	Detection Switch	500mΩ max.
Insertion and removal cycle		10,000 cycles


# Photo



### **Dimensions**




# **Mounting Dimensions**



Viewed from mounting face side.

# **Packing Specifications**

### **Taping**



Number of packages (pcs.)	s 1 reel	2,000
	1 case / Japan	6,000
	1 case / export packing	12,000
Reel width W(mm)		24.4
Tape width (mm)		24
Export package measurements (mm)		403×403×249

# **Soldering Conditions**

## **Example of Reflow Soldering Condition (Reference)**


1. Heating method

Double heating method with infrared heater.

2. Temperature measurement

Thermocouple 0.1 to 0.2  $\Phi$  CA (K) or CC (T) at soldering portion.

3. Temperature profile.



# Notes are common to this series/models.

- 1. This site catalog shows only outline specifications. When using the products, please obtain formal specifications for supply.
- 2. Please place purchase orders per minimum order unit (integer).