

**Specification**

Insulator Material: Polyesetr, UL94V-0

Standard: P.B.T

Contact Material: Brass

Contact plated: Gold Over 50u" Nickel

Poles: 2~40P


Current Rating : 3Amp

Contact Resistance: 20 Milliohms Max

Insulation Resistance : 1000M Ω Min.

Dielectric withstanding Voltage: AC 500V

Operation Temperature : -40 °C -- +105 °C

APPROVED:	DATE:	 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRYCO., LTD			
CHECKED:	DATE:	TITLE: 210S-1*XP (6.0/2.54/3.0)			
DRAWN:	DATE:	CLIENT	P/N	/	
LYF	2010-08-12	UNIT	mm	SCALE	free
TOLERANCE TABLE .0 ±0.20 .00 ±0.10 .000 ±0.05		FILE NO.	Ckmtw-210-00001	REV.	A