




SPECIFICATIONS

Current rating: 3A AC/DC
 Voltage rating: 250V AC/DC
 Contact resistance: 20mΩ max.
 Withstand voltage: 1000V AC/min
 Insulation resistance: 1000MΩ/min.
 Temperature range: -25° C~+85° C

Material:

Part No: 2~15
 Housing: Nylon66, UL 94V-0



| Poles | Part No | Dimension mm | |
|-------|-----------|--------------|------|
| | | A | B |
| 2 | 2503H-2P | 2.50 | 6.0 |
| 3 | 2503H-3P | 5.00 | 8.5 |
| 4 | 2503H-4P | 7.50 | 11.0 |
| 5 | 2503H-5P | 10.00 | 13.5 |
| 6 | 2503H-6P | 12.50 | 16.0 |
| 7 | 2503H-7P | 15.00 | 18.5 |
| 8 | 2503H-8P | 17.50 | 21.0 |
| 9 | 2503H-9P | 20.00 | 23.5 |
| 10 | 2503H-10P | 22.50 | 26.0 |
| 11 | 2503H-11P | 25.00 | 28.5 |
| 12 | 2503H-12P | 27.50 | 31.0 |
| 13 | 2503H-13P | 30.00 | 33.5 |
| 14 | 2503H-14P | 32.50 | 36.0 |
| 15 | 2503H-15P | 35.00 | 38.5 |

TOLERANCE TABLE

| | |
|------|-------|
| .0 | ±0.20 |
| .00 | ±0.10 |
| .000 | ±0.05 |

| | | |
|------------|-----------------|---|
| APPROVED: | DATE: | 深圳市灿科盟实业有限公司 C km tw CHANKEMENG INDUSTRYCO., LTD |
| CHECKED: | DATE: | |
| DRAWN: | DATE: | TITLE: |
| LYF | 2008-04-07 | 2503H-XP |
| CLIENT P/N | | SCALE |
| UNIT | mm | free |
| FILE NO. | Ckmtw-2503-0002 | REV. |
| | | A |