



SPECIFICATION

Poles: 2-24

Voltage rating: AC, DC 250V

Current rating: AC, DC, 7A

Withstand voltage: 1500V AC/min.

Insulation resistance: 1000M Ω/min.

Temperature range: -25°C ~ +85°C

Applicable PC board thickness: 0.031" ~ 0.063" (0.8 ~ 1.6mm)

Contact resistance: Initial value/10m Ω max.

After environmental

testing/20m Ω max.

Material: Nylon66 UL94V-2

APPROVED:

DATE:

深圳市灿科盟实业有限公司
CKimtW CHANKLEMENT INDUSTRYCO., LTD

CHECKED:

DATE:

TITLE:
5557HP-2*XP

TOLERANCE TABLE

.0	±0.20
.00	±0.10
.000	±0.05

DRAWN:

DATE:

CLIENT P/N /	
UNIT	SCALE
mm	free
FILE NO.	REV.
CKimtW-5557-0007	A

LYF **2008-04-07**