# PESD5V0S1BA; PESD5V0S1BB; PESD5V0S1BL

Low capacitance bidirectional ESD protection diodes

Rev. 04 — 20 August 2009

**Product data sheet** 

#### **Product profile** 1.

### 1.1 General description

Low capacitance ElectroStatic Discharge (ESD) protection diodes in ultra small SMD plastic packages designed to protect one signal line from the damage caused by ESD and other transients.

#### **Product overview** Table 1.

| Type number | Package |       |  |
|-------------|---------|-------|--|
|             | NXP     | JEITA |  |
| PESD5V0S1BA | SOD323  | SC-76 |  |
| PESD5V0S1BB | SOD523  | SC-79 |  |
| PESD5V0S1BL | SOD882  | -     |  |

### 1.2 Features

- Bidirectional ESD protection of one line ESD protection > 30 kV
- Max. peak pulse power: P<sub>PP</sub> = 130 W
- Low clamping voltage: V<sub>(CL)R</sub> = 14 V
- Ultra low leakage current: I<sub>RM</sub> = 5 nA

### 1.3 Applications

- Cellular handsets and accessories
- Portable electronics
- Computers and peripherals

# 1.4 Quick reference data

- IEC 61000-4-2, level 4 (ESD)
- IEC 61000-4-5 (surge); I<sub>PP</sub> = 12 A
- Ultra small SMD plastic packages
- Communication systems
- Audio and video equipment

| Symbol           | Parameter                 | Conditions                         | Min | Тур | Max | Unit |
|------------------|---------------------------|------------------------------------|-----|-----|-----|------|
| V <sub>RWM</sub> | reverse stand-off voltage |                                    | -   | -   | 5   | V    |
| C <sub>d</sub>   | diode capacitance         | V <sub>R</sub> = 0 V;<br>f = 1 MHz | -   | 35  | 45  | pF   |



### Low capacitance bidirectional ESD protection diodes

## 2. Pinning information

| Pin       | Description | Simplified outline      | Symbol        |
|-----------|-------------|-------------------------|---------------|
| SOD323, 9 | SOD523      |                         |               |
| 1         | cathode 1   |                         |               |
| 2         | cathode 2   | 1 2<br>001aab540        | 1 2<br>sym045 |
| SOD882    |             |                         |               |
| 1         | cathode 1   |                         |               |
| 2         | cathode 2   | 1 2                     | 1 2<br>sym045 |
|           |             | Transparent<br>top view |               |

# 3. Ordering information

#### Table 4.Ordering information

| Type number | Package |  |         |  |  |  |
|-------------|---------|--|---------|--|--|--|
|             | Name    | Description  | Version |  |  |  |
| PESD5V0S1BA | SC-76   | plastic surface mounted package; 2 leads   | SOD323  |  |  |  |
| PESD5V0S1BB | SC-79   | plastic surface mounted package; 2 leads   | SOD523  |  |  |  |
| PESD5V0S1BL | -       | leadless ultra small plastic package; 2 terminals; body $1.0 \times 0.6 \times 0.5$ mm | SOD882  |  |  |  |

### 4. Marking

| Table 5. Marking codes |              |
|------------------------|--------------|
| Type number            | Marking code |
| PESD5V0S1BA            | E6           |
| PESD5V0S1BB            | L7           |
| PESD5V0S1BL            | F1           |

### Low capacitance bidirectional ESD protection diodes

### 5. Limiting values

#### Table 6.Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134).

| Symbol           | Parameter            | Conditions |               | Min | Max  | Unit |
|------------------|----------------------|------------|---------------|-----|------|------|
| Per diode        |                      |            |               |     |      |      |
| P <sub>PP</sub>  | peak pulse power     | 8/20 μs    | [1][2]        | -   | 130  | W    |
| I <sub>PP</sub>  | peak pulse current   | 8/20 μs    | <u>[1][2]</u> | -   | 12   | А    |
| Tj               | junction temperature |            |               | -   | 150  | °C   |
| T <sub>amb</sub> | ambient temperature  |            |               | -65 | +150 | °C   |
| T <sub>stg</sub> | storage temperature  |            |               | -65 | +150 | °C   |

 Non-repetitive current pulse 8/20 μs exponentially decaying waveform according to IEC61000-4-5; see Figure 1.

[2] Measured from pin 1 to pin 2.

#### Table 7. ESD maximum ratings

| Symbol | Parameter                          | Conditions                        | Min             | n Max | Unit |
|--------|------------------------------------|-----------------------------------|-----------------|-------|------|
| ESD    | electrostatic discharge capability | IEC 61000-4-2 (contact discharge) | <u>[1][2]</u> _ | 30    | kV   |
|        |                                    | HBM MIL-Std 883                   | -               | 10    | kV   |

[1] Measured from pin 1 to pin 2.


[2] Device stressed with ten non-repetitive ElectroStatic Discharge (ESD) pulses; see Figure 2.

#### Table 8.ESD standards compliance

| Standard                               | Conditions                      |
|--|---------------------------------|
| IEC 61000-4-2, level 4 (ESD); Figure 2 | > 15 kV (air); > 8 kV (contact) |
| HBM MIL-STD 883; class 3               | > 4 kV                          |

# PESD5V0S1BA/BB/BL

Low capacitance bidirectional ESD protection diodes



Low capacitance bidirectional ESD protection diodes

### 6. Characteristics

### Table 9. Characteristics

 $T_{amb} = 25 \circ C$  unless otherwise specified


| Symbol             | Parameter                 | Conditions  |        | Min | Тур | Max | Unit |
|--------------------|---------------------------|---|--------|-----|-----|-----|------|
| Per diode          |                           |   |        |     |     |     |      |
| V <sub>RWM</sub>   | reverse stand-off voltage |   |        | -   | -   | 5   | V    |
| I <sub>RM</sub>    | reverse leakage current   | V <sub>RWM</sub> = 5 V;<br>see <u>Figure 6</u>          |        | -   | 5   | 100 | nA   |
| V <sub>(CL)R</sub> | clamping voltage          | I <sub>PP</sub> = 1 A                                   | [1][2] | -   | -   | 10  | V    |
|                    |                           | I <sub>PP</sub> = 12 A                                  | [1][2] | -   | -   | 14  | V    |
| V <sub>(BR)</sub>  | breakdown voltage         | I <sub>R</sub> = 1 mA                                   |        | 5.5 | -   | 9.5 | V    |
| r <sub>dif</sub>   | differential resistance   | I <sub>R</sub> = 1 mA                                   |        | -   | -   | 50  | Ω    |
| C <sub>d</sub>     | diode capacitance         | V <sub>R</sub> = 0 V; f = 1 MHz;<br>see <u>Figure 5</u> |        | -   | 35  | 45  | pF   |
|                    |                           |   |        |     |     |     |      |

[1] Non-repetitive current pulse 8/20 µs exponentially decaying waveform according to IEC61000-4-5; see Figure 1.

[2] Measures from pin 1 to pin 2.


# PESD5V0S1BA/BB/BL

### Low capacitance bidirectional ESD protection diodes



# PESD5V0S1BA/BB/BL


#### Low capacitance bidirectional ESD protection diodes



#### Low capacitance bidirectional ESD protection diodes

### 7. Application information

PESD5V0S1Bx series is designed for the protection of one bidirectional signal line from the damage caused by ElectroStatic Discharge (ESD) and surge pulses. The devices may be used on lines where the signal polarities are above and below ground. They provide a surge capability of up to 130 W per line for a 8/20  $\mu$ s waveform.



#### Circuit board layout and protection device placement:


Circuit board layout is critical for the suppression of ESD, EFT and surge transients. The following guidelines are recommended:

- 1. Place the protection device as close to the input terminal or connector as possible.
- 2. The path length between the protection device and the protected line should be minimized.
- 3. Keep parallel signal paths to a minimum.
- 4. Avoid running protection conductors in parallel with unprotected conductor.
- 5. Minimize all printed-circuit board conductive loops including power and ground loops.
- 6. Minimize the length of the transient return path to ground.
- 7. Avoid using shared transient return paths to a common ground point.
- 8. Ground planes should be used whenever possible. For multilayer printed-circuit boards, use ground vias.

# PESD5V0S1BA/BB/BL


Low capacitance bidirectional ESD protection diodes

### 8. Package outline




#### Fig 9. Package outline SOD323 (SC-76)

Low capacitance bidirectional ESD protection diodes



### Fig 10. Package outline SOD523 (SC-79)

Low capacitance bidirectional ESD protection diodes



#### Fig 11. Package outline SOD882

**Product data sheet** 

Low capacitance bidirectional ESD protection diodes

## 9. Packing information

### Table 10. Packing methods

The indicated -xxx are the last three digits of the 12NC ordering code.[1]

| Type number Package Description |        | Description                    | Packing qua | Packing quantity |  |  |
|---------------------------------|--------|--------------------------------|-------------|------------------|--|--|
|                                 |        |                                | 3000        | 10000            |  |  |
| PESD5V0S1BA                     | SOD323 | 4 mm pitch, 8 mm tape and reel | -115        | -135             |  |  |
| PESD5V0S1BB                     | SOD523 | 4 mm pitch, 8 mm tape and reel | -115        | -135             |  |  |
| PESD5V0S1BL                     | SOD882 | 4 mm pitch, 8 mm tape and reel | -           | -315             |  |  |

[1] For further information and the availability of packing methods, see Section 12.

### Low capacitance bidirectional ESD protection diodes

# **10. Revision history**

| Table 11. Revision histor | ry                                  |  |                |  |  |  |
|---------------------------|-------------------------------------|--|----------------|--|--|--|
| Document ID               | Release date                        | Data sheet status  | Change notice  | Supersedes   |  |  |
| PESD5V0S1BA_BB_BL_4       | 20090820                            | Product data sheet   | -              | PESD5V0S1BA_BB_BL_3                                  |  |  |
| Modifications:            |                                     | et was changed to reflect th<br>legal definitions and discla |                | me NXP Semiconductors,<br>were made to the technical |  |  |
|                           | <ul> <li>Table 3 "Pinnii</li> </ul> | ng": amended   |                |  |  |  |
|                           | <ul> <li>Figure 9 "Pack</li> </ul>  | kage outline SOD323 (SC-                                     | 76)": updated  |  |  |  |
|                           | Figure 10 "Page 10"                 | ckage outline SOD523 (SC                                     | -79)": updated |  |  |  |
| PESD5V0S1BA_BB_BL_3       | 20041217                            | Product data sheet   | -              | PESD5V0S1BA_BB_BL_2                                  |  |  |
| PESD5V0S1BA_BB_BL_2       | 20040802                            | Product data sheet   | -              | PESD5V0S1BA_1<br>PESD5V0S1BB_1                       |  |  |
| PESD5V0S1BA_1             | 20040322                            | Product specification  | -              | -  |  |  |
| PESD5V0S1BB_1             | 20040304                            | Product specification  | -              | -  |  |  |
|                           |                                     |  |                |  |  |  |

### **11. Legal information**

### 11.1 Data sheet status

| Document status[1][2]          | Product status <sup>[3]</sup> | Definition  |
|--------------------------------|-------------------------------|---|
| Objective [short] data sheet   | Development                   | This document contains data from the objective specification for product development. |
| Preliminary [short] data sheet | Qualification                 | This document contains data from the preliminary specification.                       |
| Product [short] data sheet     | Production                    | This document contains the product specification.                                     |

[1] Please consult the most recently issued document before initiating or completing a design.

[2] The term 'short data sheet' is explained in section "Definitions".

[3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nxp.com.

### 11.2 Definitions

**Draft** — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local NXP Semiconductors sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

### 11.3 Disclaimers

**General** — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

**Right to make changes** — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in medical, military, aircraft, space or life support equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors accepts no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) may cause permanent damage to the device. Limiting values are stress ratings only and operation of the device at these or any other conditions above those given in the Characteristics sections of this document is not implied. Exposure to limiting values for extended periods may affect device reliability.

Terms and conditions of sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at <a href="http://www.nxp.com/profile/terms">http://www.nxp.com/profile/terms</a>, including those pertaining to warranty, intellectual property rights infringement and limitation of liability, unless explicitly otherwise agreed to in writing by NXP Semiconductors. In case of any inconsistency or conflict between information in this document and such terms and conditions, the latter will prevail.

**No offer to sell or license** — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from national authorities.

**Quick reference data** — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

### 11.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

### **12. Contact information**

For more information, please visit: http://www.nxp.com

For sales office addresses, please send an email to: salesaddresses@nxp.com

PESD5V0S1BA\_BB\_BL\_4

# PESD5V0S1BA/BB/BL

Low capacitance bidirectional ESD protection diodes

### 13. Contents

| 1    | Product profile 1         |
|------|---------------------------|
| 1.1  | General description       |
| 1.2  | Features 1                |
| 1.3  | Applications 1            |
| 1.4  | Quick reference data 1    |
| 2    | Pinning information 2     |
| 3    | Ordering information 2    |
| 4    | Marking                   |
| 5    | Limiting values 3         |
| 6    | Characteristics 5         |
| 7    | Application information 8 |
| 8    | Package outline 9         |
| 9    | Packing information 12    |
| 10   | Revision history 13       |
| 11   | Legal information 14      |
| 11.1 | Data sheet status 14      |
| 11.2 | Definitions 14            |
| 11.3 | Disclaimers 14            |
| 11.4 | Trademarks 14             |
| 12   | Contact information 14    |
| 13   | Contents                  |

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.

© NXP B.V. 2009.

All rights reserved.

For more information, please visit: http://www.nxp.com For sales office addresses, please send an email to: salesaddresses@nxp.com

Date of release: 20 August 2009 Document identifier: PESD5V0S1BA\_BB\_BL\_4

