



PCB Layout

**SPECIFICATION**

Current Rate: 3Amp  
 Contact Resistance: 20mΩ MAX.at DC 1A  
 Insulation Resistance: 1000MΩ MIN.at DC500V  
 Dielectric Strength: AC500V PER minute  
 Operation Temperature: -40°to +105°

**MATERIAL**

Insulator: Polyester, UL94V-0  
 Standard: PA6T  
 CONTACT: Brass  
 Contact plated: Gold Over Nickel  
 Poles: 2~40P (Double)  
 Color: Black

**TOLERANCE TABLE**

.0	±0.20
.00	±0.10
.000	±0.05

APPROVED:	DATE:	 深圳市灿科盟实业有限公司 KIMT W CHANKEMENG INDUSTRY CO., LTD
CHECKED:	DATE:	
DRAWN:	DATE:	TITLE: 220S-2*XP H=8.5MM
LXF	2008-04-29	CLIENT P/N /
		UNIT mm
		SCALE free
		FILE NO. Chantw-220-000002
		REV. A