


THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION		LOC	DIST	REVISIONS					
© COPYRIGHT		ALL INTERNATIONAL RIGHTS RESERVED.		J	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
								D5 REVISED PER ECR-17-018148	13DEC17	SC	BH



1. APPLICABLE CONTACT PART NUMBER;
 TAB CONTACT: 175150-□ (#20-#16AWG)
 175149-□ (#26-#22AWG)
2. TO BE USED WITH THE CONTACT WHICH IS RATED 105°C MAX
3. MATERIAL: PA66, UL94 V-0, GWIT 775°C

1-176271-5	130°C MAX	3	GREEN 绿	2	1-176282-5
1-176271-1	130°C MAX	3	NATURAL 自然色		1-176282-1 2
176271-□	105°C MAX	PA66	BLACK 黒	2	176282-9
			BLUE 青		176282-6
			YELLOW 黄		176282-4
			RED 赤		176282-2
			NATURAL 自然色		176282-1
MATING CONN. PART NUMBER 嵌合相手型番	TEMPERATURE RATING 定格温度	TYPE 種類	HOUSING COLOR 色	Pos. 極数	PART NUMBER 型番

1. 適用端子型番;
 リセコンタクト: 175150-□ (#20-#16AWG)
 175149-□ (#26-#22AWG)
2. 適用コンタクトの使用温度は最大105°C

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: ≤ 10 ± 0.2 $10 < \leq 30$ ± 0.25 $30 <$ ± 0.3 ANGLES ± 3° FINISH	DWN Y.NARISAWA 19NOV1990 CHK Y.FUJITA 19NOV1990 APVD N.ONOUE 20NOV1990 PRODUCT SPEC 108-5302 APPLICATION SPEC		
MATERIAL SEE TABLE		NAME AMP UNIVERSAL POWER CONN. 3.96mm PITCH CAP HOUSING 2 Pos. (SGL ROW) AMP ユニバーサルパワーコネクタ 2極 3.96mmピッチ キャップハウジング	SIZE A3	CAGE CODE 00779
		RESTRICTED TO	DRAWING NO C-176282	RESTRICTED TO
		RESTRICTED CUSTOMER	SCALE NTS	SHEET 1 OF 1
				REV D5