



Rating:0.5A 30V DC
 Contact Resistance:100 mΩ Max.
 Operating temperature:-20℃~70℃
 Operating force:3-20N
 Operating Life:5,000cycles

Model No.	PJ-3250-A	PJ-3250-B	PJ-3250-C	PJ-3250-D
Schematic				

② Terminal	5	Phosphor bronze	Au Plating
① Housing	1	Nylon	Black
ITEM PART NAME	TERN.O.	QTY.	MATERIAL FINISHING
APPROVALS	DATE	REMARK	

DRAWN J.X.Zhang 2013/11/11
 TITLE: PHONE JACKS
 ELECTRONICS CO.,LTD

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			
TOLERANCES ARE: 30 ^{±0.15} 10 ^{±0.20} 5 ^{±0.15} ~5 ±0.10 ANGLE ±2° UNIT: mm SCALE: 1:1 PROJ: P. SHEET 1 OF 1						