muRata Capacitor Data Sheet GRM188R60J225KE01# "#" indicates a package specification code.



< List of part numbers with package codes >

Shape

GRM188R60J225KE01D , GRM188R60J225KE01J

ondpo		
L size	1.6 ±0.1mm	
W size	0.8 ±0.1mm	
T size	0.8 ±0.1mm	
External terminal width e	0.2 to 0.5mm	
Distance between external terminals g	0.5mm min.	
Size code in inch(mm)	0603 (1608M)	

## References

Packaging	Specifications	Minimum quantity
D	φ180mm Paper taping	4000
J	φ330mm Paper taping	10000

## Specifications

Capacitance	2.2µF ±10%
Rated voltage	6.3Vdc
Temperature characteristics (complied standard)	X5R(EIA)
Capacitance change rate	±15.0%
Temperature range of temperature characteristics	-55 to 85℃
Operating temperature range	-55 to 85℃

## 🔔 Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2. This datasheet has only typical specifications because there is no space for detailed specifications. Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.