

PRODUCT NO.	DSHP03TSGER
RoHS compliant	

NOTES :1.Specification:





- 1>.Operating force:1000gf Max
- 2>.Operating Temperature: -40° to+85°
- 3>.Storage Temperature: -40° to+85°
- 4>.Electrical Life:1000cycles 25mA 24VDC
- 5>.Mechanical Life:3000cycles Operations

2. PLATING:


GOLD FLASH 1u"(min.) SOLDER TAIL,  
3u" GOLD PLATING ON THE CONTACT AREA,  
WITH 50u" NICKEL UNDERPLATINGOVERALL.

3. PART NUMBER DESCRIPTION :

DSHP XX I S G E I



RECOMMENDED P.C.B. LAYOUT (TOP VIEW)




Number	Part Name	Material	Finished
①	Actuator	UL94 V0	White
②	Cover	UL94 V0	Black
③	Movable	Beryllium Copper	3μ Gold
④	Terminal	Brass	1μ Gold
⑤	Base	UL94 V0	Black
⑥	Terminal Contact	Brass	3μ Gold
⑦	Mylor	UL94 V0	0.05mm

TOLERANCE UNLESS OTHERWISE SPECIFIED		INSPECTION COPY	
LINER	ANGLES	PROJECTION	
0 ± 0.25	0 ± 2'		
.00 ± 0.15	.0 ± 1'		
.000± 0.10	.00± 0.5'		
DESIGN	kathy	03/20/12	
DRAWING			
CHECK			
APPRO.			
FILE NO.	DSHP03TSGER-A		
SIZE	UNIT	SCALE	SHEET
A4	mm	2 : 1	1 OF 1

**东莞市广智实业有限公司**  
Dongguan Kingtek Industrial Co., Ltd.

TITLE  
BY DSHP SERIES PITCH 1.27mm

PRODUCT FAMILY DSHP SERIES  
PRAT NO. DSHP03TSGER



- [包装方式: T=管装 R=Reel]
- [电镀层: B=镀锡3u" 焊脚部1.2u" G=镀镍3u" 焊脚部3u" F=镀镍10u" 焊脚部10u"]
- [G=镀全金 S=内镀金(接触部) 外镀锡(焊脚部)]
- [脚型: S脚 / J脚 / 环脚 / A脚 / 2脚]
- [T=低推贴胶 S=低推不贴胶 L=长推]
- [产品规格: 02=2P 04=4P 06=6P 08=8P 10=10P 12=12P]

[推钮行程]

Mylor