


CIRCUIT DIAGRAM
回路图

规格 Specifications

额定负荷 Rating	DC 12V/0.5A
接触电阻 Contact Resistance	≤0.03Ω
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V(50-60Hz) 60S min.
操作力 Operation force	360-50gf
寿命试验 Operating Life	100,000 cycles
行程 Travels	0.50±0.1mm



RECOMMENDED P.C.B. LAYOUT
安装尺寸图

PRODUCT NO.: 1TS018A***-***-***-CT
轻触开关
6X6X3, 4硅胶包脚系列

外形:
按钮颜色:
底座颜色:
盖板颜色:
产品高度 (H): 3.40-3.4mm

操作力度:
160-160gf
260-260gf
380-380gf
手感:
0-初握
1-大手感
2-小手感
3-特殊手感

CT
非编带, 不启用

材质:
0-初始材质
1-新增材质
依次增加

ITEM	PART NAME	MATERIAL
5	弹片	不锈钢复模
4	盖板	不锈钢304
3	按钮	硅胶米黄色
2	基座	PPA棕色
1	卡件	H65黄铜镀镍

UNITS	MM	INCH
X. ± 0.3	X. ± 0.3	0.0125 ± 0.0118
X. ± 0.2	X. ± 0.2	0.0079 ± 0.0079
XX ± 0.1	XX ± 0.1	0.0039 ± 0.0039
XXX ± 0.05	XXX ± 0.05	0.0016 ± 0.0016

NAME (INTENDED USE)	HON YUAN
PART NO. (INTENDED USE)	1TS018AW***-***-***Q
APPD:	20-4/27/2016
CHKD:	M.H.LI 4/27/2016
DR:	Y.X.Chen 4/27/2016

TITLE:	PRODUCT DRAWING
DWG NO.:	1TS018AW
SCALE:	1/1

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF HON YUAN PRECISION IND. CO., LTD. AND SHALL NOT BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, INCLUDING PHOTOCOPYING, RECORDING, OR BY ANY INFORMATION STORAGE AND RETRIEVAL SYSTEM. THE PRIOR WRITTEN CONSENT OF HON YUAN PRECISION IND. CO., LTD.