



电气性能/Electrical

参考标准/Standard: UL IEC
 额定电压/Rated voltage: 300V 250V
 额定电流/Rated current: 5A 8A
 使用线径/Wire range: 22-18AWG 1.0mm²
 耐电压/Withstanding voltage: AC2000V/1Min
 绝缘电阻/Insulation resistance: 500M Ω /DC500V
 机械性能/Mechanical

温度范围/Temp.Range: -40 $^{\circ}$ C⁺+105 $^{\circ}$ C
 瞬间温度/MAX Soldering: +250 $^{\circ}$ C, for 5 Sec
 剥线长度/Strip length: 8-9mm
 尺寸/Dimensions

间距/Pitch: 3.5mm
 极数/Poles: 1P-XXP
 材质及电镀/Material
 塑件/Housing: PA66, UL94V-0
 焊针/Pin header: Phosphor bronze, Tin plated
 按钮/Pushbutton: PA66, UL94V-0

订购方式:
HOW TO ORDER

型号/Model	-	极数/POLE	-	P	-	客户请求 Customer Request																		
<table border="1"> <tr> <td>本色/Gray</td> <td>10</td> <td>绿色/Green</td> <td>40</td> <td>透明/Transparent</td> <td>70</td> </tr> <tr> <td>蓝色/Blue</td> <td>20</td> <td>黄色/Yellow</td> <td>50</td> <td>黄色/Yellow</td> <td>80</td> </tr> <tr> <td>黑色/Black</td> <td>30</td> <td>红色/Red</td> <td>60</td> <td>白色/White</td> <td>90</td> </tr> </table>							本色/Gray	10	绿色/Green	40	透明/Transparent	70	蓝色/Blue	20	黄色/Yellow	50	黄色/Yellow	80	黑色/Black	30	红色/Red	60	白色/White	90
本色/Gray	10	绿色/Green	40	透明/Transparent	70																			
蓝色/Blue	20	黄色/Yellow	50	黄色/Yellow	80																			
黑色/Black	30	红色/Red	60	白色/White	90																			

TOLERANCES EXCEPT AS NOTED

	linear dimension	fillet	chamfer	short angle sid	≡	□	//	⊥
variable range	6 to 30 over 30 to 120 over 120 to 480	all to 6	6 to 10 over 10 to 50 over 50 to 120	10 to 50 over 50 to 120	all to 5	5 to 30 over 30 to 120	over 30 to 120	over 120 to 480
tolerance	±0.1 to ±0.2 ±0.3 to ±0.5 ±0.9 to ±0.5	±0.2 to ±0.5	±1 to ±1	1 $^{\circ}$ to 30'	0.5 to 10'	0.025 to 0.12	0.06 to 0.12	0.4 to 0.4

第一视角/FIRST ANGLE PROJECTION

