


通用FPC寸法  
Applicable FPC



PCB 寸法  
PCB Layout

- 备注:
- 1: 塑胶件表面应光洁、无毛刺; 无明显收缩、裂胶等现象.
  - 2: 额定电流 Current rating: 0.4A.
  - 3: 额定电压 Voltage rating: 50V.
  - 4: 耐压 Withstand voltage: 200V AC/minute.
  - 5: 接触电阻 Contact resistance:  $\leq 20m\Omega$ .
  - 6: 绝缘电阻 Insulation resistance:  $500M\Omega$ .
  - 7: 工作温度 Working temperature:  $-20^{\circ}C$  —  $+80^{\circ}C$

TOLERANCE TABLE

|      |       |
|------|-------|
| .0   | ±0.30 |
| .00  | ±0.20 |
| .000 | ±0.05 |

|           |            |   |           |                 |             |
|-----------|------------|---|-----------|-----------------|-------------|
| APPROVED: | DATE:      | TITLE:  | UNIT      | SCALE           | REV.        |
| CHECKED:  | DATE:      | FPC1.0-XP 下接 抽拉式                              | mm        | free            | A           |
| DRAWN:    | DATE:      | 深圳市如科盟实业有限公司<br>CHANKLEMENT INDUSTRY CO., LTD | PROD. P/N | FILE NO.        | CS-08-07/16 |
| 审核        | 2012-09-21 |   | /         | Chantw-FPC-0057 |             |