


规格 Specifications	
额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	100mΩ max.
绝缘电阻 Insulation resistance	DC:100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V(50~60HZ) 60S min.
操作力 Operation force	160±30gf      250±50gf
寿命试验 Operating Life	100,000 cycles      70,000 cycles
行程 Travels	0.25±0.1mm

RECOMMENDED P.C.B. LAYOUT

安装尺寸图



PRODUCT NO.: 1TS005A\*\*\*\*-\*\*\*\*\* - CT

- 轻触开关
- 系列
- 外形:
- 按钮颜色:
- 底座颜色:
- 盖板颜色:
- 初始颜色, 则不启用
- 操作力度:
- 手感:
- 材质:
- 0=初始材质
- 1=新增材质
- 依次增加
- 产品高度(H):
- 430=4.3mm
- 700=7.0mm
- 编织带
- 非编织带, 不启用

ITEM	PART NAME	QUANTITY	MATERIAL	FINISH
5	COVER	1	Stainless Steel	NATURAL
4	ACTUATOR	1	PPA	BLACK
3	DOVE	1	Phosphor Bronze/Ag	Ag-PLATED
2	TERMINAL	1	BRASS	Ag-PLATED
1	HOUSING	1	PPA	BLACK

X. ±	0.3	X. ±	3'	UNITS	MM
X. ±	0.2	X. ±	2'	MAT'L	
.XX ±	0.1	.XX ±	1'	FINISH	
.XXX ±	0.05	.XXX ±	0.5'		

NAME(INTENDED USE)	HON YUAN
6X6 TACT SWITCH	HON YUAN PRECISION IND. CO.,LTD. SHENZHEN, CHINA.
PART NO.(INTENDED USE)	PRODUCT DRAWING
1TS005A-****-***1	
APPD: ZO 2013/06/29	DWG NO.: 1TS005A
CHKD: M.H.LI 2013/06/29	
DRY:Y.Chen 2013/06/29	

SCALE	SHEET	REV.
10/1	2/2	A

THESE DIMENSIONS AND SPECIFICATIONS ARE THE PROPERTY OF HON YUAN PRECISION IND. CO., LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF HON YUAN PRECISION IND. CO., LTD.