




REV.	DESCRIPTION	DRAWN	CHECKED	APPROVED
A	NEW RELEASE	YCH 01/05/09'	~	




Dimension


Position	A±0.2	B±0.2	C±0.3
9	17.90	24.99	30.80
15	26.50	33.32	39.14
25	40.00	47.04	53.04
37	56.50	63.50	69.32



Standard



CC TYPE



CS TYPE

NOTES:

- ELECTRICAL CHARACTERISTICS:
  - CONTACT RESISTANCE: 20mΩ Max. INITIAL.
  - DIELECTRIC WITHSTANDING VOLTAGE: 500V AC(rms) FOR 1 MINUTE.
  - INSULATION RESISTANCE: 1000MΩ Min.
- ENVIRONMENT CHARACTERISTICS:
 

TEMPERATURE RANGE: -45°C~+105°C.
- PART NUMBER: DS1033-10
- PRODUCT NUMBER CODE:

DS1033-10- X X X X X X X

SCREW DIM. A  
S: Standard(W/O nut)  
1: 5.00  
2: 3.00  
3: 5.20  
4: 4.80  
5: 5.80  
6: 4.00


SCREW TYPE  
S: Standard(W/O nut)  
1: CC TYPE  
2: CS TYPE

CONTACT PLATING  
8: FULL GOLD FLASH  
6: FULL Tin  
0: SELECTIVE GOLD FLASH  
J: SELECTIVE 5u" GOLD

SHELL PLATING  
T: FRONT & BACK SHELL Tin  
N: FRONT SHELL Nickel,  
BACK SHELL Tin

HOUSING COLOR  
B: BLACK  
W: WHITE  
U: BLUE  
CONNECTOR TYPE  
M: Male

No. OF CONTACTS  
09: 9pos.  
15: 15pos.  
25: 25pos.  
37: 37pos.  
50: 50pos.



50pin Male Figure

Tel:86-574-6350817  
Fax:86-574-63510817

GENERAL TOLERANCE		ANGLE TOLERANCE		PROJECTION	TITLE
X.	±0.60	X.	±5°		D-SUB SOLDER TYPE
.X	±0.38	.X	±3°	UNITS	mm
.XX	±0.25	.XX	±2°	SHEET SIZE	A4
DRAWING TYPE				CUSTOMER	SERIES
SCALE				1:1	SHEET 1 OF 1
DRAWING NO.				C-DS1033-10-XXXXXXX	DS1033-10 SERIES

晨翔电子有限公司  
CONNFLY CONNFLY ELECTRONIC CO. LTD

Town Cixi Ningbo China