











宏聚电子五金制品有限公司

HONGJU ELECTRONIC & METAL PRODUCTS CO.,LTD

S-03-11-1



Rating: 15A 250V AC (UL CUL)  
 10A 250V AC (VDE CCC) 
 Insulation Resistance: DC 500V 100MΩ Min.
 Dielectric Strength: AC2000V 1 minute
 MATERIAL:
 Body: PBT
 Terminal: Brass, Silver or Tin plated



CUT-OUT

		公差 TOLERANCES		.X±0.3	.XX±0.15	角度 ANGLE ±1°		单位 DIMENSION UNIT		mm.
		版本 VERSION	A0	比例尺 SCALE	NONE	日期 DATE	2008.07.08	品名 TITLE	S-03-11-1	
		核准 APPROVED BY	Xinchao_Lee	核对 CHECKED BY	Gokey_Guo	绘图 DRAWN BY	Gokey_Guo	图号 DRAWING NO	S-03-11-1_A0	
版本 VER.	New Issue	变更说明 CHANGE DESCRIPTION	日期 DATE	ECN NO.						
			2008.07.08	N/A						

File Code: HJ-WI-E-03A