



SPECIFICATION

Voltage rating: AC, DC 250V
 Current rating: AC, DC, 7A
 Withstand voltage: 1500V AC/min.
 Insulation resistance: 1000M Ω /min.
 Temperature range: -25 °C ~ +85 °C

Applicable wires: AWG#24 ~ 18

Material: Brass.

Finish: Tin plated

Thickness: 0.2mm

APPROVED:	DATE:	C 深圳市灿科盟实业有限公司 kmTW CHANKLEMENT INDUSTRYCO., LTD			
CHECKED:	DATE:	TITLE: 5557TP (公端子)			
DRAWN:	DATE:	CLIENT P/N	/	SCALE	free
LYF	2008-04-07	UNIT	mm	REV.	A
TOLERANCE TABLE		FILE NO.	Ckmtw-5557-0016		
.0	±0.20				
.00	±0.10				
.000	±0.05				