







| REV. | DESCRIPTION | DATE |
|------|-------------|-----------|
| A | RELEASE | 2007.3.18 |



MATERIAL&FINISH

Insulator: PBT Glass Fiber(UL94V-0)
 Contact : Brass
 Contact : Gold-Plated Over Nickel.

SPECIFICATIONS
 Current Rating :1A AC,DC
 Voltage Rating : 250V AC,DC
 Temperature Range:-40°C To+105°C
 Contact Resistance:20mΩ Min
 Insulation Resistance:1000MΩ Min
 Withstanding Voltage:500V AC/Min

| PART NO | Dim. A | Dim. B | Dim. C |
|---------|--------|--------|--------|
| FC-6P | 5.08 | 12.32 | 1.9 |
| FC-8P | 7.62 | 14.86 | 1.9 |
| FC-10P | 10.16 | 17.40 | 3.8 |
| FC-12P | 12.7 | 19.94 | 3.8 |
| FC-14P | 15.24 | 22.48 | 3.8 |
| FC-16P | 17.78 | 25.02 | 3.8 |
| FC-18P | 20.32 | 27.56 | 3.8 |
| FC-20P | 22.86 | 30.10 | 3.8 |
| FC-24P | 27.94 | 35.18 | 3.8 |
| FC-26P | 30.48 | 37.72 | 3.8 |
| FC-28P | 33.02 | 40.26 | 3.8 |
| FC-30P | 35.56 | 42.80 | 3.8 |
| FC-34P | 40.64 | 47.88 | 3.8 |
| FC-40P | 48.26 | 55.5 | 3.8 |
| FC-50P | 60.96 | 68.20 | 3.8 |
| FC-60P | 73.66 | 80.90 | 3.8 |
| FC-64P | 78.74 | 85.98 | 3.8 |

| | | | | | |
|------------------|--------------|------------|-----------|------|---------------|
| UNLESS TOLERANCE | | DRAW BY | YUAN | | ITEM : |
| GENERAL | ANGLE | DESIGN BY | 2007.3.18 | | |
| X. ± 0.30 | X.' ± 3.0' | CHECK BY | | | |
| .X ± 0.20 | .X' ± 2.0' | APPROVE BY | | | |
| .XX ± 0.15 | .XX' ± 1.0' | SCALE | SHEET | UNIT | DRW NO: FC-XP |
| .XXX ± 0.08 | .XXX' ± 0.5' | 1:1 | 1/1 | MM | |