

PRODUCT NO.	DSHP04TSGE1
RohS compliant	






NOTES :1.Specification:

- 1>.Operating force:1000gf Max
- 2>.Operating Temperature: -40° to+85°
- 3>.Storage Temperature: -40° to+85°
- 4>.Electricalife Life:1000cycles 25mA 24VDC
- 5>.Mechanical Life:3000cycles Operations



2. PLATING:  
 GOLD FLASH 1u"(min.) SOLDERTAIL,  
 3u" GOLD PLATING ON THE CONTACT AREA,  
 WITH 50u" NICKEL UNDERPLATINGOVERALL.

3. PART NUMBER DESCRIPTION :

- [包装方式: T=管装 R=Reel]
- [电键层: B=接触部3u"焊脚部1.2u" G=接触部3u"焊脚部3u" F=接触部10u"焊脚部10u"]
- [G=键全金 S=内镀金(接触部)外镀锡(焊脚部)]
- [脚型: S脚 / J脚 / 埋脚 / A脚 / 2脚]
- [T=低推贴胶 S=低推不贴胶 L=长推]
- [产品P数: 02=2P 04=4P 06=6P 08=8P 10=10P 12=12P]



RECOMMENDED P.C.B. LAYOUT (TOP VIEW)



Number	Part Name	Material	Finished
①	Actuator	UL94 V0	White
②	Cover	UL94 V0	Black
③	Movable	Beryllium Copper	3u" Gold
④	Terminal	Brass	1u" Gold
⑤	Base	UL94 V0	Black
⑥	Terminal Contact	Brass	3u" Gold
⑦	Mylor	UL94 V0	0.05mm

TOLERANCE UNLESS OTHERWISE SPECIFIED		INSPECTION COPY	
LINER	ANGLES	PROJECTION	
0 ± 0.25	0 ± 2'		
.00 ± 0.15	.0 ± 1'		
.000 ± 0.10	.00 ± 0.5'		
DESIGN	kathy	03/20/12	
DRAWING			
CHECK			
APPRO.			

**东莞市广智实业有限公司**  
 Dongguan Kingtek Industrial Co., Ltd.

TITLE  
 BY DSHP SERIES PITCH 1.27mm

PRODUCT FAMILY DSHP SERIES  
 PRAT NO. DSHP04TSGE1

FILE NO. DSHP04TSGE1-A  
 SIZE UNIT SCALE SHEET REV.  
 A4 mm Z: 1 1OF 1 A