





防水等级: IPX7




此处打胶防水

3D示意图




Recommended PCB Layout



- Specifications
1. Rating : DC 30V 0.5A
 2. Dielectric withstanding: 100V(AC) for 1min
 3. Contact Resistance : 50mΩMax
 4. Insulation Resistance: 100MΩ Min
 5. Operating Temperature Range: -25°C+80°C
 6. Operating Force : 8-30N
 7. Operating Life : 5,000Cycles

B-B 剖视图



配合示意图

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
③	Shell	—	1	SUS	Natural	—
②	Contact	—	5	Copper Alloy	Au Plated	—
①	Housing	—	1	LCP	Black	—

APPROVALS	DATE	TITLE:
DRAWN JKUN.LU	2014/9/29	防水USB CONNECTOR

HLRQ
ELECTRONICS CO.,LTD

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	TOLERANCES ARE	ANGLE	UNIT:	SCALE:	PROJ:	SHEET
—	A	—	NEW	—	—	—	30~0.15 10~0.30 5~0.10	±0.30 ±0.25 ±0.20	mm	1:1	U-E-MSS-W-1	1 OF 1