





PRODUCT NO.	DSPV08LHGCT
RoHS compliant	

NOTES : 1 Specification:


- 1>.Operating force:10000gf Max
- 2>.Operating Temperature: -40° to+85°
- 3>.Storage Temperature: -40° to+85°
- 4>.Mechanical Life:3000cycles minimum
- 5>Electrical Life:2000cycles minimum



DS XX T S G E T  
 [Packing: T=Tube R=Reel]  
 [Finish: F=3u" Gold-plated F=10u" Gold-plated]  
 [Finish: G=Full Gold S=Contact-Gold-plated]  
 [Terminal: S=SMD type B=Strait:.....]  
 [Actuator: T=Tape sealed S=Low profile W/O Tape L=Extension]  
 [HP=Half-Pitch IC=IC type PV=Plano type]

2. PLATING:  
GOLD FLASH 1u"(min.) SOLDER TALL,  
3u" GOLD PLATING ON THE CONTACT AREA,  
WITH 50u" NICKEL UNDERPLATING OVERALL.
3. CONTACT RATING:  
1. SWITCHING: 25mA at 24VDC  
2. NON-SWITCHING: 100mA at 50VDC  
WITH 50u" NICKEL UNDERPLATING OVERALL.

4. PART NUMBER DESCRIPTION :



Number	Part Name	Material	Finished
①	Actuator	UL94 V0	White
②	Cover	UL94 V0	Black
③	Movable	Copper Alloy	3u" Gold
④	Terminal	Brass	1u" Gold
⑤	Base	UL94 V0	Black
⑥	Terminal Contact	Brass	3u" Gold

TOLERANCE UNLESS OTHERWISE SPECIFIED		INSPECTION COPY	
LINER	ANGLES	PROJECTION	COPY
0 ± 0.25	0 ± 2'		BY DSPV SERIES PITCH 2.54mm PRODUCT FAMILY DSPV SERIES PRAT NO. DSPV08LHGCT
.00 ± 0.15	.0 ± 1'		
.000± 0.10	.00± 0.5'		
DESIGN kathy		03/20/12'	
DRAWING			
CHECK			
APPRO.			

 东莞市广睿实业有限公司 Dongguan Kingtek Industrial Co., Ltd.			
FILE NO.	DSPV08LHGCT-A	UNIT SCALE	SHEET REV.
SIZE	A4	SCALE	1 : 1
UNIT	mm	SCALE	TOP: 1