



安装尺寸图

规格 Specifications

额定负荷 Rating	DC 12V/50mA	
接触电阻 Contact Resistance	100mΩ max.	
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min.	
抗电强度 Dielectric strength	AC250V(50-60HZ) 60S min.	
操作力 Operation force	≤180±30gf	≤300±50gf
寿命试验 Operating Life	50,000 cycles	30,000 cycles
行程 Travels	0.25±0.1mm	

REV	ECN NO.	APPD
A	HC-11-0027	PROJQM
B	HC-11-0062	PROJQM
C	HC-12-0061	PROJQM
D	HC-15-0064	PROJQM

PRODUCT NO.: 1TS002*****-CT

- 轻触开关
- 3X6系列
- 外形:
 - A=插脚
 - B=贴片
 - C=贴片带柱
 - E=贴片2.5高
 - K=贴片带柱8.8
 - L=贴片10.2
- 按钮颜色:
 - 底座颜色:
 - 盖板颜色:
 - 操作力度:
 - 130=130±20gf
 - 160=160±30gf
 - 180=180±30gf
 - 220=220±40gf
 - 250=250±50gf
 - 300=300±50gf
 - 手感:
 - 0=常规
 - 1=大手感
 - 2=小手感
 - 3=特殊手感
 - 材料:
 - 0=PA66
 - 1=LCP+PPA
 - 2=LCP
 - 3=PA66+PPA
 - 4=新增材质依次增加
 - 产品高度(H):
 - 430=4.3mm
 - 500=5.0mm
 - 初始颜色 则不启用

ITEM	PART NAME	QUANTITY	MATERIAL	FINISH
5	ACTUATOR	1	PAG6	WHITE
4	COVER	1	STAINLESS STEEL	NATURAL
3	DOME	1	STAINLESS STEEL	Ag-PLATED
2	HOUSING	1	PAG6	WHITE
1	TERMINAL	1	BRASS	Ag-PLATED/0.2μm

X	±	0.3	X' ±	0.3'	UNITS	MM
X	±	0.2	X' ±	0.2'	MATL	
.XX	±	0.1	.XX' ±	0.1'	FINISH	
.XXX	±	0.05	.XXX' ±	0.05'		

NAME(INTENDED USE)	3X6 SMT SERIES(POST)	TACT SWITCH	HON YUAN
PART NO.(INTENDED USE)	1TS002C****-*****0		HON YUAN PRECISION IND. CO.,LTD.
APPD:	ZO 2015/11/12		SHENZHEN, CHINA.
CHKD:	M.H.LI 2015/11/12		TITLE: PRODUCT DRAWING
DR:	WP.LU 2015/11/11		DWG NO.: 1TS002C

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF HON YUAN PRECISION IND. CO., LTD. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT PERMISSION IN WRITING FROM HON YUAN PRECISION IND. CO., LTD.

SCALE	10/1	SHEET	1/4	REV.	D
-------	------	-------	-----	------	---