





REV	ECN NO.	APPD
A	HC-17-0082	ZO



额定负荷 Rating	DC 12V/50mA
接触电阻 Contact Resistance	500mΩ max.
绝缘电阻 Insulation resistance	DC100V 60S 100MΩ min.
抗电强度 Dielectric strength	AC250V/(50~60HZ) 60S min.
操作力 Operation force	160±30gf / 180±30gf / 240±50gf
寿命试验 Operating Life	300,000 cycles
行程 Travels	0.13±0.05mm



RECOMMENDED P.C.B. LAYOUT
安装尺寸图

LAND PATTERN PLAN
印刷电路板焊盘参考图

PRODUCT NO. : 1TS015A***-***-***-***-***

轻触开关

3X2系列

外形: A=两脚
B=四脚

按点颜色:
底座颜色:
贴膜颜色:

操作力度:
160=160gf
180=180gf
200=200gf
220=220gf
240=240gf

初始颜色
则不启用

材质:
0=初始材质
1=新增材质
依次增加


产品高度(H):
050=0.5mm
060=0.6mm
070=0.7mm

手感:
0=常规(弹片)
1=大手感(弹片)
2=小手感(弹片)
3=特殊手感(弹片)

其它:
CT=编带(非编带,不启用)

ITEM	PART NAME	QUANTITY	MATERIAL	FINISH
5	KNOB	1	POLYAMIDE	BLACK
4	FILM	1	POLYAMIDE	WHITE
3	DOVE	2	SUS301	Ag-PLATED
2	HOUSING	1	POLYAMIDE	BLACK
1	TERMINAL	1	PHOSPHOR BRONZE	Ag-PLATED

X. ± 0.2	X. ± 0.2	UNITS	MM	NAME(INTENDED USE)	HON YUAN HON YUAN PRECISION IND. CO.,LTD. SHENZHEN, CHINA.
.X ± 0.1	.X' ± 0.1'	MAT'L		3X2 SERIES TACT SWITCHES	
.XX ± 0.01	.XX' ± 0.01'	FINISH		PART NO.(INTENDED USE)	PRODUCT DRAWING
.XXX ± 0.002	.XXX' ± 0.002'			1TS015A***-***-***-***0	
		Q'TY		APPD: ZO 11/16/2017	DWG NO.: 1TS015A
				CHKD: LI 11/16/2017	
				DR: WP.LU 11/16/2017	



1 2 3 4 5 6 7