



**Specification**

**Insulator Material: Polyacet, UL94V-0**

**Standard: P A6T**

**Contact Material: Brass**

**Contact plated: Gold Over Nickel**

**Poles: 2~40P**

**Current Rating : 3Amp**

**Contact Resistance: 20 Milliohms Max**

**Insulation Resistance : 1000MΩ Min.**

**Dielectric withstanding Voltage: AC 500V**

**Operation Temperature : -40 °C -- +105 °C**

TOLERANCE TABLE	
.0	±0.20
.00	±0.10
.000	±0.05

<b>APPROVED:</b>	<b>DATE:</b>	<b>CLIENT P/N</b> C124375 <b>UNIT</b> mm <b>SCALE</b> free 
<b>CHECKED:</b>	<b>DATE:</b>	
<b>DRAWN:</b>	<b>DATE:</b>	<b>FILE NO.</b> B-2100S02P-A110 <b>REV.</b> A
<b>LXF</b>	<b>2010-08-12</b>	
<b>TITLE:</b> 210S-1*2P L=11.6mm PA6T 镀金		
<b>CLIENT:</b> 深圳市灿科盟实业有限公司 CHANKEMENG INDUSTRY CO., LTD		