



**SPECIFICATIONS**

Current rating: 3A AC/DC  
 Voltage rating: 250V AC/DC  
 Contact resistance: 20mΩ max.  
 Withstand voltage: 1000V AC/min  
 Insulation resistance: 1000MΩ/min.  
 Temperature range: -25°C~+85°C  
 Applicable PC board thickness: 0.063"(1.6)

**Material:**

Part No: 2~20  
 Post: Brass, Tin/plated  
 Base: Nylon66 UL94V-2/0

Poles	Part No.	Dimension mm	
		A	B
2	2501R-2P	2.50	7.50
3	2501R-3P	5.00	10.00
4	2501R-4P	7.50	12.50
5	2501R-5P	10.00	15.00
6	2501R-6P	12.50	17.50
7	2501R-7P	15.00	20.00
8	2501R-8P	17.50	22.50
9	2501R-9P	20.00	25.00
10	2501R-10P	22.50	27.50
11	2501R-11P	25.00	30.00
12	2501R-12P	27.50	32.50
13	2501R-13P	30.00	35.00
14	2501R-14P	32.50	37.50
15	2501R-15P	35.00	40.00
16	2501R-16P	37.50	42.50
17	2501R-17P	40.00	45.00
18	2501R-18P	42.50	47.50
19	2501R-19P	45.00	50.00
20	2501R-20P	47.50	52.50

**TOLERANCE TABLE**

.0	±0.20
.00	±0.10
.000	±0.05

APPROVED:	DATE:	 深圳市如科盟实业有限公司 CHANKLEMENT INDUSTRY CO., LTD
CHECKED:	DATE:	
DRAWN:	DATE:	TITLE:
LXF	2008-04-07	2501R-XP 不带定位
CLIENT P/N	SCALE	UNIT
/	free	mm
FILE NO.	REV.	SCALE
Chantw-2501-0003	A	free