皓宇(香港)有限公司	文件編號	HY-WI-32		
HAOYU (HONG KONG) LIMITED	發行日期	2008-07-23		
SPECIFICATION 承認書	第 B-2 版	第1頁 共3頁		

SERI	SERIES 產品系列 XLR 系列卡儂插座 TYPE 產品型號			環保	環保					
DRAWN 設 計		LIU FAZHAN				APVD 審 批		ZHOU ZHI	ZHOU ZHIQUAN	
1A. 4	額定負荷	定負荷								
RATI	ATED LOAD DC 50V 3A									
			Apply to the apper	ly to the appended drawing.						
2 · OPERATING TEMPERATURE RANGE 操作溫度範圍 PRESERVATIVE TEMPERATURE RANGE 儲存溫度範圍 儲存溫度範圍			E RANGE	20°C~70°C						
ITEM		TEST CONDITIO	NS 測試條件	ı				SPECIFICA	TIONS 規格	
3 · E	LECTRICAL PERF	ORMANCE(電氣性	生能規格):							
3A	TO BE MEASURED AT 1kHz AND 100m A MAX. WHEN THE MEASUREMENT SHALL BE MADE BY A MATING PLUG, OXIDATION FILM ON THE SURFACE MUST BE WIPED. RESISTANCE OF A PLUG CODE SHALL NOT BE INCLUDED AS A MEASUREMENT VALUE. 使用插頭插入即 1kHz 100mA 以下的微電流進行測定			IG, 50mΩ ma D. 50毫歐以下	50mΩ max 50 毫歐以下					
3В	INSULATION RESISTANCE 絕緣阻抗	TO BE MEASUR DC 導體之間在 DC50		ADJACEN	NT TE	ERMINALS A	AT 500	nin 上.		
3C	DIELECTRIC STRENGTH 耐電壓	A VOLTAGE OF AC 1500VSHALL BE APPLIED BETWEEN ADJACENT TERMINALS FOR 1 MIN. AT 50~60Hz 在導體相互之間外加 AC1500V 50~60Hz 1 分鐘			TO PARTS OR BREAK	WITHOUT DAMAGE TO PARTS ARCING OR BREAKDOWN ETC 沒有損傷 變形絕緣破壞等異常.				
4.ME	CHANICAL PERFO	PRMANCE(機械性的	 能規格)					<u> </u>		
4A	INSERTION AND EXTRACTED SLOWLY AFTER FIXING A MATING PLUG AS SHOWN IN SECTION 1B TO THE PUSH-PULL SCALE. 使用標準插頭進行測定		AS 4~40N	4~40N						
4B	TERMINAL THE FORCE OF 4.9N SHALL BE APPLIED TO THE TERMINAL FOR STRENGTH 10 SEC(3 DIRECTION)		DR BREAKDO BEND SHA	WITHOUT LOOSING AND BREAKDOWN. TERMINAL BEND SHALL BE ACCEPTED。 不應出現脫落,破損等但可以彎曲						
4C	UNLESS OTHERWISE SPECIFIED. THE STANDRD RANGE OF ATMOSPHERIC CONDITIONS FOR MAKING MEASUREMENTS AND TESTS ARE AS FOLLOWS: AMDIENT TEMPERATURE: 15℃ TO 35℃ RELATIVE HUMIDITY :25%TO75%RH AIR PRESSURE :80Kpa TO 106Kpa			度、氣壓如 (1) 溫 (2) 濕	(2) 濕度爲 25%~75%RH					

皓宇(香港)有限公司	文件編號	HY-WI-32		
HAOYU (HONG KONG) LIMITED	發行日期	2008-07-23		
SPECIFICATION 承認書	第 B-2 版	第2頁 共3頁		

5 · D	DURABILITY (耐久性)			
5A	RESISTANCE TO SOLDERING HEAT TEST 耐焊性試驗	THE TOP OF THE TERMINALS SHALL BEDIPPED 2mm . THE PLASTIC BODY IS 1.6mm ABOVE THE TIN LIGUID. 端子頂部被浸入焊錫池中 2mm 深,膠身距離錫液 1.6mm。Wave-soldering is to be performed within 3seconds at 260 +/-5 ℃ 波峰焊接溫度 260 +/-5 ℃ 時間 3 秒。Hand weilding to be performed within 3 seconds at 380℃ or below. 手工焊接溫度為 380℃或以內,時間爲 3±0.5 秒。注:本產品只適合用手焊、波峰焊。	WITHOUT DEFORMATION OF CASE OREXCESSIVE LOOSENESS OF TERMINALSELECTRICAL CHARACTERISTICS SHALL BE SATISFIED. 本體無變形, 能滿足於機械、電氣性能。	
5B	LIFE TEST. 壽命試驗	WITHOUT LOAD INSERTIONS AND EXTRACTIONS OF 5000 CYCLES SHALL BE MADE AT RATE OF 10 TO 20 CYCLES PER MINUTE 在負荷狀態下 10~20/分鐘,來回插入及拔出至 5000 次	 (1) CONTACT RESISTANCE SHALLBE 200m Ω max (2) MECHANICAL AND ELECTRICAL CHARACTERISTICS SHALL BESATISFIED。 (1) 接觸電阻不能超於 200m Ω (2) 其他滿足於機械電器性能。 	
5C	HEAT TEST. 耐熱試驗	85±2℃ FOR 96 HOURS AFTER TEST KEEP IN NORMAL CONDITION FOR 1 HOUR. 在 85±2℃環境中放 96 小時,再放在正常環境中 1 小時後進行測試。		
5D	HUMIDITY TEST. 耐濕試驗	40±2℃ 90~96%RH FOR 96 HOURS, TEST AFTER KEEPING IN NORMAL CONDITION FOR 1 HOUR. 在 40±2℃ 90~96%RH 環境中放 96 小時,再放在正常環境中,1 小時後進行測試。	THERE SHALL BE NO DAMAGE ON APPEARANCE • MECHANICAL AND ELECTRICAL CHARACTERISTICS SHALL BE	
5E	COLD TEST. 耐冷試驗	At -40±2℃ for 96 HRS. AFTER TEST KEEP IN NORMAL CONDITION FOR 1 HOUR. 在-40±2℃環境中放 96 小時,再置於正常環境中 1 小時後進行 測試。	SATISFIED 外觀無異常,滿足於機械,電器性能	
5F	SALT SPRAY TEST 噴霧試驗	5% SALT SOLUTION CONCENTRATION BY WEIGHT AT 35±1℃ FOR 24 HOURS(SPRAY 8 HOURS,REST 16 HOURS BY WATER) MEASUREMENT SHALL BE MADE, AFTER WASHING PRODUCT WITHOUT USING SOAP, REMOVING WATER DROP, AND REMAINING AT ROOM CONDITION FOR 30 MINUTES. 濃度 5%的鹽水,經 8 小時噴霧、16 小時水洗耳恭聽後,放入常溫下 30 分鐘進行測試(試驗溫度:35±1℃)	WITHOUT EXCESSIVE CORROSION OR CRACK IN APPEARANCE 表面無明顯腐蝕或鍍層脫落現象	

皓宇(香港)有限公司	文件編號	HY-WI-32		
HAOYU (HONG KONG) LIMITED	發行日期	2008-07-23		
SPECIFICATION 承認書	第 B-2 版	第3頁 共3頁		

1、在耐焊接過程中,不得把松香等絕緣、有腐蝕性物質浸入產品內。

(ROSIN AND OTHER INSULATING AND CAUSTIC MATERIAL CAN NOT BE DIPPED INTO THE ROCKET DURING SOLDERING.)

2、產品焊接後不能用氣槍吹或用溶劑沖洗。

(PRODUCTS CAN NOT BE BLOWN WITH AIR GUN OR CLEANED WITH A SOLVENT AFTER SOLDERING.)

3、產品焊接前各零件不能被溶化。

(ALL PARTS OF THE PRODUCTS CAN NOT BE DISSOLVED BEFORE SOLDERING.)

- 4、避免儲藏於高溫、潮濕及腐蝕的場所。
 - (AVOID STORING THE PRODUCTS IN A PLACE AT HIGH TEMPERATURE, HIGH HUMIDITY AND IN CORROSIVE GASES.)
- 5、貯存期限:自發貨之日起,貯存期不超過180天.若超出貯存期限,產生不良品,本公司概不負責。

(SHELF LIFE IS LESS THAN 180 DAYS SINCE THE GOODS WARE SENT OUT FROM OUR FACTORY. OUR COMPANY

DOESN'T ACCEPT RESPONSIBILITY FOR REJECTS IF THE SHELF LIFE OF GOODS EXCEEDS 180 DAYS.)

6、本產品如有不良事件,望廠家及時回饋,以便及時記錄、查核、改善、跟蹤。

(PLEASE FEEL FREE TO REPORT TO US IF YOU DISCOVER THE INFERIOR GOODS, SO THAT WE CAN TAKE NOTE, CHECK, TRACK AND IMPROVE THEM. THANKS.)

皓字(香港)有限公司 HAOYU (HONG KONG) LIMITED

