



RECOMMENDED P.C.B HOLE LAYOUT



- NOTES:
- MATERIAL:
HSG: LCP, GLASS-FILLED, UL94V-0,
COLOR: BLACK
PIN: 0.64MM SQ PIN, COPPER ALLOY
 - PLATING TYPE:
 - 0.0254 μ m GOLD FLASH OVER
1.25 μ m MIN. NICKEL OVERALL.
 - 0.025 μ m MIN. GOLD PLATE ON CONTACT AND
1.88 μ m MIN. TIN ON SOLDER TAIL OVER
1.25 μ m MIN. NICKEL OVERALL.
 - 0.25 μ m MIN. GOLD PLATE ON CONTACT AND
1.88 μ m MIN. TIN ON SOLDER TAIL OVER
1.25 μ m MIN. NICKEL OVERALL.
 - 0.38 μ m MIN. GOLD PLATE ON CONTACT AND
1.88 μ m MIN. TIN ON SOLDER TAIL OVER
1.25 μ m MIN. NICKEL OVERALL.
 - 0.75 μ m MIN. GOLD PLATE ON CONTACT AND
1.88 μ m MIN. TIN ON SOLDER TAIL OVER
1.25 μ m MIN. NICKEL OVERALL.
 - 2.50 μ m MIN. TIN OVER 1.25 m MIN. NICKEL OVERALL.
 - 0.38 μ m MIN. GOLD PLATE ON CONTACT AND
2.50 μ m MIN. TIN ON SOLDER TAIL OVER
1.25 μ m MIN. NICKEL OVERALL.
 - 0.38 μ m MIN. GOLD PLATE ON CONTACT AND
0.05 μ m MIN. GOLD FLASH ON SOLDER TAIL OVER
1.25 μ m MIN. NICKEL OVERALL.
 - 0.05 - 0.25 μ m MIN. GOLD FLASH OVER
1.25 μ m MIN. NICKEL OVERALL.
 - PIN PUSHOUT FORCE: 1KG MIN IN EITHER DIRECTION
 - THE ABOVE 14 CKT IS FOR ILLUSTRATION PURPOSE ONLY.
 - FOR PACKAGING OPTION PLEASE REFER TO THE TABLE.
 - RECOMMENDED PCB THICKNESS 1.60MM.
 - PRODUCT SPECIFICATION: PS-87920-019
 - WAFER TO BE FLAT WITHIN 0.003mm/mm
 - IRREGULAR CIRCUIT CUTOFF WITHIN BREAKAWAY SECTION IS PERMISSIBLE. CUTTING OR CHIPPING OF THE MAIN BODY IS NOT ACCEPTABLE.
 - PARTS ARE NOT STACKABLE ON 2.54 CENTER
 - CAP TO BE PLACED AS CENTRAL OF PART AS POSSIBLE WITH THE TOP SURFACE FLAT FOR PICK AND PLACE.
 - PACKAGING SPECIFICATION:
TRAY: PK-89990-489
BULK: PK-89990-491
TUBE: PK-87914-300



REVISION OF DRAWING MAY BE CHANGED DURING FINAL RELEASED FOR PRODUCTION.

RELEASE STATUS	RELEASE DATE
----------------	--------------

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										
MIGRATED TO NX EC NO: 114031 DRWN: FCSCC CHK'D: REV APPR: KHLIM	2017/03/17	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION UNITS		SCALE					
	2017/05/09		MM	INCH	MM	NTS				
			4 PLACES	±	±	DRWN BY	DATE	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H		
			3 PLACES	±	±	KCHO	2004/11/05			
			2 PLACES	± 0.2	±	CHK'D BY	DATE	PRODUCT CUSTOMER DRAWING		
	1 PLACES	±	±	PTLIM	2004/12/08					
	0 PLACES	±	±	APPR BY	DATE	SERIES	MATERIAL NUMBER	CUSTOMER		
		ANGULAR TOL = 3.0	DRAWING SIZE		THIRD ANGLE PROJECTION		87914	SEE TABLE	GENERAL MARKET	
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	A3				DOCUMENT NUMBER	DOC TYPE	DOC PART	SHEET NUMBER
D18							SD-87914-013	PSD	000	1 OF 45

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-0211	-----	-----	-----	-----	2	-----	1	2.54	----	10.92	5.84	2.79
87914-0221	-----	-----	-----	-----	2	-----	1	2.54	----	12.25	7.00	2.96
87914-0231	-----	-----	-----	-----	2	-----	1	2.54	----	13.38	6.09	5.00
87914-0212	-----	-----	-----	-----	2	-----	2	2.54	----	10.92	5.84	2.79
87914-0222	-----	-----	-----	-----	2	-----	2	2.54	----	12.25	7.00	2.96
87914-0232	-----	-----	-----	-----	2	-----	2	2.54	----	13.38	6.09	5.00
87914-0213	-----	-----	-----	-----	2	-----	3	2.54	----	10.92	5.84	2.79
87914-0223	-----	-----	-----	-----	2	-----	3	2.54	----	12.25	7.00	2.96
87914-0233	-----	-----	-----	-----	2	-----	3	2.54	----	13.38	6.09	5.00
87914-0214	-----	-----	-----	-----	2	-----	4	2.54	----	10.92	5.84	2.79
87914-0224	-----	-----	-----	-----	2	-----	4	2.54	----	12.25	7.00	2.96
87914-0234	-----	-----	-----	-----	2	-----	4	2.54	----	13.38	6.09	5.00
87914-0215	-----	-----	-----	-----	2	-----	5	2.54	----	10.92	5.84	2.79
87914-0225	-----	-----	-----	-----	2	-----	5	2.54	----	12.25	7.00	2.96
87914-0235	-----	-----	-----	-----	2	-----	5	2.54	----	13.38	6.09	5.00
87914-0216	-----	-----	-----	-----	2	-----	6	2.54	----	10.92	5.84	2.79
87914-0226	-----	-----	-----	-----	2	-----	6	2.54	----	12.25	7.00	2.96
87914-0236	-----	-----	-----	-----	2	-----	6	2.54	----	13.38	6.09	5.00

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

MIGRATED TO NX 2017/03/17 2017/05/09 EC NO: 114031 DRWN: FCSCC CHK'D: KHLIM REV APPR:	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE				
			MM	INCH	MM	NTS			
	4 PLACES	±	±	DRWN BY	DATE		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H		
	3 PLACES	±	±	KCHO	2004/11/05				
	2 PLACES	± 0.2	±	CHK'D BY	DATE				
	1 PLACES	±	±	PTLIM	2004/12/08				
	0 PLACES	±	±	APPR BY	DATE		PRODUCT CUSTOMER DRAWING		
				MLONG	2010/09/06				
	ANGULAR TOL = 3.0			DRAWING SIZE	THIRD ANGLE PROJECTION		SERIES	MATERIAL NUMBER	CUSTOMER
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			A3			87914	SEE TABLE	GENERAL MARKET
						DOCUMENT NUMBER	DOC TYPE	DOC PART	SHEET NUMBER
						SD-87914-013	PSD	000	2 OF 45

RELEASE STATUS	RELEASE DATE

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-0411	-----	-----	-----	-----	4	-----	1	5.08	2.54	10.92	5.84	2.79
87914-0421	-----	-----	-----	-----	4	-----	1	5.08	2.54	12.25	7.00	2.96
87914-0431	-----	-----	-----	-----	4	-----	1	5.08	2.54	13.38	6.09	5.00
87914-0412	-----	-----	-----	-----	4	-----	2	5.08	2.54	10.92	5.84	2.79
87914-0422	-----	-----	-----	-----	4	-----	2	5.08	2.54	12.25	7.00	2.96
87914-0432	-----	-----	-----	-----	4	-----	2	5.08	2.54	13.38	6.09	5.00
87914-0413	-----	-----	-----	-----	4	-----	3	5.08	2.54	10.92	5.84	2.79
87914-0423	-----	-----	-----	-----	4	-----	3	5.08	2.54	12.25	7.00	2.96
87914-0433	-----	-----	-----	-----	4	-----	3	5.08	2.54	13.38	6.09	5.00
87914-0414	-----	-----	-----	-----	4	-----	4	5.08	2.54	10.92	5.84	2.79
87914-0424	-----	-----	-----	-----	4	-----	4	5.08	2.54	12.25	7.00	2.96
87914-0434	-----	-----	-----	-----	4	-----	4	5.08	2.54	13.38	6.09	5.00
87914-0415	-----	-----	-----	-----	4	-----	5	5.08	2.54	10.92	5.84	2.79
87914-0425	-----	-----	-----	-----	4	-----	5	5.08	2.54	12.25	7.00	2.96
87914-0435	-----	-----	-----	-----	4	-----	5	5.08	2.54	13.38	6.09	5.00
87914-0416	-----	-----	-----	-----	4	-----	6	5.08	2.54	10.92	5.84	2.79
87914-0426	-----	-----	-----	-----	4	-----	6	5.08	2.54	12.25	7.00	2.96
87914-0436	-----	-----	-----	-----	4	-----	6	5.08	2.54	13.38	6.09	5.00

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

MIGRATED TO NX EC NO: 114031 DRWN: FCSCC CHK'D: KHLIM REV APPR: KHLIM	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE	
			MM	INCH	MM	NTS
	4 PLACES	±			DRWN BY	DATE
	3 PLACES	±			KCHO	2004/11/05
	2 PLACES	± 0.2			CHK'D BY	DATE
	1 PLACES	±			PTLIM	2004/12/08
	0 PLACES	±			APPR BY	DATE
					MLONG	2010/09/06
	ANGULAR TOL = 3.0		DRAWING SIZE	THIRD ANGLE PROJECTION		
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		A3			

2.54MM PITCH
DUAL ROW HEADER SINGLE WAFER, T/H


PRODUCT CUSTOMER DRAWING

SERIES	MATERIAL NUMBER	CUSTOMER
87914	SEE TABLE	GENERAL MARKET
DOCUMENT NUMBER	DOC TYPE	DOC PART
SD-87914-013	PSD	000
SHEET NUMBER		
3 OF 45		

RELEASE STATUS	RELEASE DATE
----------------	--------------

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION					
								A	B	F	M	P	G
87914-0611	-----	-----	-----	-----	6	-----	1	7.62	5.08	10.92	5.84	2.79	----
87914-0621	-----	-----	-----	-----	6	-----	1	7.62	5.08	12.25	7.00	2.96	----
87914-0631	-----	-----	-----	-----	6	-----	1	7.62	5.08	13.38	6.09	5.00	----
87914-0612	-----	-----	-----	-----	6	-----	2	7.62	5.08	10.92	5.84	2.79	----
87914-0622	-----	-----	-----	-----	6	-----	2	7.62	5.08	12.25	7.00	2.96	----
87914-0632	-----	-----	-----	-----	6	-----	2	7.62	5.08	13.38	6.09	5.00	----
87914-0613	-----	-----	-----	-----	6	-----	3	7.62	5.08	10.92	5.84	2.79	----
87914-0623	-----	-----	-----	-----	6	-----	3	7.62	5.08	12.25	7.00	2.96	----
87914-0633	-----	-----	-----	-----	6	-----	3	7.62	5.08	13.38	6.09	5.00	----
87914-0614	-----	-----	-----	-----	6	-----	4	7.62	5.08	10.92	5.84	2.79	----
87914-0624	-----	-----	-----	-----	6	-----	4	7.62	5.08	12.25	7.00	2.96	----
87914-0634	-----	-----	-----	-----	6	-----	4	7.62	5.08	13.38	6.09	5.00	----
87914-0615	-----	-----	-----	-----	6	-----	5	7.62	5.08	10.92	5.84	2.79	----
87914-0625	-----	-----	-----	-----	6	-----	5	7.62	5.08	12.25	7.00	2.96	----
87914-0635	-----	-----	-----	-----	6	-----	5	7.62	5.08	13.38	6.09	5.00	----
87914-0616	-----	-----	-----	-----	6	-----	6	7.62	5.08	10.92	5.84	2.79	----
87914-0626	-----	-----	-----	-----	6	-----	6	7.62	5.08	12.25	7.00	2.96	----
87914-0636	-----	-----	-----	-----	6	-----	6	7.62	5.08	13.38	6.09	5.00	----

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

MIGRATED TO NX	2017/03/17	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H			
				MM	INCH	MM	NTS				
		4 PLACES	±	±	DRWN BY	DATE	KCHO 2004/11/05				
		3 PLACES	±	±	CHK'D BY	DATE	PTLIM 2004/12/08				
						APPR BY	DATE	PRODUCT CUSTOMER DRAWING			
2 PLACES	±	±	MLONG 2010/09/06		SERIES	MATERIAL NUMBER	CUSTOMER				
1 PLACES	±	±	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		87914	SEE TABLE	GENERAL MARKET				
0 PLACES	±	±			DOCUMENT NUMBER	DOC TYPE	DOC PART		SHEET NUMBER		
						A3		SD-87914-013	PSD	000	4 OF 45

RELEASE STATUS	RELEASE DATE
----------------	--------------

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-0009	-----	-----	-----	-----	6	-----	1	7.62	5.08	18.84	13.25	3.30
87914-0642	-----	-----	-----	-----	6	-----	2	7.62	5.08	18.84	13.25	3.30
87914-0643	-----	-----	-----	-----	6	-----	3	7.62	5.08	18.84	13.25	3.30
87914-0644	-----	-----	-----	-----	6	-----	4	7.62	5.08	18.84	13.25	3.30
87914-0645	-----	-----	-----	-----	6	-----	5	7.62	5.08	18.84	13.25	3.30
87914-0646	-----	-----	-----	-----	6	-----	6	7.62	5.08	18.84	13.25	3.30

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

MIGRATED TO NX 2017/03/17 EC NO: 114031 DRWN: FCSCC CHK'D: REV APPR: KHLIM	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE	
			MM	INCH	MM	NTS
	4 PLACES	±	±	DRWN BY		DATE
	3 PLACES	±	±	KCHO		2004/11/05
	2 PLACES	±	0.2	CHK'D BY		DATE
	1 PLACES	±	±	PTLIM		2004/12/08
	0 PLACES	±	±	APPR BY		DATE
	ANGULAR TOL = 3.0		DRAWING SIZE		THIRD ANGLE PROJECTION	
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		A3			

molex [®]		
2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H		
PRODUCT CUSTOMER DRAWING		
SERIES	MATERIAL NUMBER	CUSTOMER
87914	SEE TABLE	GENERAL MARKET
DOCUMENT NUMBER	DOC TYPE	DOC PART SHEET NUMBER
SD-87914-013	PSD	000 5 OF 45

RELEASE STATUS	RELEASE DATE
----------------	--------------

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION					
								A	B	F	M	P	G
87914-0811	-----	-----	-----	-----	8	-----	1	10.16	7.62	10.92	5.84	2.79	----
87914-0821	-----	-----	-----	-----	8	-----	1	10.16	7.62	12.25	7.00	2.96	----
87914-0831	-----	-----	-----	-----	8	-----	1	10.16	7.62	13.38	6.09	5.00	----
87914-0812	-----	-----	-----	-----	8	-----	2	10.16	7.62	10.92	5.84	2.79	----
87914-0822	-----	-----	-----	-----	8	-----	2	10.16	7.62	12.25	7.00	2.96	----
87914-0832	-----	-----	-----	-----	8	-----	2	10.16	7.62	13.38	6.09	5.00	----
87914-0813	-----	-----	-----	-----	8	-----	3	10.16	7.62	10.92	5.84	2.79	----
87914-0823	-----	-----	-----	-----	8	-----	3	10.16	7.62	12.25	7.00	2.96	----
87914-0833	-----	-----	-----	-----	8	-----	4	10.16	7.62	13.38	6.09	5.00	----
87914-0814	-----	-----	-----	-----	8	-----	4	10.16	7.62	10.92	5.84	2.79	----
87914-0824	-----	-----	-----	-----	8	-----	4	10.16	7.62	12.25	7.00	2.96	----
87914-0834	-----	-----	-----	-----	8	-----	4	10.16	7.62	13.38	6.09	5.00	----
87914-0815	-----	-----	-----	-----	8	-----	5	10.16	7.62	10.92	5.84	2.79	----
87914-0825	-----	-----	-----	-----	8	-----	5	10.16	7.62	12.25	7.00	2.96	----
87914-0835	-----	-----	-----	-----	8	-----	5	10.16	7.62	13.38	6.09	5.00	----
87914-0816	-----	-----	-----	-----	8	-----	6	10.16	7.62	10.92	5.84	2.79	----
87914-0826	-----	-----	-----	-----	8	-----	6	10.16	7.62	12.25	7.00	2.96	----
87914-0836	-----	-----	-----	-----	8	-----	6	10.16	7.62	13.38	6.09	5.00	----

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

MIGRATED TO NX 2017/03/17 2017/05/09 EC NO: 114031 DRWN: FCSCC CHK'D: REV APPR: KHLIM	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE	
			MM	INCH	MM	NTS
	4 PLACES	±			DRWN BY	DATE
	3 PLACES	±			KCHO	2004/11/05
	2 PLACES	± 0.2			CHK'D BY	DATE
	1 PLACES	±			PTLIM	2004/12/08
	0 PLACES	±			APPR BY	DATE
					MLONG	2010/09/06
	ANGULAR TOL = 3.0			DRAWING SIZE	THIRD ANGLE PROJECTION	
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			A3		

molex®		
2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H		
PRODUCT CUSTOMER DRAWING		
SERIES	MATERIAL NUMBER	CUSTOMER
87914	SEE TABLE	GENERAL MARKET
DOCUMENT NUMBER		DOC TYPE
SD-87914-013		PSD
DOC PART	SHEET NUMBER	
000	6 OF 45	

RELEASE STATUS	RELEASE DATE

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-0841	-----	-----	-----	-----	8	-----	1	10.16	7.62	13.51	8.75	2.47
87914-0842	-----	-----	-----	-----	8	-----	2	10.16	7.62	13.51	8.75	2.47
87914-0843	-----	-----	-----	-----	8	-----	3	10.16	7.62	13.51	8.75	2.47
87914-0844	-----	-----	-----	-----	8	-----	4	10.16	7.62	13.51	8.75	2.47
87914-0845	-----	-----	-----	-----	8	-----	5	10.16	7.62	13.51	8.75	2.47
87914-0005	-----	-----	-----	-----	8	-----	6	10.16	7.62	13.51	8.75	2.47

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

MIGRATED TO NX EC NO: 114031 DRWN: FCSCC CHK'D: KHLIM REV APPR: KHLIM 2017/03/17 2017/05/09	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS	SCALE	<h1 style="margin: 0;">molex®</h1> <p style="margin: 0;">2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H</p> <p style="margin: 0;">PRODUCT CUSTOMER DRAWING</p>
	MM	INCH	MM	NTS	
	4 PLACES ±	±	DRWN BY	DATE	
	3 PLACES ±	±	KCHO	2004/11/05	
	2 PLACES ± 0.2	±	CHK'D BY	DATE	
	1 PLACES ±	±	PTLIM	2004/12/08	
0 PLACES ±	±	APPR BY	DATE		
ANGULAR TOL = 3.0		MLONG	2010/09/06	SERIES: 87914 MATERIAL NUMBER: SEE TABLE CUSTOMER: GENERAL MARKET	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DRAWING SIZE	THIRD ANGLE PROJECTION		
		A3		DOCUMENT NUMBER: SD-87914-013 DOC TYPE: PSD DOC PART: 000 SHEET NUMBER: 7 OF 45	

RELEASE STATUS	RELEASE DATE
----------------	--------------

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	PART NO. FOR BULK PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION					
									A	B	F	M	P	G
87914-1011	-----	-----	-----	-----	-----	10	-----	1	12.70	10.16	10.92	5.84	2.79	----
87914-1021	-----	-----	-----	-----	-----	10	-----	1	12.70	10.16	12.25	7.00	2.96	----
87914-1031	-----	-----	-----	-----	-----	10	-----	1	12.70	10.16	13.38	6.09	5.00	----
87914-1012	-----	-----	-----	-----	-----	10	-----	2	12.70	10.16	10.92	5.84	2.79	----
87914-1022	-----	-----	-----	-----	-----	10	-----	2	12.70	10.16	12.25	7.00	2.96	----
87914-1032	-----	-----	-----	-----	-----	10	-----	2	12.70	10.16	13.38	6.09	5.00	----
87914-1013	-----	-----	-----	-----	-----	10	-----	3	12.70	10.16	10.92	5.84	2.79	----
87914-1023	-----	-----	-----	-----	-----	10	-----	3	12.70	10.16	12.25	7.00	2.96	----
87914-1033	-----	-----	-----	-----	-----	10	-----	3	12.70	10.16	13.38	6.09	5.00	----
87914-1014	-----	-----	-----	-----	-----	10	-----	4	12.70	10.16	10.92	5.84	2.79	----
87914-1024	-----	-----	-----	-----	-----	10	-----	4	12.70	10.16	12.25	7.00	2.96	----
87914-1034	-----	-----	-----	-----	-----	10	-----	4	12.70	10.16	13.38	6.09	5.00	----
87914-1015	-----	-----	-----	-----	-----	10	-----	5	12.70	10.16	10.92	5.84	2.79	----
87914-1025	-----	-----	-----	-----	-----	10	-----	5	12.70	10.16	12.25	7.00	2.96	----
87914-1035	-----	-----	-----	-----	-----	10	-----	5	12.70	10.16	13.38	6.09	5.00	----
87914-1016	-----	-----	-----	-----	-----	10	-----	6	12.70	10.16	10.92	5.84	2.79	----
87914-1026	-----	-----	-----	-----	-----	10	-----	6	12.70	10.16	12.25	7.00	2.96	----
87914-1036	-----	-----	-----	-----	-----	10	-----	6	12.70	10.16	13.38	6.09	5.00	----
-----	-----	-----	-----	-----	87914-1037	10	9	4	12.70	10.16	10.92	5.84	2.79	----

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION



MIGRATED TO NX EC NO: 114031 DRWN: FCSCC CHK'D: KHLIM REV APPR: KHLIM	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE	
			MM	INCH	MM	NTS
	4 PLACES	±	±	DRWN BY	DATE	
	3 PLACES	±	±	KCHO	2004/11/05	
	2 PLACES	± 0.2	±	CHK'D BY	DATE	
	1 PLACES	±	±	PTLIM	2004/12/08	
0 PLACES	±	±	APPR BY	DATE		
			MLONG	2010/09/06		
ANGULAR TOL = 3.0			DRAWING SIZE	THIRD ANGLE PROJECTION		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			A3			

molex®		
2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H		
PRODUCT CUSTOMER DRAWING		
SERIES	MATERIAL NUMBER	CUSTOMER
87914	SEE TABLE	GENERAL MARKET
DOCUMENT NUMBER	DOC TYPE	DOC PART SHEET NUMBER
SD-87914-013	PSD	000 8 OF 45

RELEASE STATUS	RELEASE DATE
----------------	--------------

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-1211	-----	-----	-----	-----	12	-----	1	15.24	12.70	10.92	5.84	2.79
-----	87914-1291	-----	-----	-----	12	-----	9	15.24	12.70	10.92	5.84	2.79
87914-1221	-----	-----	-----	-----	12	-----	1	15.24	12.70	12.25	7.00	2.96
87914-1231	-----	-----	-----	-----	12	-----	1	15.24	12.70	13.38	6.09	5.00
87914-1212	-----	-----	-----	-----	12	-----	2	15.24	12.70	10.92	5.84	2.79
87914-1222	-----	-----	-----	-----	12	-----	2	15.24	12.70	12.25	7.00	2.96
87914-1232	-----	-----	-----	-----	12	-----	2	15.24	12.70	13.38	6.09	5.00
87914-1213	-----	-----	-----	-----	12	-----	3	15.24	12.70	10.92	5.84	2.79
87914-1223	-----	-----	-----	-----	12	-----	3	15.24	12.70	12.25	7.00	2.96
87914-1233	-----	-----	-----	-----	12	-----	3	15.24	12.70	13.38	6.09	5.00
87914-1214	-----	-----	-----	-----	12	-----	4	15.24	12.70	10.92	5.84	2.79
87914-1224	-----	-----	-----	-----	12	-----	4	15.24	12.70	12.25	7.00	2.96
87914-1234	-----	-----	-----	-----	12	-----	4	15.24	12.70	13.38	6.09	5.00
87914-1215	-----	-----	-----	-----	12	-----	5	15.24	12.70	10.92	5.84	2.79
87914-1225	-----	-----	-----	-----	12	-----	5	15.24	12.70	12.25	7.00	2.96
87914-1235	-----	-----	-----	-----	12	-----	5	15.24	12.70	13.38	6.09	5.00
87914-1216	-----	-----	-----	-----	12	-----	6	15.24	12.70	10.92	5.84	2.79
87914-1226	-----	-----	-----	-----	12	-----	6	15.24	12.70	12.25	7.00	2.96
87914-1236	-----	-----	-----	-----	12	-----	6	15.24	12.70	13.38	6.09	5.00

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

MIGRATED TO NX EC NO: 114031 DRWN: FCSCC CHK'D: KHLIM REV APPR: 2017/03/17 2017/05/09	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE					
			MM	INCH	MM	NTS				
	4 PLACES ±		±	±	DRWN BY	DATE		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H		
	3 PLACES ±		±	±	KCHO	2004/11/05				
	2 PLACES ± 0.2		±	±	CHK'D BY	DATE				
	1 PLACES ±		±	±	PTLIM	2004/12/08		PRODUCT CUSTOMER DRAWING		
	0 PLACES ±		±	±	APPR BY	DATE				
	ANGULAR TOL = 3.0				MLONG	2010/09/06		SERIES	MATERIAL NUMBER	CUSTOMER
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				DRAWING SIZE	THIRD ANGLE PROJECTION		87914	SEE TABLE	GENERAL MARKET
					A3			DOCUMENT NUMBER	DOC TYPE	DOC PART
							SD-87914-013	PSD	000	9 OF 45

RELEASE STATUS	RELEASE DATE
----------------	--------------

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-1251	-----	-----	-----	-----	12	-----	1	15.24	12.70	18.40	13.08	3.03
87914-1252	-----	-----	-----	-----	12	-----	2	15.24	12.70	18.40	13.08	3.03
87914-1253	-----	-----	-----	-----	12	-----	3	15.24	12.70	18.40	13.08	3.03
87914-1254	-----	-----	-----	-----	12	-----	4	15.24	12.70	18.40	13.08	3.03
87914-1255	-----	-----	-----	-----	12	-----	5	15.24	12.70	18.40	13.08	3.03
87914-1256	-----	-----	-----	-----	12	-----	6	15.24	12.70	18.40	13.08	3.03
87914-1241	-----	-----	-----	-----	12	-----	1	15.24	12.70	12.50	6.95	3.26
87914-1242	-----	-----	-----	-----	12	-----	2	15.24	12.70	12.50	6.95	3.26
87914-1243	-----	-----	-----	-----	12	-----	3	15.24	12.70	12.50	6.95	3.26
87914-1244	-----	-----	-----	-----	12	-----	4	15.24	12.70	12.50	6.95	3.26
87914-1245	-----	-----	-----	-----	12	-----	5	15.24	12.70	12.50	6.95	3.26



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

MIGRATED TO NX EC NO: 114031 DRWN: FCSCC CHKD: KHLIM 2017/03/17 2017/05/09	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS	SCALE	<h1>molex®</h1> <p>2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H</p> <p>PRODUCT CUSTOMER DRAWING</p> <p>SERIES: 87914 MATERIAL NUMBER: SEE TABLE CUSTOMER: GENERAL MARKET</p> <p>DOCUMENT NUMBER: SD-87914-013 DOC TYPE: PSD DOC PART: 000 SHEET NUMBER: 10 OF 45</p>	
			MM	NTS		
	4 PLACES	±	MM	INCH		DRWN BY: KCHO DATE: 2004/11/05
	3 PLACES	±				CHK'D BY: PTLIM DATE: 2004/12/08
	2 PLACES	± 0.2				APPR BY: MLONG DATE: 2010/09/06
1 PLACES	±					
0 PLACES	±					
		ANGULAR TOL = 3.0		DRAWING SIZE: A3	THIRD ANGLE PROJECTION	
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				

RELEASE STATUS	RELEASE DATE
----------------	--------------

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-1411	-----	-----	-----	-----	14	-----	1	17.78	15.24	10.92	5.84	2.79
87914-1421	-----	-----	-----	-----	14	-----	1	17.78	15.24	12.25	7.00	2.96
87914-1431	-----	-----	-----	-----	14	-----	1	17.78	15.24	13.38	6.09	5.00
87914-1412	-----	-----	-----	-----	14	-----	2	17.78	15.24	10.92	5.84	2.79
87914-1422	-----	-----	-----	-----	14	-----	2	17.78	15.24	12.25	7.00	2.96
87914-1432	-----	-----	-----	-----	14	-----	2	17.78	15.24	13.38	6.09	5.00
87914-1413	-----	-----	-----	-----	14	-----	3	17.78	15.24	10.92	5.84	2.79
87914-1423	-----	-----	-----	-----	14	-----	3	17.78	15.24	12.25	7.00	2.96
87914-1433	-----	-----	-----	-----	14	-----	3	17.78	15.24	13.38	6.09	5.00
87914-1414	-----	-----	-----	-----	14	-----	4	17.78	15.24	10.92	5.84	2.79
87914-1424	-----	-----	-----	-----	14	-----	4	17.78	15.24	12.25	7.00	2.96
87914-1434	-----	-----	-----	-----	14	-----	4	17.78	15.24	13.38	6.09	5.00
87914-1415	-----	-----	-----	-----	14	-----	5	17.78	15.24	10.92	5.84	2.79
87914-1425	-----	-----	-----	-----	14	-----	5	17.78	15.24	12.25	7.00	2.96
87914-1435	-----	-----	-----	-----	14	-----	5	17.78	15.24	13.38	6.09	5.00
87914-1416	-----	-----	-----	-----	14	-----	6	17.78	15.24	10.92	5.84	2.79
87914-1426	-----	-----	-----	-----	14	-----	6	17.78	15.24	12.25	7.00	2.96
87914-1436	-----	-----	-----	-----	14	-----	6	17.78	15.24	13.38	6.09	5.00


THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

MIGRATED TO NX EC NO: 114031 DRWN: FCSCC CHK'D: KHLIM REV APPR: 2017/03/17 2017/05/09	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE								
			MM	INCH	MM	NTS							
	4 PLACES	±		±	DRWN BY	DATE		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H					
	3 PLACES	±		±	KCHO	2004/11/05							
	2 PLACES	± 0.2		±	CHK'D BY	DATE							
	1 PLACES	±		±	PTLIM	2004/12/08		PRODUCT CUSTOMER DRAWING					
	0 PLACES	±		±	APPR BY	DATE							
	ANGULAR TOL = 3.0		DRAWING SIZE		THIRD ANGLE PROJECTION		MLONG		2010/09/06				
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		A3				SERIES		MATERIAL NUMBER		CUSTOMER		
							87914		SEE TABLE		GENERAL MARKET		
						DOCUMENT NUMBER		DOC TYPE		DOC PART		SHEET NUMBER	
						SD-87914-013		PSD		000		11 OF 45	

RELEASE STATUS	RELEASE DATE
----------------	--------------

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-1441	-----	-----	-----	-----	14	-----	1	17.78	15.24	13.42	8.08	3.05
87914-1442	-----	-----	-----	-----	14	-----	2	17.78	15.24	13.42	8.08	3.05
87914-1443	-----	-----	-----	-----	14	-----	3	17.78	15.24	13.42	8.08	3.05
87914-1444	-----	-----	-----	-----	14	-----	4	17.78	15.24	13.42	8.08	3.05
87914-1445	-----	-----	-----	-----	14	-----	5	17.78	15.24	13.42	8.08	3.05



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

MIGRATED TO NX EC NO: 114031 DRWN: FCSCC CHK'D: KHLIM REV APPR: 2017/03/17 2017/05/09	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS	SCALE	molex®			
	MM	INCH	MM	NTS				
	4 PLACES ±	±	DRWN BY	DATE	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H			
	3 PLACES ±	±	KCHO	2004/11/05				
	2 PLACES ±	0.2 ±	CHK'D BY	DATE				
	1 PLACES ±	±	PTLIM	2004/12/08				
0 PLACES ±	±	APPR BY	DATE					
ANGULAR TOL = 3.0		MLONG	2010/09/06	PRODUCT CUSTOMER DRAWING				
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DRAWING SIZE	THIRD ANGLE PROJECTION			SERIES	MATERIAL NUMBER	CUSTOMER
		A3				87914	SEE TABLE	GENERAL MARKET
DOCUMENT NUMBER		DOC TYPE	DOC PART	SHEET NUMBER				
D18		SD-87914-013	PSD	000	12 OF 45			

RELEASE STATUS	RELEASE DATE
----------------	--------------

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-1611	-----	-----	-----	-----	16	-----	1	20.32	17.78	10.92	5.84	2.79
87914-1621	-----	-----	-----	-----	16	-----	1	20.32	17.78	12.25	7.00	2.96
87914-1631	-----	-----	-----	-----	16	-----	1	20.32	17.78	13.38	6.09	5.00
87914-1612	-----	-----	-----	-----	16	-----	2	20.32	17.78	10.92	5.84	2.79
87914-1622	-----	-----	-----	-----	16	-----	2	20.32	17.78	12.25	7.00	2.96
87914-1632	-----	-----	-----	-----	16	-----	2	20.32	17.78	13.38	6.09	5.00
87914-1613	-----	-----	-----	-----	16	-----	3	20.32	17.78	10.92	5.84	2.79
87914-1623	-----	-----	-----	-----	16	-----	3	20.32	17.78	12.25	7.00	2.96
87914-1633	-----	-----	-----	-----	16	-----	3	20.32	17.78	13.38	6.09	5.00
87914-1614	-----	-----	-----	-----	16	-----	4	20.32	17.78	10.92	5.84	2.79
87914-1624	-----	-----	-----	-----	16	-----	4	20.32	17.78	12.25	7.00	2.96
87914-1634	-----	-----	-----	-----	16	-----	4	20.32	17.78	13.38	6.09	5.00
87914-1615	-----	-----	-----	-----	16	-----	5	20.32	17.78	10.92	5.84	2.79
87914-1625	-----	-----	-----	-----	16	-----	5	20.32	17.78	12.25	7.00	2.96
87914-1635	-----	-----	-----	-----	16	-----	5	20.32	17.78	13.38	6.09	5.00
87914-1616	-----	-----	-----	-----	16	-----	6	20.32	17.78	10.92	5.84	2.79
87914-1626	-----	-----	-----	-----	16	-----	6	20.32	17.78	12.25	7.00	2.96
87914-1636	-----	-----	-----	-----	16	-----	6	20.32	17.78	13.38	6.09	5.00

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

MIGRATED TO NX EC NO: 114031 DRWN: FCSCC CHK'D: KHLIM REV APPR: KHLIM	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE					
			MM	INCH	MM	NTS				
	4 PLACES ±		±	±	DRWN BY	DATE		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H		
	3 PLACES ±		±	±	KCHO	2004/11/05				
	2 PLACES ± 0.2		±	±	CHK'D BY	DATE				
	1 PLACES ±		±	±	PTLIM	2004/12/08		PRODUCT CUSTOMER DRAWING		
	0 PLACES ±		±	±	APPR BY	DATE				
	ANGULAR TOL = 3.0				MLONG	2010/09/06		SERIES	MATERIAL NUMBER	CUSTOMER
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				DRAWING SIZE	THIRD ANGLE PROJECTION		87914	SEE TABLE	GENERAL MARKET
					A3			DOCUMENT NUMBER	DOC TYPE	DOC PART
							SD-87914-013	PSD	000	13 OF 45

RELEASE STATUS	RELEASE DATE
----------------	--------------

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION					
								A	B	F	M	P	G
87914-1811	-----	-----	-----	-----	18	-----	1	22.86	20.32	10.92	5.84	2.79	----
87914-1821	-----	-----	-----	-----	18	-----	1	22.86	20.32	12.25	7.00	2.96	----
87914-1831	-----	-----	-----	-----	18	-----	1	22.86	20.32	13.38	6.09	5.00	----
87914-1812	-----	-----	-----	-----	18	-----	2	22.86	20.32	10.92	5.84	2.79	----
87914-1822	-----	-----	-----	-----	18	-----	2	22.86	20.32	12.25	7.00	2.96	----
87914-1832	-----	-----	-----	-----	18	-----	2	22.86	20.32	13.38	6.09	5.00	----
87914-1813	-----	-----	-----	-----	18	-----	3	22.86	20.32	10.92	5.84	2.79	----
87914-1823	-----	-----	-----	-----	18	-----	3	22.86	20.32	12.25	7.00	2.96	----
87914-1833	-----	-----	-----	-----	18	-----	3	22.86	20.32	13.38	6.09	5.00	----
87914-1814	-----	-----	-----	-----	18	-----	4	22.86	20.32	10.92	5.84	2.79	----
87914-1824	-----	-----	-----	-----	18	-----	4	22.86	20.32	12.25	7.00	2.96	----
87914-1834	-----	-----	-----	-----	18	-----	4	22.86	20.32	13.38	6.09	5.00	----
87914-1815	-----	-----	-----	-----	18	-----	5	22.86	20.32	10.92	5.84	2.79	----
87914-1825	-----	-----	-----	-----	18	-----	5	22.86	20.32	12.25	7.00	2.96	----
87914-1835	-----	-----	-----	-----	18	-----	5	22.86	20.32	13.38	6.09	5.00	----
87914-1816	-----	-----	-----	-----	18	-----	6	22.86	20.32	10.92	5.84	2.79	----
87914-1826	-----	-----	-----	-----	18	-----	6	22.86	20.32	12.25	7.00	2.96	----
87914-1836	-----	-----	-----	-----	18	-----	6	22.86	20.32	13.38	6.09	5.00	----

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION


MIGRATED TO NX 2017/03/17 2017/05/09 EC NO: 114031 DRWN: FCSCC CHK'D: KHLIM REV APPR:	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE	
			MM	INCH	MM	NTS
	4 PLACES	±			DRWN BY	DATE
	3 PLACES	±			KCHO	2004/11/05
	2 PLACES	± 0.2			CHK'D BY	DATE
	1 PLACES	±			PTLIM	2004/12/08
	0 PLACES	±			APPR BY	DATE
					MLONG	2010/09/06
	ANGULAR TOL = 3.0		DRAWING SIZE	THIRD ANGLE PROJECTION		
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		A3			


molex®		
2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H		
PRODUCT CUSTOMER DRAWING		
SERIES	MATERIAL NUMBER	CUSTOMER
87914	SEE TABLE	GENERAL MARKET
DOCUMENT NUMBER	DOC TYPE	DOC PART SHEET NUMBER
SD-87914-013	PSD	000 14 OF 45

RELEASE STATUS	RELEASE DATE
----------------	--------------

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-2011	-----	-----	-----	-----	20	-----	1	25.40	22.86	10.92	5.84	2.79
87914-2021	-----	-----	-----	-----	20	-----	1	25.40	22.86	12.25	7.00	2.96
87914-2031	-----	-----	-----	-----	20	-----	1	25.40	22.86	13.38	6.09	5.00
87914-2012	-----	-----	-----	-----	20	-----	2	25.40	22.86	10.92	5.84	2.79
87914-2022	-----	-----	-----	-----	20	-----	2	25.40	22.86	12.25	7.00	2.96
87914-2032	-----	-----	-----	-----	20	-----	2	25.40	22.86	13.38	6.09	5.00
87914-2013	-----	-----	-----	-----	20	-----	3	25.40	22.86	10.92	5.84	2.79
87914-2023	-----	-----	-----	-----	20	-----	3	25.40	22.86	12.25	7.00	2.96
87914-2033	-----	-----	-----	-----	20	-----	3	25.40	22.86	13.38	6.09	5.00
87914-2014	-----	-----	-----	-----	20	-----	4	25.40	22.86	10.92	5.84	2.79
87914-2024	-----	-----	-----	-----	20	-----	4	25.40	22.86	12.25	7.00	2.96
87914-2034	-----	-----	-----	-----	20	-----	4	25.40	22.86	13.38	6.09	5.00
87914-2015	-----	-----	-----	-----	20	-----	5	25.40	22.86	10.92	5.84	2.79
87914-2025	-----	-----	-----	-----	20	-----	5	25.40	22.86	12.25	7.00	2.96
87914-2035	-----	-----	-----	-----	20	-----	5	25.40	22.86	13.38	6.09	5.00
87914-2016	-----	-----	-----	-----	20	-----	6	25.40	22.86	10.92	5.84	2.79
87914-2026	-----	-----	-----	-----	20	-----	6	25.40	22.86	12.25	7.00	2.96
87914-2036	-----	-----	-----	-----	20	-----	6	25.40	22.86	13.38	6.09	5.00

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

MIGRATED TO NX 2017/03/17 EC NO: 114031 DRWN: FCSCC CHK'D: REV APPR: KHLIM	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE	
			MM	INCH	MM	NTS
	4 PLACES	±			DRWN BY	DATE
	3 PLACES	±			KCHO	2004/11/05
	2 PLACES	± 0.2			CHK'D BY	DATE
	1 PLACES	±			PTLIM	2004/12/08
0 PLACES	±			APPR BY	DATE	
				MLONG	2010/09/06	
ANGULAR TOL = 3.0			DRAWING SIZE	THIRD ANGLE PROJECTION		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			A3			



2.54MM PITCH
DUAL ROW HEADER SINGLE WAFER, T/H

PRODUCT CUSTOMER DRAWING



SERIES	MATERIAL NUMBER	CUSTOMER
87914	SEE TABLE	GENERAL MARKET

DOCUMENT NUMBER	DOC TYPE	DOC PART	SHEET NUMBER
SD-87914-013	PSD	000	15 OF 45

RELEASE STATUS	RELEASE DATE
----------------	--------------

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-2211	-----	-----	-----	-----	22	-----	1	27.94	25.40	10.92	5.84	2.79
87914-2221	-----	-----	-----	-----	22	-----	1	27.94	25.40	12.25	7.00	2.96
87914-2231	-----	-----	-----	-----	22	-----	1	27.94	25.40	13.38	6.09	5.00
87914-2212	-----	-----	-----	-----	22	-----	2	27.94	25.40	10.92	5.84	2.79
87914-2222	-----	-----	-----	-----	22	-----	2	27.94	25.40	12.25	7.00	2.96
87914-2232	-----	-----	-----	-----	22	-----	2	27.94	25.40	13.38	6.09	5.00
87914-2213	-----	-----	-----	-----	22	-----	3	27.94	25.40	10.92	5.84	2.79
87914-2223	-----	-----	-----	-----	22	-----	3	27.94	25.40	12.25	7.00	2.96
87914-2233	-----	-----	-----	-----	22	-----	3	27.94	25.40	13.38	6.09	5.00
87914-2214	-----	-----	-----	-----	22	-----	4	27.94	25.40	10.92	5.84	2.79
87914-2224	-----	-----	-----	-----	22	-----	4	27.94	25.40	12.25	7.00	2.96
87914-2234	-----	-----	-----	-----	22	-----	4	27.94	25.40	13.38	6.09	5.00
87914-2215	-----	-----	-----	-----	22	-----	5	27.94	25.40	10.92	5.84	2.79
87914-2225	-----	-----	-----	-----	22	-----	5	27.94	25.40	12.25	7.00	2.96
87914-2235	-----	-----	-----	-----	22	-----	5	27.94	25.40	13.38	6.09	5.00
87914-2216	-----	-----	-----	-----	22	-----	6	27.94	25.40	10.92	5.84	2.79
87914-2226	-----	-----	-----	-----	22	-----	6	27.94	25.40	12.25	7.00	2.96
87914-2236	-----	-----	-----	-----	22	-----	6	27.94	25.40	13.38	6.09	5.00

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION


MIGRATED TO NX 2017/03/17 EC NO: 114031 DRWN: FCSCC CHK'D: REV APPR: KHLIM	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H PRODUCT CUSTOMER DRAWING
			MM	INCH	MM	NTS	
	4 PLACES	±		±	DRWN BY	DATE	
	3 PLACES	±		±	KCHO	2004/11/05	
	2 PLACES	± 0.2		±	CHK'D BY	DATE	
1 PLACES	±		±	PTLIM	2004/12/08		
0 PLACES	±		±	APPR BY	DATE		
				MLONG	2010/09/06		
ANGULAR TOL = 3.0			DRAWING SIZE	THIRD ANGLE PROJECTION			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			A3				

SERIES	MATERIAL NUMBER	CUSTOMER
87914	SEE TABLE	GENERAL MARKET
DOCUMENT NUMBER	DOC TYPE	DOC PART
SD-87914-013	PSD	000
SHEET NUMBER		
16 OF 45		

RELEASE STATUS	RELEASE DATE

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-2411	-----	-----	-----	-----	24	-----	1	30.48	27.94	10.92	5.84	2.79
87914-2421	-----	-----	-----	-----	24	-----	1	30.48	27.94	12.25	7.00	2.96
87914-2431	-----	-----	-----	-----	24	-----	1	30.48	27.94	13.38	6.09	5.00
87914-2412	-----	-----	-----	-----	24	-----	2	30.48	27.94	10.92	5.84	2.79
87914-2422	-----	-----	-----	-----	24	-----	2	30.48	27.94	12.25	7.00	2.96
87914-2432	-----	-----	-----	-----	24	-----	2	30.48	27.94	13.38	6.09	5.00
87914-2413	-----	-----	-----	-----	24	-----	3	30.48	27.94	10.92	5.84	2.79
87914-2423	-----	-----	-----	-----	24	-----	3	30.48	27.94	12.25	7.00	2.96
87914-2433	-----	-----	-----	-----	24	-----	3	30.48	27.94	13.38	6.09	5.00
87914-2414	-----	-----	-----	-----	24	-----	4	30.48	27.94	10.92	5.84	2.79
87914-2424	-----	-----	-----	-----	24	-----	4	30.48	27.94	12.25	7.00	2.96
87914-2434	-----	-----	-----	-----	24	-----	4	30.48	27.94	13.38	6.09	5.00
87914-2415	-----	-----	-----	-----	24	-----	5	30.48	27.94	10.92	5.84	2.79
87914-2425	-----	-----	-----	-----	24	-----	5	30.48	27.94	12.25	7.00	2.96
87914-2435	-----	-----	-----	-----	24	-----	5	30.48	27.94	13.38	6.09	5.00
87914-2416	-----	-----	-----	-----	24	-----	6	30.48	27.94	10.92	5.84	2.79
87914-2426	-----	-----	-----	-----	24	-----	6	30.48	27.94	12.25	7.00	2.96
87914-2436	-----	-----	-----	-----	24	-----	6	30.48	27.94	13.38	6.09	5.00

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

MIGRATED TO NX 2017/03/17 2017/05/09 EC NO: 114031 DRWN: FCSCC CHK'D: REV APPR: KHLIM	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE	
			MM	INCH	MM	NTS
	4 PLACES	±			DRWN BY	DATE
	3 PLACES	±			KCHO	2004/11/05
	2 PLACES	± 0.2			CHK'D BY	DATE
	1 PLACES	±			PTLIM	2004/12/08
	0 PLACES	±			APPR BY	DATE
					MLONG	2010/09/06
	ANGULAR TOL = 3.0		DRAWING SIZE	THIRD ANGLE PROJECTION		
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		A3			

molex®

2.54MM PITCH
DUAL ROW HEADER SINGLE WAFER, T/H

PRODUCT CUSTOMER DRAWING

SERIES	MATERIAL NUMBER	CUSTOMER
87914	SEE TABLE	GENERAL MARKET
DOCUMENT NUMBER	DOC TYPE	DOC PART
SD-87914-013	PSD	000
SHEET NUMBER		
17 OF 45		



PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-2611	-----	-----	-----	-----	26	-----	1	33.02	30.48	10.92	5.84	2.79
87914-2621	-----	-----	-----	-----	26	-----	1	33.02	30.48	12.25	7.00	2.96
87914-2631	-----	-----	-----	-----	26	-----	1	33.02	30.48	13.38	6.09	5.00
87914-2612	-----	-----	-----	-----	26	-----	2	33.02	30.48	10.92	5.84	2.79
87914-2622	-----	-----	-----	-----	26	-----	2	33.02	30.48	12.25	7.00	2.96
87914-2632	-----	-----	-----	-----	26	-----	2	33.02	30.48	13.38	6.09	5.00
87914-2613	-----	-----	-----	-----	26	-----	3	33.02	30.48	10.92	5.84	2.79
87914-2623	-----	-----	-----	-----	26	-----	3	33.02	30.48	12.25	7.00	2.96
87914-2633	-----	-----	-----	-----	26	-----	3	33.02	30.48	13.38	6.09	5.00
87914-2614	-----	-----	-----	-----	26	-----	4	33.02	30.48	10.92	5.84	2.79
87914-2624	-----	-----	-----	-----	26	-----	4	33.02	30.48	12.25	7.00	2.96
87914-2634	-----	-----	-----	-----	26	-----	4	33.02	30.48	13.38	6.09	5.00
87914-2615	-----	-----	-----	-----	26	-----	5	33.02	30.48	10.92	5.84	2.79
87914-2625	-----	-----	-----	-----	26	-----	5	33.02	30.48	12.25	7.00	2.96
87914-2635	-----	-----	-----	-----	26	-----	5	33.02	30.48	13.38	6.09	5.00
87914-2616	-----	-----	-----	-----	26	-----	6	33.02	30.48	10.92	5.84	2.79
87914-2626	-----	-----	-----	-----	26	-----	6	33.02	30.48	12.25	7.00	2.96
87914-2636	-----	-----	-----	-----	26	-----	6	33.02	30.48	13.38	6.09	5.00

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

MIGRATED TO NX EC NO: 114031 DRWN: FCSCC CHK'D: KHLIM REV APPR: KHLIM	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE			
			MM	INCH	NTS			
	4 PLACES	±			DRWN BY	DATE		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H
	3 PLACES	±			KCHO	2004/11/05		
	2 PLACES	± 0.2			CHK'D BY	DATE		
	1 PLACES	±			PTLIM	2004/12/08		PRODUCT CUSTOMER DRAWING
	0 PLACES	±			APPR BY	DATE		
ANGULAR TOL = 3.0		DRAWING SIZE		THIRD ANGLE PROJECTION		SERIES: 87914 MATERIAL NUMBER: SEE TABLE CUSTOMER: GENERAL MARKET		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		A3				DOCUMENT NUMBER: SD-87914-013 DOC TYPE: PSD DOC PART: 000 SHEET NUMBER: 18 OF 45		

RELEASE STATUS	RELEASE DATE
----------------	--------------

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-2811	-----	-----	-----	-----	28	-----	1	35.56	33.02	10.92	5.84	2.79
87914-2821	-----	-----	-----	-----	28	-----	1	35.56	33.02	12.25	7.00	2.96
87914-2831	-----	-----	-----	-----	28	-----	1	35.56	33.02	13.38	6.09	5.00
87914-2812	-----	-----	-----	-----	28	-----	2	35.56	33.02	10.92	5.84	2.79
87914-2822	-----	-----	-----	-----	28	-----	2	35.56	33.02	12.25	7.00	2.96
87914-2832	-----	-----	-----	-----	28	-----	2	35.56	33.02	13.38	6.09	5.00
87914-2813	-----	-----	-----	-----	28	-----	3	35.56	33.02	10.92	5.84	2.79
87914-2823	-----	-----	-----	-----	28	-----	3	35.56	33.02	12.25	7.00	2.96
87914-2833	-----	-----	-----	-----	28	-----	3	35.56	33.02	13.38	6.09	5.00
87914-2814	-----	-----	-----	-----	28	-----	4	35.56	33.02	10.92	5.84	2.79
87914-2824	-----	-----	-----	-----	28	-----	4	35.56	33.02	12.25	7.00	2.96
87914-2834	-----	-----	-----	-----	28	-----	4	35.56	33.02	13.38	6.09	5.00
87914-2815	-----	-----	-----	-----	28	-----	5	35.56	33.02	10.92	5.84	2.79
87914-2825	-----	-----	-----	-----	28	-----	5	35.56	33.02	12.25	7.00	2.96
87914-2835	-----	-----	-----	-----	28	-----	5	35.56	33.02	13.38	6.09	5.00
87914-2816	-----	-----	-----	-----	28	-----	6	35.56	33.02	10.92	5.84	2.79
87914-2826	-----	-----	-----	-----	28	-----	6	35.56	33.02	12.25	7.00	2.96
87914-2836	-----	-----	-----	-----	28	-----	6	35.56	33.02	13.38	6.09	5.00

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										
MIGRATED TO NX	2017/03/17	2017/05/09	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS	SCALE	 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H			
			MM	INCH	MM	NTS				
			4 PLACES ±		DRWN BY	DATE	PRODUCT CUSTOMER DRAWING			
			3 PLACES ±		KCHO	2004/11/05				
			2 PLACES ± 0.2		CHK'D BY	DATE	SERIES MATERIAL NUMBER CUSTOMER 87914 SEE TABLE GENERAL MARKET			
			1 PLACES ±		PTLIM	2004/12/08				
			0 PLACES ±		APPR BY	DATE	DOCUMENT NUMBER DOC TYPE DOC PART SHEET NUMBER SD-87914-013 PSD 000 19 OF 45			
			ANGULAR TOL = 3.0		MLONG	2010/09/06				
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DRAWING SIZE	THIRD ANGLE PROJECTION							
				A3						

RELEASE STATUS	RELEASE DATE
----------------	--------------


PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-3011	-----	-----	-----	-----	30	-----	1	38.10	35.56	10.92	5.84	2.79
87914-3021	-----	-----	-----	-----	30	-----	1	38.10	35.56	12.25	7.00	2.96
87914-3031	-----	-----	-----	-----	30	-----	1	38.10	35.56	13.38	6.09	5.00
87914-3012	-----	-----	-----	-----	30	-----	2	38.10	35.56	10.92	5.84	2.79
87914-3022	-----	-----	-----	-----	30	-----	2	38.10	35.56	12.25	7.00	2.96
87914-3032	-----	-----	-----	-----	30	-----	2	38.10	35.56	13.38	6.09	5.00
87914-3013	-----	-----	-----	-----	30	-----	3	38.10	35.56	10.92	5.84	2.79
87914-3023	-----	-----	-----	-----	30	-----	3	38.10	35.56	12.25	7.00	2.96
87914-3033	-----	-----	-----	-----	30	-----	3	38.10	35.56	13.38	6.09	5.00
87914-3014	-----	-----	-----	-----	30	-----	4	38.10	35.56	10.92	5.84	2.79
87914-3024	-----	-----	-----	-----	30	-----	4	38.10	35.56	12.25	7.00	2.96
87914-3034	-----	-----	-----	-----	30	-----	4	38.10	35.56	13.38	6.09	5.00
87914-3015	-----	-----	-----	-----	30	-----	5	38.10	35.56	10.92	5.84	2.79
87914-3025	-----	-----	-----	-----	30	-----	5	38.10	35.56	12.25	7.00	2.96
87914-3035	-----	-----	-----	-----	30	-----	5	38.10	35.56	13.38	6.09	5.00
87914-3016	-----	-----	-----	-----	30	-----	6	38.10	35.56	10.92	5.84	2.79
87914-3026	-----	-----	-----	-----	30	-----	6	38.10	35.56	12.25	7.00	2.96
87914-3036	-----	-----	-----	-----	30	-----	6	38.10	35.56	13.38	6.09	5.00

C

B

A

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

MIGRATED TO NX EC NO: 114031 DRWN: FCSCC CHK'D: KHLIM REV APPR: KHLIM	2017/03/17 2017/05/09		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE									
		MM	INCH	MM	INCH	DRWN BY	DATE	NTS								
	4 PLACES	±	±	KCHO			2004/11/05		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H							
	3 PLACES	±	±	CHK'D BY												
	2 PLACES	± 0.2	±	PTLIM			2004/12/08		PRODUCT CUSTOMER DRAWING							
	1 PLACES	±	±	APPR BY												
0 PLACES	±	±	MLONG			2010/09/06		SERIES: 87914		MATERIAL NUMBER: SEE TABLE		CUSTOMER: GENERAL MARKET				
ANGULAR TOL = 3.0			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		DRAWING SIZE: A3		THIRD ANGLE PROJECTION		DOCUMENT NUMBER: SD-87914-013		DOC TYPE: PSD		DOC PART: 000		SHEET NUMBER: 20 OF 45	

RELEASE STATUS	RELEASE DATE
----------------	--------------

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-3211	-----	-----	-----	-----	32	-----	1	40.64	38.10	10.92	5.84	2.79
87914-3221	-----	-----	-----	-----	32	-----	1	40.64	38.10	12.25	7.00	2.96
87914-3231	-----	-----	-----	-----	32	-----	1	40.64	38.10	13.38	6.09	5.00
87914-3212	-----	-----	-----	-----	32	-----	2	40.64	38.10	10.92	5.84	2.79
87914-3222	-----	-----	-----	-----	32	-----	2	40.64	38.10	12.25	7.00	2.96
87914-3232	-----	-----	-----	-----	32	-----	2	40.64	38.10	13.38	6.09	5.00
87914-3213	-----	-----	-----	-----	32	-----	3	40.64	38.10	10.92	5.84	2.79
87914-3223	-----	-----	-----	-----	32	-----	3	40.64	38.10	12.25	7.00	2.96
87914-3233	-----	-----	-----	-----	32	-----	3	40.64	38.10	13.38	6.09	5.00
87914-3214	-----	-----	-----	-----	32	-----	4	40.64	38.10	10.92	5.84	2.79
87914-3224	-----	-----	-----	-----	32	-----	4	40.64	38.10	12.25	7.00	2.96
87914-3234	-----	-----	-----	-----	32	-----	4	40.64	38.10	13.38	6.09	5.00
87914-3215	-----	-----	-----	-----	32	-----	5	40.64	38.10	10.92	5.84	2.79
87914-3225	-----	-----	-----	-----	32	-----	5	40.64	38.10	12.25	7.00	2.96
87914-3235	-----	-----	-----	-----	32	-----	5	40.64	38.10	13.38	6.09	5.00
87914-3216	-----	-----	-----	-----	32	-----	6	40.64	38.10	10.92	5.84	2.79
87914-3226	-----	-----	-----	-----	32	-----	6	40.64	38.10	12.25	7.00	2.96
87914-3236	-----	-----	-----	-----	32	-----	6	40.64	38.10	13.38	6.09	5.00

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

MIGRATED TO NX EC NO: 114031 DRWN: FCSCC CHK'D: KHLIM REV APPR: 2017/03/17 2017/05/09	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE	
			MM		MM	NTS
			INCH		DRWN BY	DATE
	4 PLACES	±	±	KCHO	2004/11/05	 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H
	3 PLACES	±	±	CHK'D BY	DATE	
	2 PLACES	± 0.2	±	PTLIM	2004/12/08	
	1 PLACES	±	±	APPR BY	DATE	PRODUCT CUSTOMER DRAWING SERIES: 87914 MATERIAL NUMBER: SEE TABLE CUSTOMER: GENERAL MARKET
0 PLACES	±	±	MLONG	2010/09/06		
ANGULAR TOL = 3.0			DRAWING SIZE	THIRD ANGLE PROJECTION		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			A3			

DOCUMENT NUMBER: SD-87914-013 DOC TYPE: PSD DOC PART: 000 SHEET NUMBER: 21 OF 45

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-3411	-----	-----	-----	-----	34	-----	1	43.18	40.64	10.92	5.84	2.79
87914-3421	-----	-----	-----	-----	34	-----	1	43.18	40.64	12.25	7.00	2.96
87914-3431	-----	-----	-----	-----	34	-----	1	43.18	40.64	13.38	6.09	5.00
87914-3412	-----	-----	-----	-----	34	-----	2	43.18	40.64	10.92	5.84	2.79
87914-3422	-----	-----	-----	-----	34	-----	2	43.18	40.64	12.25	7.00	2.96
87914-3432	-----	-----	-----	-----	34	-----	2	43.18	40.64	13.38	6.09	5.00
87914-3413	-----	-----	-----	-----	34	-----	3	43.18	40.64	10.92	5.84	2.79
87914-3423	-----	-----	-----	-----	34	-----	3	43.18	40.64	12.25	7.00	2.96
87914-3433	-----	-----	-----	-----	34	-----	3	43.18	40.64	13.38	6.09	5.00
87914-3414	-----	-----	-----	-----	34	-----	4	43.18	40.64	10.92	5.84	2.79
87914-3424	-----	-----	-----	-----	34	-----	4	43.18	40.64	12.25	7.00	2.96
87914-3434	-----	-----	-----	-----	34	-----	4	43.18	40.64	13.38	6.09	5.00
87914-3415	-----	-----	-----	-----	34	-----	5	43.18	40.64	10.92	5.84	2.79
87914-3425	-----	-----	-----	-----	34	-----	5	43.18	40.64	12.25	7.00	2.96
87914-3435	-----	-----	-----	-----	34	-----	5	43.18	40.64	13.38	6.09	5.00
87914-3416	-----	-----	-----	-----	34	-----	6	43.18	40.64	10.92	5.84	2.79
87914-3426	-----	-----	-----	-----	34	-----	6	43.18	40.64	12.25	7.00	2.96
87914-3436	-----	-----	-----	-----	34	-----	6	43.18	40.64	13.38	6.09	5.00

RELEASE STATUS: RELEASE DATE:

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

MIGRATED TO NX 2017/03/17 EC NO: 114031 DRWN: FCSCC CHK'D: KHLIM APPR: KHLIM	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		molex®	
			MM	INCH	MM	NTS		
					DRWN BY	DATE		
	4 PLACES ±				KCHO	2004/11/05	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H	
	3 PLACES ±				CHK'D BY	DATE		
	2 PLACES ± 0.2				PTLIM	2004/12/08		
	1 PLACES ±				APPR BY	DATE		
	0 PLACES ±				MLONG	2010/09/06		
	ANGULAR TOL = 3.0				DRAWING SIZE	THIRD ANGLE PROJECTION	PRODUCT CUSTOMER DRAWING SERIES: 87914 MATERIAL NUMBER: SEE TABLE CUSTOMER: GENERAL MARKET	
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				A3		DOCUMENT NUMBER: SD-87914-013 DOC TYPE: PSD DOC PART: 000 SHEET NUMBER: 22 OF 45	

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-3611	-----	-----	-----	-----	36	-----	1	45.72	43.18	10.92	5.84	2.79
87914-3621	-----	-----	-----	-----	36	-----	1	45.72	43.18	12.25	7.00	2.96
87914-3631	-----	-----	-----	-----	36	-----	1	45.72	43.18	13.38	6.09	5.00
87914-3612	-----	-----	-----	-----	36	-----	2	45.72	43.18	10.92	5.84	2.79
87914-3622	-----	-----	-----	-----	36	-----	2	45.72	43.18	12.25	7.00	2.96
87914-3632	-----	-----	-----	-----	36	-----	2	45.72	43.18	13.38	6.09	5.00
87914-3613	-----	-----	-----	-----	36	-----	3	45.72	43.18	10.92	5.84	2.79
87914-3623	-----	-----	-----	-----	36	-----	3	45.72	43.18	12.25	7.00	2.96
87914-3633	-----	-----	-----	-----	36	-----	3	45.72	43.18	13.38	6.09	5.00
87914-3614	-----	-----	-----	-----	36	-----	4	45.72	43.18	10.92	5.84	2.79
87914-3624	-----	-----	-----	-----	36	-----	4	45.72	43.18	12.25	7.00	2.96
87914-3634	-----	-----	-----	-----	36	-----	4	45.72	43.18	13.38	6.09	5.00
87914-3615	-----	-----	-----	-----	36	-----	5	45.72	43.18	10.92	5.84	2.79
87914-3625	-----	-----	-----	-----	36	-----	5	45.72	43.18	12.25	7.00	2.96
87914-3635	-----	-----	-----	-----	36	-----	5	45.72	43.18	13.38	6.09	5.00
87914-3616	-----	-----	-----	-----	36	-----	6	45.72	43.18	10.92	5.84	2.79
87914-3626	-----	-----	-----	-----	36	-----	6	45.72	43.18	12.25	7.00	2.96
87914-3636	-----	-----	-----	-----	36	-----	6	45.72	43.18	13.38	6.09	5.00



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

MIGRATED TO NX 2017/03/17 EC NO: 114031 DRWN: FCSCC CHK'D: REV APPR: KHLIM 2017/05/09	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE	
			MM	INCH	MM	NTS
	4 PLACES	±			DRWN BY	DATE
	3 PLACES	±			KCHO	2004/11/05
	2 PLACES	± 0.2			CHK'D BY	DATE
	1 PLACES	±			PTLIM	2004/12/08
0 PLACES	±			APPR BY	DATE	
				MLONG	2010/09/06	
	ANGULAR TOL = 3.0		DRAWING SIZE		THIRD ANGLE PROJECTION	
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		A3			

molex®		
2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H		
PRODUCT CUSTOMER DRAWING		
SERIES	MATERIAL NUMBER	CUSTOMER
87914	SEE TABLE	GENERAL MARKET
DOCUMENT NUMBER	DOC TYPE	DOC PART SHEET NUMBER
SD-87914-013	PSD	000 23 OF 45

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-3811	-----	-----	-----	-----	38	-----	1	48.26	45.72	10.92	5.84	2.79
87914-3821	-----	-----	-----	-----	38	-----	1	48.26	45.72	12.25	7.00	2.96
87914-3831	-----	-----	-----	-----	38	-----	1	48.26	45.72	13.38	6.09	5.00
87914-3812	-----	-----	-----	-----	38	-----	2	48.26	45.72	10.92	5.84	2.79
87914-3822	-----	-----	-----	-----	38	-----	2	48.26	45.72	12.25	7.00	2.96
87914-3832	-----	-----	-----	-----	38	-----	2	48.26	45.72	13.38	6.09	5.00
87914-3813	-----	-----	-----	-----	38	-----	3	48.26	45.72	10.92	5.84	2.79
87914-3823	-----	-----	-----	-----	38	-----	3	48.26	45.72	12.25	7.00	2.96
87914-3833	-----	-----	-----	-----	38	-----	3	48.26	45.72	13.38	6.09	5.00
87914-3814	-----	-----	-----	-----	38	-----	4	48.26	45.72	10.92	5.84	2.79
87914-3824	-----	-----	-----	-----	38	-----	4	48.26	45.72	12.25	7.00	2.96
87914-3834	-----	-----	-----	-----	38	-----	4	48.26	45.72	13.38	6.09	5.00
87914-3815	-----	-----	-----	-----	38	-----	5	48.26	45.72	10.92	5.84	2.79
87914-3825	-----	-----	-----	-----	38	-----	5	48.26	45.72	12.25	7.00	2.96
87914-3835	-----	-----	-----	-----	38	-----	5	48.26	45.72	13.38	6.09	5.00
87914-3816	-----	-----	-----	-----	38	-----	6	48.26	45.72	10.92	5.84	2.79
87914-3826	-----	-----	-----	-----	38	-----	6	48.26	45.72	12.25	7.00	2.96
87914-3836	-----	-----	-----	-----	38	-----	6	48.26	45.72	13.38	6.09	5.00


THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

MIGRATED TO NX EC NO: 114031 DRWN: FCSCC CHK'D: KHLIM REV APPR: KHLIM	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H PRODUCT CUSTOMER DRAWING	
			MM	INCH	MM	NTS		
	4 PLACES	±			DRWN BY	DATE		SERIES: 87914 MATERIAL NUMBER: SEE TABLE CUSTOMER: GENERAL MARKET DOCUMENT NUMBER: SD-87914-013 DOC TYPE: PSD DOC PART: 000 SHEET NUMBER: 24 OF 45
	3 PLACES	±			KCHO	2004/11/05		
	2 PLACES	± 0.2			CHK'D BY	DATE		
	1 PLACES	±			PTLIM	2004/12/08		
0 PLACES	±			APPR BY	DATE			
		ANGULAR TOL = 3.0	DRAWING SIZE		THIRD ANGLE PROJECTION			
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	A3					

RELEASE STATUS	RELEASE DATE
----------------	--------------

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-4011	-----	-----	-----	-----	40	-----	1	50.80	48.26	10.92	5.84	2.79
87914-4021	-----	-----	-----	-----	40	-----	1	50.80	48.26	12.25	7.00	2.96
87914-4031	-----	-----	-----	-----	40	-----	1	50.80	48.26	13.38	6.09	5.00
87914-4012	-----	-----	-----	-----	40	-----	2	50.80	48.26	10.92	5.84	2.79
87914-4022	-----	-----	-----	-----	40	-----	2	50.80	48.26	12.25	7.00	2.96
87914-4032	-----	-----	-----	-----	40	-----	2	50.80	48.26	13.38	6.09	5.00
87914-4013	-----	-----	-----	-----	40	-----	3	50.80	48.26	10.92	5.84	2.79
87914-4023	-----	-----	-----	-----	40	-----	3	50.80	48.26	12.25	7.00	2.96
87914-4033	-----	-----	-----	-----	40	-----	3	50.80	48.26	13.38	6.09	5.00
87914-4014	-----	-----	-----	-----	40	-----	4	50.80	48.26	10.92	5.84	2.79
87914-4024	-----	-----	-----	-----	40	-----	4	50.80	48.26	12.25	7.00	2.96
87914-4034	-----	-----	-----	-----	40	-----	4	50.80	48.26	13.38	6.09	5.00
87914-4015	-----	-----	-----	-----	40	-----	5	50.80	48.26	10.92	5.84	2.79
87914-4025	-----	-----	-----	-----	40	-----	5	50.80	48.26	12.25	7.00	2.96
87914-4035	-----	-----	-----	-----	40	-----	5	50.80	48.26	13.38	6.09	5.00
87914-4016	-----	-----	-----	-----	40	-----	6	50.80	48.26	10.92	5.84	2.79
87914-4026	-----	-----	-----	-----	40	-----	6	50.80	48.26	12.25	7.00	2.96
87914-4036	-----	-----	-----	-----	40	-----	6	50.80	48.26	13.38	6.09	5.00



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

MIGRATED TO NX EC NO: 114031 DRWN: FCSCC CHK'D: REV APPR: KHLIM	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE	
			MM		NTS	
	4 PLACES	±	MM	INCH	DRWN BY	DATE
	3 PLACES	±			KCHO	2004/11/05
	2 PLACES	± 0.2			CHK'D BY	DATE
	1 PLACES	±			PTLIM	2004/12/08
	0 PLACES	±			APPR BY	DATE
ANGULAR TOL = 3.0			DRAWING SIZE		THIRD ANGLE PROJECTION	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			A3			
			78914		SEE TABLE	
			DOCUMENT NUMBER		DOC TYPE	
			SD-87914-013		PSD	
			DOC PART		SHEET NUMBER	
			000		25 OF 45	

RELEASE STATUS	RELEASE DATE
----------------	--------------

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-4211	-----	-----	-----	-----	42	-----	1	53.34	50.80	10.92	5.84	2.79
87914-4221	-----	-----	-----	-----	42	-----	1	53.34	50.80	12.25	7.00	2.96
87914-4212	-----	-----	-----	-----	42	-----	2	53.34	50.80	10.92	5.84	2.79
87914-4222	-----	-----	-----	-----	42	-----	2	53.34	50.80	12.25	7.00	2.96
87914-4213	-----	-----	-----	-----	42	-----	3	53.34	50.80	10.92	5.84	2.79
87914-4223	-----	-----	-----	-----	42	-----	3	53.34	50.80	12.25	7.00	2.96
87914-4214	-----	-----	-----	-----	42	-----	4	53.34	50.80	10.92	5.84	2.79
87914-4224	-----	-----	-----	-----	42	-----	4	53.34	50.80	12.25	7.00	2.96
87914-4215	-----	-----	-----	-----	42	-----	5	53.34	50.80	10.92	5.84	2.79
87914-4225	-----	-----	-----	-----	42	-----	5	53.34	50.80	12.25	7.00	2.96
87914-4216	-----	-----	-----	-----	42	-----	6	53.34	50.80	10.92	5.84	2.79
87914-4226	-----	-----	-----	-----	42	-----	6	53.34	50.80	12.25	7.00	2.96



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

MIGRATED TO NX EC NO: 114031 DRWN: FCSCC CHK'D: KHLIM REV APPR: 2017/03/17 2017/05/09	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H PRODUCT CUSTOMER DRAWING	
			MM	INCH	MM	NTS		
	4 PLACES	±		±	DRWN BY	DATE		KCHO 2004/11/05
	3 PLACES	±		±	CHK'D BY	DATE		
	2 PLACES	± 0.2		±	PTLIM	2004/12/08		
	1 PLACES	±		±	APPR BY	DATE		MLONG 2010/09/06
	0 PLACES	±		±				
ANGULAR TOL = 3.0			DRAWING SIZE	THIRD ANGLE PROJECTION		A3		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS								
SERIES		MATERIAL NUMBER		CUSTOMER		87914 SEE TABLE GENERAL MARKET		
DOCUMENT NUMBER		DOC TYPE		DOC PART			SHEET NUMBER	
SD-87914-013		PSD		000		26 OF 45		

RELEASE STATUS	RELEASE DATE
----------------	--------------

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-4411	-----	-----	-----	-----	44	-----	1	55.88	53.34	10.92	5.84	2.79
87914-4421	-----	-----	-----	-----	44	-----	1	55.88	53.34	12.25	7.00	2.96
87914-4412	-----	-----	-----	-----	44	-----	2	55.88	53.34	10.92	5.84	2.79
87914-4422	-----	-----	-----	-----	44	-----	2	55.88	53.34	12.25	7.00	2.96
87914-4413	-----	-----	-----	-----	44	-----	3	55.88	53.34	10.92	5.84	2.79
87914-4423	-----	-----	-----	-----	44	-----	3	55.88	53.34	12.25	7.00	2.96
87914-4414	-----	-----	-----	-----	44	-----	4	55.88	53.34	10.92	5.84	2.79
87914-4424	-----	-----	-----	-----	44	-----	4	55.88	53.34	12.25	7.00	2.96
87914-4415	-----	-----	-----	-----	44	-----	5	55.88	53.34	10.92	5.84	2.79
87914-4425	-----	-----	-----	-----	44	-----	5	55.88	53.34	12.25	7.00	2.96
87914-4416	-----	-----	-----	-----	44	-----	6	55.88	53.34	10.92	5.84	2.79
87914-4426	-----	-----	-----	-----	44	-----	6	55.88	53.34	12.25	7.00	2.96

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

MIGRATED TO NX EC NO: 114031 DRWN: FCSCC CHK'D: KHLIM APPR: KHLIM	2017/03/17		2017/05/09		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE								
							MM INCH		MM NTS								
	4 PLACES		±		±		KCHO		DATE		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H						
	3 PLACES		±		±		CHK'D BY		DATE								
	2 PLACES		± 0.2		±		PTLIM		DATE								
	1 PLACES		±		±		APPR BY		DATE		PRODUCT CUSTOMER DRAWING						
	0 PLACES		±		±		MLONG		DATE								
							ANGULAR TOL = 3.0		DRAWING SIZE		THIRD ANGLE PROJECTION		SERIES	MATERIAL NUMBER		CUSTOMER	
							DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		A3				87914	SEE TABLE		GENERAL MARKET	
	D18	REV											DOCUMENT NUMBER		DOC TYPE	DOC PART	SHEET NUMBER
												SD-87914-013		PSD	000	27 OF 45	

RELEASE STATUS	RELEASE DATE
----------------	--------------

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-4611	-----	-----	-----	-----	46	-----	1	58.42	55.88	10.92	5.84	2.79
87914-4621	-----	-----	-----	-----	46	-----	1	58.42	55.88	12.25	7.00	2.96
87914-4612	-----	-----	-----	-----	46	-----	2	58.42	55.88	10.92	5.84	2.79
87914-4622	-----	-----	-----	-----	46	-----	2	58.42	55.88	12.25	7.00	2.96
87914-4613	-----	-----	-----	-----	46	-----	3	58.42	55.88	10.92	5.84	2.79
87914-4623	-----	-----	-----	-----	46	-----	3	58.42	55.88	12.25	7.00	2.96
87914-4614	-----	-----	-----	-----	46	-----	4	58.42	55.88	10.92	5.84	2.79
87914-4624	-----	-----	-----	-----	46	-----	4	58.42	55.88	12.25	7.00	2.96
87914-4615	-----	-----	-----	-----	46	-----	5	58.42	55.88	10.92	5.84	2.79
87914-4625	-----	-----	-----	-----	46	-----	5	58.42	55.88	12.25	7.00	2.96
87914-4616	-----	-----	-----	-----	46	-----	6	58.42	55.88	10.92	5.84	2.79
87914-4626	-----	-----	-----	-----	46	-----	6	58.42	55.88	12.25	7.00	2.96



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

MIGRATED TO NX 2017/03/17 EC NO: 114031 DRWN: FCSCC CHK'D: REV	2017/05/09 KHLIM	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		molex 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H PRODUCT CUSTOMER DRAWING SERIES: 87914 MATERIAL NUMBER: SEE TABLE CUSTOMER: GENERAL MARKET DOCUMENT NUMBER: SD-87914-013 DOC TYPE: PSD DOC PART: 000 SHEET NUMBER: 28 OF 45		
				MM		MM	NTS			
						DRWN BY	DATE		KCHO	2004/11/05
		4 PLACES	±	MM	INCH					
				CHK'D BY	DATE	PTLIM	2004/12/08			
3 PLACES	±									
				APPR BY	DATE	MLONG	2010/09/06			
2 PLACES	± 0.2									
		ANGULAR TOL = 3.0		DRAWING SIZE	THIRD ANGLE PROJECTION	A3				
1 PLACES	±	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS								
0 PLACES	±									

RELEASE STATUS	RELEASE DATE
----------------	--------------



PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-4811	-----	-----	-----	-----	48	-----	1	60.96	58.42	10.92	5.84	2.79
87914-4821	-----	-----	-----	-----	48	-----	1	60.96	58.42	12.25	7.00	2.96
87914-4812	-----	-----	-----	-----	48	-----	2	60.96	58.42	10.92	5.84	2.79
87914-4822	-----	-----	-----	-----	48	-----	2	60.96	58.42	12.25	7.00	2.96
87914-4813	-----	-----	-----	-----	48	-----	3	60.96	58.42	10.92	5.84	2.79
87914-4823	-----	-----	-----	-----	48	-----	3	60.96	58.42	12.25	7.00	2.96
87914-4814	-----	-----	-----	-----	48	-----	4	60.96	58.42	10.92	5.84	2.79
87914-4824	-----	-----	-----	-----	48	-----	4	60.96	58.42	12.25	7.00	2.96
87914-4815	-----	-----	-----	-----	48	-----	5	60.96	58.42	10.92	5.84	2.79
87914-4825	-----	-----	-----	-----	48	-----	5	60.96	58.42	12.25	7.00	2.96
87914-4816	-----	-----	-----	-----	48	-----	6	60.96	58.42	10.92	5.84	2.79
87914-4826	-----	-----	-----	-----	48	-----	6	60.96	58.42	12.25	7.00	2.96

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

MIGRATED TO NX EC NO: 114031 DRWN: FCSCC CHK'D: KHLIM REV APPR: KHLIM	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE						
			MM	INCH	MM	NTS					
	4 PLACES	±		±	DRWN BY	DATE		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H			
	3 PLACES	±		±	KCHO	2004/11/05					
	2 PLACES	± 0.2		±	CHK'D BY	DATE					
	1 PLACES	±		±	PTLIM	2004/12/08		PRODUCT CUSTOMER DRAWING			
0 PLACES	±		±	APPR BY	DATE						
ANGULAR TOL = 3.0		DRAWING SIZE		THIRD ANGLE PROJECTION		MLONG 2010/09/06	SERIES: 87914 MATERIAL NUMBER: SEE TABLE CUSTOMER: GENERAL MARKET				
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				A3							
RELEASE STATUS		RELEASE DATE		DOCUMENT NUMBER		DOC TYPE		DOC PART		SHEET NUMBER	
				SD-87914-013		PSD		000		29 OF 45	

PART NO FOR TRAY PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-5011	-----	-----	-----	-----	50	-----	1	63.50	60.96	10.92	5.84	2.79
87914-5021	-----	-----	-----	-----	50	-----	1	63.50	60.96	12.25	7.00	2.96
87914-5012	-----	-----	-----	-----	50	-----	2	63.50	60.96	10.92	5.84	2.79
87914-5022	-----	-----	-----	-----	50	-----	2	63.50	60.96	12.25	7.00	2.96
87914-5013	-----	-----	-----	-----	50	-----	3	63.50	60.96	10.92	5.84	2.79
87914-5023	-----	-----	-----	-----	50	-----	3	63.50	60.96	12.25	7.00	2.96
87914-5014	-----	-----	-----	-----	50	-----	4	63.50	60.96	10.92	5.84	2.79
87914-5024	-----	-----	-----	-----	50	-----	4	63.50	60.96	12.25	7.00	2.96
87914-5015	-----	-----	-----	-----	50	-----	5	63.50	60.96	10.92	5.84	2.79
87914-5025	-----	-----	-----	-----	50	-----	5	63.50	60.96	12.25	7.00	2.96
87914-5016	-----	-----	-----	-----	50	-----	6	63.50	60.96	10.92	5.84	2.79
87914-5026	-----	-----	-----	-----	50	-----	6	63.50	60.96	12.25	7.00	2.96


THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

MIGRATED TO NX EC NO: 114031 DRWN: FCSCC CHK'D: KHLIM REV APPR: KHLIM	2017/03/17		2017/05/09		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE				
							MM INCH		MM NTS				
	4 PLACES		±		±		KCHO		DATE		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H		
	3 PLACES		±		±		CHK'D BY		DATE				
	2 PLACES		± 0.2		±		PTLIM		DATE				
	1 PLACES		±		±		APPR BY		DATE		PRODUCT CUSTOMER DRAWING		
	0 PLACES		±		±		MLONG		DATE				
	ANGULAR TOL = 3.0						DRAWING SIZE		THIRD ANGLE PROJECTION		SERIES: 87914 MATERIAL NUMBER: SEE TABLE CUSTOMER: GENERAL MARKET		
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						A3						
	D18										DOCUMENT NUMBER: SD-87914-013 DOC TYPE: PSD DOC PART: 000 SHEET NUMBER: 30 OF 45		

RELEASE STATUS	RELEASE DATE
----------------	--------------

PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-5211	-----	-----	-----	-----	52	-----	1	66.04	63.50	10.92	5.84	2.79
87914-5221	-----	-----	-----	-----	52	-----	1	66.04	63.50	12.25	7.00	2.96
87914-5212	-----	-----	-----	-----	52	-----	2	66.04	63.50	10.92	5.84	2.79
87914-5222	-----	-----	-----	-----	52	-----	2	66.04	63.50	12.25	7.00	2.96
87914-5213	-----	-----	-----	-----	52	-----	3	66.04	63.50	10.92	5.84	2.79
87914-5223	-----	-----	-----	-----	52	-----	3	66.04	63.50	12.25	7.00	2.96
87914-5214	-----	-----	-----	-----	52	-----	4	66.04	63.50	10.92	5.84	2.79
87914-5224	-----	-----	-----	-----	52	-----	4	66.04	63.50	12.25	7.00	2.96
87914-5215	-----	-----	-----	-----	52	-----	5	66.04	63.50	10.92	5.84	2.79
87914-5225	-----	-----	-----	-----	52	-----	5	66.04	63.50	12.25	7.00	2.96
87914-5216	-----	-----	-----	-----	52	-----	6	66.04	63.50	10.92	5.84	2.79
87914-5226	-----	-----	-----	-----	52	-----	6	66.04	63.50	12.25	7.00	2.96



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

MIGRATED TO NX EC NO: 114031 DRWN: FCSCC CHK'D: KHLIM REV APPR: KHLIM	2017/03/17		2017/05/09		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		molex® 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H				
					MM INCH		MM NTS		NTS						
	4 PLACES ±		±		DRWN BY		DATE		KCHO		2004/11/05		PRODUCT CUSTOMER DRAWING SERIES: 87914 MATERIAL NUMBER: SEE TABLE CUSTOMER: GENERAL MARKET DOCUMENT NUMBER: SD-87914-013 DOC TYPE: PSD DOC PART: 000 SHEET NUMBER: 31 OF 45		
	3 PLACES ±		±		CHK'D BY		DATE		PTLIM		2004/12/08				
	2 PLACES ± 0.2		±		APPR BY		DATE		MLONG		2010/09/06				
	1 PLACES ±		±		DRAWING SIZE		THIRD ANGLE PROJECTION		A3						
	0 PLACES ±		±		ANGULAR TOL = 3.0		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS								

RELEASE STATUS	RELEASE DATE
----------------	--------------

PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-5411	-----	-----	-----	-----	54	-----	1	68.58	66.04	10.92	5.84	2.79
87914-5421	-----	-----	-----	-----	54	-----	1	68.58	66.04	12.25	7.00	2.96
87914-5412	-----	-----	-----	-----	54	-----	2	68.58	66.04	10.92	5.84	2.79
87914-5422	-----	-----	-----	-----	54	-----	2	68.58	66.04	12.25	7.00	2.96
87914-5413	-----	-----	-----	-----	54	-----	3	68.58	66.04	10.92	5.84	2.79
87914-5423	-----	-----	-----	-----	54	-----	3	68.58	66.04	12.25	7.00	2.96
87914-5414	-----	-----	-----	-----	54	-----	4	68.58	66.04	10.92	5.84	2.79
87914-5424	-----	-----	-----	-----	54	-----	4	68.58	66.04	12.25	7.00	2.96
87914-5415	-----	-----	-----	-----	54	-----	5	68.58	66.04	10.92	5.84	2.79
87914-5425	-----	-----	-----	-----	54	-----	5	68.58	66.04	12.25	7.00	2.96
87914-5416	-----	-----	-----	-----	54	-----	6	68.58	66.04	10.92	5.84	2.79
87914-5426	-----	-----	-----	-----	54	-----	6	68.58	66.04	12.25	7.00	2.96



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

MIGRATED TO NX EC NO: 114031 DRWN: FCSCC CHK'D: KHLIM REV APPR: 2017/03/17 2017/05/09	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE				
			MM	INCH	MM	NTS			
	4 PLACES	±	±	DRWN BY	DATE		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H		
	3 PLACES	±	±	KCHO	2004/11/05				
	2 PLACES	±	0.2	CHK'D BY	DATE				
	1 PLACES	±	±	PTLIM	2004/12/08				
	0 PLACES	±	±	APPR BY	DATE		PRODUCT CUSTOMER DRAWING		
	ANGULAR TOL = 3.0			MLONG	2010/09/06		SERIES	MATERIAL NUMBER	CUSTOMER
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			DRAWING SIZE	THIRD ANGLE PROJECTION		87914	SEE TABLE	GENERAL MARKET	
D18			A3			DOCUMENT NUMBER	DOC TYPE	DOC PART	SHEET NUMBER
						SD-87914-013	PSD	000	32 OF 45

RELEASE STATUS	RELEASE DATE
----------------	--------------

PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-5611	-----	-----	-----	-----	56	-----	1	71.12	68.58	10.92	5.84	2.79
87914-5621	-----	-----	-----	-----	56	-----	1	71.12	68.58	12.25	7.00	2.96
87914-5612	-----	-----	-----	-----	56	-----	2	71.12	68.58	10.92	5.84	2.79
87914-5622	-----	-----	-----	-----	56	-----	2	71.12	68.58	12.25	7.00	2.96
87914-5613	-----	-----	-----	-----	56	-----	3	71.12	68.58	10.92	5.84	2.79
87914-5623	-----	-----	-----	-----	56	-----	3	71.12	68.58	12.25	7.00	2.96
87914-5614	-----	-----	-----	-----	56	-----	4	71.12	68.58	10.92	5.84	2.79
87914-5624	-----	-----	-----	-----	56	-----	4	71.12	68.58	12.25	7.00	2.96
87914-5615	-----	-----	-----	-----	56	-----	5	71.12	68.58	10.92	5.84	2.79
87914-5625	-----	-----	-----	-----	56	-----	5	71.12	68.58	12.25	7.00	2.96
87914-5616	-----	-----	-----	-----	56	-----	6	71.12	68.58	10.92	5.84	2.79
87914-5626	-----	-----	-----	-----	56	-----	6	71.12	68.58	12.25	7.00	2.96

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION



MIGRATED TO NX EC NO: 114031 DRWN: FCSCC CHK'D: KHLIM REV APPR: KHLIM	2017/03/17		2017/05/09		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE				
							MM INCH		MM NTS				
	4 PLACES ±		±		KCHO		DATE		2004/11/05		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H		
	3 PLACES ±		±		CHK'D BY		DATE		2004/12/08				
	2 PLACES ± 0.2		±		PTLIM		DATE		2010/09/06				
	1 PLACES ±		±		APPR BY		DATE				PRODUCT CUSTOMER DRAWING		
0 PLACES ±		±		MLONG		DATE							
ANGULAR TOL = 3.0				DRAWING SIZE		THIRD ANGLE PROJECTION		A3					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS													

SERIES	MATERIAL NUMBER	CUSTOMER	
87914	SEE TABLE	GENERAL MARKET	
DOCUMENT NUMBER	DOC TYPE	DOC PART	SHEET NUMBER
SD-87914-013	PSD	000	33 OF 45

RELEASE STATUS	RELEASE DATE

PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-5811	-----	-----	-----	-----	58	-----	1	73.66	71.12	10.92	5.84	2.79
87914-5821	-----	-----	-----	-----	58	-----	1	73.66	71.12	12.25	7.00	2.96
87914-5812	-----	-----	-----	-----	58	-----	2	73.66	71.12	10.92	5.84	2.79
87914-5822	-----	-----	-----	-----	58	-----	2	73.66	71.12	12.25	7.00	2.96
87914-5813	-----	-----	-----	-----	58	-----	3	73.66	71.12	10.92	5.84	2.79
87914-5823	-----	-----	-----	-----	58	-----	3	73.66	71.12	12.25	7.00	2.96
87914-5814	-----	-----	-----	-----	58	-----	4	73.66	71.12	10.92	5.84	2.79
87914-5824	-----	-----	-----	-----	58	-----	4	73.66	71.12	12.25	7.00	2.96
87914-5815	-----	-----	-----	-----	58	-----	5	73.66	71.12	10.92	5.84	2.79
87914-5825	-----	-----	-----	-----	58	-----	5	73.66	71.12	12.25	7.00	2.96
87914-5816	-----	-----	-----	-----	58	-----	6	73.66	71.12	10.92	5.84	2.79
87914-5826	-----	-----	-----	-----	58	-----	6	73.66	71.12	12.25	7.00	2.96

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION



MIGRATED TO NX EC NO: 114031 DRWN: FCSCC CHK'D: KHLIM 2017/03/17 2017/05/09	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H PRODUCT CUSTOMER DRAWING
			MM	INCH	MM	NTS	
	4 PLACES	±			DRWN BY	DATE	
	3 PLACES	±			KCHO	2004/11/05	
	2 PLACES	± 0.2			CHK'D BY	DATE	
	1 PLACES	±			PTLIM	2004/12/08	
	0 PLACES	±			APPR BY	DATE	
					MLONG	2010/09/06	
			ANGULAR TOL = 3.0		DRAWING SIZE	THIRD ANGLE PROJECTION	
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		A3		

SERIES	MATERIAL NUMBER	CUSTOMER	
87914	SEE TABLE	GENERAL MARKET	
DOCUMENT NUMBER	DOC TYPE	DOC PART	SHEET NUMBER
SD-87914-013	PSD	000	34 OF 45

RELEASE STATUS	RELEASE DATE
----------------	--------------

PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-6011	-----	-----	-----	-----	60	-----	1	76.20	73.66	10.92	5.84	2.79
87914-6021	-----	-----	-----	-----	60	-----	1	76.20	73.66	12.25	7.00	2.96
87914-6012	-----	-----	-----	-----	60	-----	2	76.20	73.66	10.92	5.84	2.79
87914-6022	-----	-----	-----	-----	60	-----	2	76.20	73.66	12.25	7.00	2.96
87914-6013	-----	-----	-----	-----	60	-----	3	76.20	73.66	10.92	5.84	2.79
87914-6023	-----	-----	-----	-----	60	-----	3	76.20	73.66	12.25	7.00	2.96
87914-6014	-----	-----	-----	-----	60	-----	4	76.20	73.66	10.92	5.84	2.79
87914-6024	-----	-----	-----	-----	60	-----	4	76.20	73.66	12.25	7.00	2.96
87914-6015	-----	-----	-----	-----	60	-----	5	76.20	73.66	10.92	5.84	2.79
87914-6025	-----	-----	-----	-----	60	-----	5	76.20	73.66	12.25	7.00	2.96
87914-6016	-----	-----	-----	-----	60	-----	6	76.20	73.66	10.92	5.84	2.79
87914-6026	-----	-----	-----	-----	60	-----	6	76.20	73.66	12.25	7.00	2.96



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

MIGRATED TO NX EC NO: 114031 DRWN: FCSCC CHK'D: KHLIM REV APPR: KHLIM	2017/03/17		2017/05/09		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE						
							MM INCH		MM NTS						
	4 PLACES		±		±		KCHO		DATE		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H PRODUCT CUSTOMER DRAWING				
	3 PLACES		±		±		PTLIM		DATE						
	2 PLACES		± 0.2		±		MLONG		DATE						
	1 PLACES		±		±										
	0 PLACES		±		±										
	ANGULAR TOL = 3.0					DRAWING SIZE		THIRD ANGLE PROJECTION		SERIES		MATERIAL NUMBER		CUSTOMER	
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS					A3				87914		SEE TABLE		GENERAL MARKET	
										DOCUMENT NUMBER		DOC TYPE		DOC PART SHEET NUMBER	
									SD-87914-013		PSD		000 35 OF 45		

RELEASE STATUS	RELEASE DATE
----------------	--------------

PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-6211	-----	-----	-----	-----	62	-----	1	78.74	76.20	10.92	5.84	2.79
87914-6221	-----	-----	-----	-----	62	-----	1	78.74	76.20	12.25	7.00	2.96
87914-6212	-----	-----	-----	-----	62	-----	2	78.74	76.20	10.92	5.84	2.79
87914-6222	-----	-----	-----	-----	62	-----	2	78.74	76.20	12.25	7.00	2.96
87914-6213	-----	-----	-----	-----	62	-----	3	78.74	76.20	10.92	5.84	2.79
87914-6223	-----	-----	-----	-----	62	-----	3	78.74	76.20	12.25	7.00	2.96
87914-6214	-----	-----	-----	-----	62	-----	4	78.74	76.20	10.92	5.84	2.79
87914-6224	-----	-----	-----	-----	62	-----	4	78.74	76.20	12.25	7.00	2.96
87914-6215	-----	-----	-----	-----	62	-----	5	78.74	76.20	10.92	5.84	2.79
87914-6225	-----	-----	-----	-----	62	-----	5	78.74	76.20	12.25	7.00	2.96
87914-6216	-----	-----	-----	-----	62	-----	6	78.74	76.20	10.92	5.84	2.79
87914-6226	-----	-----	-----	-----	62	-----	6	78.74	76.20	12.25	7.00	2.96


THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION


MIGRATED TO NX EC NO: 114031 DRWN: FCSCC CHK'D: KHLIM APPR: KHLIM 2017/03/17 2017/05/09	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H PRODUCT CUSTOMER DRAWING
			MM	INCH	NTS		
	4 PLACES	±	DRWN BY	DATE			
	3 PLACES	±	KCHO	2004/11/05			
	2 PLACES	± 0.2	CHK'D BY	DATE			
	1 PLACES	±	PTLIM	2004/12/08			
	0 PLACES	±	APPR BY	DATE			
			MLONG	2010/09/06			
ANGULAR TOL = 3.0			DRAWING SIZE	THIRD ANGLE PROJECTION			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			A3				
SERIES		MATERIAL NUMBER		CUSTOMER			
87914		SEE TABLE		GENERAL MARKET			
DOCUMENT NUMBER			DOC TYPE	DOC PART	SHEET NUMBER		
SD-87914-013			PSD	000	36 OF 45		

RELEASE STATUS	RELEASE DATE
----------------	--------------

PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-6411	-----	-----	-----	-----	64	-----	1	81.28	78.74	10.92	5.84	2.79
87914-6421	-----	-----	-----	-----	64	-----	1	81.28	78.74	12.25	7.00	2.96
87914-6412	-----	-----	-----	-----	64	-----	2	81.28	78.74	10.92	5.84	2.79
87914-6422	-----	-----	-----	-----	64	-----	2	81.28	78.74	12.25	7.00	2.96
87914-6413	-----	-----	-----	-----	64	-----	3	81.28	78.74	10.92	5.84	2.79
87914-6423	-----	-----	-----	-----	64	-----	3	81.28	78.74	12.25	7.00	2.96
87914-6414	-----	-----	-----	-----	64	-----	4	81.28	78.74	10.92	5.84	2.79
87914-6424	-----	-----	-----	-----	64	-----	4	81.28	78.74	12.25	7.00	2.96
87914-6415	-----	-----	-----	-----	64	-----	5	81.28	78.74	10.92	5.84	2.79
87914-6425	-----	-----	-----	-----	64	-----	5	81.28	78.74	12.25	7.00	2.96
87914-6416	-----	-----	-----	-----	64	-----	6	81.28	78.74	10.92	5.84	2.79
87914-6426	-----	-----	-----	-----	64	-----	6	81.28	78.74	12.25	7.00	2.96

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

MIGRATED TO NX EC NO: 114031 DRWN: FCSCC CHK'D: KHLIM APPR: KHLIM 2017/03/17 2017/05/09	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE	
			MM	INCH	MM	NTS
	4 PLACES	±			DRWN BY	DATE
	3 PLACES	±			KCHO	2004/11/05
	2 PLACES	± 0.2			CHK'D BY	DATE
	1 PLACES	±			PTLIM	2004/12/08
	0 PLACES	±			APPR BY	DATE
ANGULAR TOL = 3.0		DRAWING SIZE		THIRD ANGLE PROJECTION		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		A3				



2.54MM PITCH
DUAL ROW HEADER SINGLE WAFER, T/H



PRODUCT CUSTOMER DRAWING

SERIES	MATERIAL NUMBER	CUSTOMER
87914	SEE TABLE	GENERAL MARKET
DOCUMENT NUMBER		DOC TYPE
SD-87914-013		PSD
DOC PART	SHEET NUMBER	
000	37 OF 45	

RELEASE STATUS	RELEASE DATE
----------------	--------------

PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-6611	-----	-----	-----	-----	66	-----	1	83.82	81.28	10.92	5.84	2.79
87914-6621	-----	-----	-----	-----	66	-----	1	83.82	81.28	12.25	7.00	2.96
87914-6612	-----	-----	-----	-----	66	-----	2	83.82	81.28	10.92	5.84	2.79
87914-6622	-----	-----	-----	-----	66	-----	2	83.82	81.28	12.25	7.00	2.96
87914-6613	-----	-----	-----	-----	66	-----	3	83.82	81.28	10.92	5.84	2.79
87914-6623	-----	-----	-----	-----	66	-----	3	83.82	81.28	12.25	7.00	2.96
87914-6614	-----	-----	-----	-----	66	-----	4	83.82	81.28	10.92	5.84	2.79
87914-6624	-----	-----	-----	-----	66	-----	4	83.82	81.28	12.25	7.00	2.96
87914-6615	-----	-----	-----	-----	66	-----	5	83.82	81.28	10.92	5.84	2.79
87914-6625	-----	-----	-----	-----	66	-----	5	83.82	81.28	12.25	7.00	2.96
87914-6616	-----	-----	-----	-----	66	-----	6	83.82	81.28	10.92	5.84	2.79
87914-6626	-----	-----	-----	-----	66	-----	6	83.82	81.28	12.25	7.00	2.96



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

MIGRATED TO NX EC NO: 114031 DRWN: FCSCC CHK'D: KHLIM REV APPR: 2017/03/17 2017/05/09	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE						
			MM	INCH	MM	NTS					
	4 PLACES	±		±	DRWN BY	DATE	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H				
	3 PLACES	±		±	KCHO	2004/11/05					
	2 PLACES	± 0.2		±	CHK'D BY	DATE					
	1 PLACES	±		±	PTLIM	2004/12/08					
	0 PLACES	±		±	APPR BY	DATE	PRODUCT CUSTOMER DRAWING				
					MLONG	2010/09/06					
	ANGULAR TOL = 3.0				DRAWING SIZE	THIRD ANGLE PROJECTION	SERIES	MATERIAL NUMBER	CUSTOMER		
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				A3		87914	SEE TABLE	GENERAL MARKET		
						DOCUMENT NUMBER	DOC TYPE	DOC PART	SHEET NUMBER		
						SD-87914-013	PSD	000	38 OF 45		

RELEASE STATUS	RELEASE DATE
----------------	--------------

9		8		7		6		5		4		3		2		1	
PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION									
								A	B	F	M	P					
87914-6811	-----	-----	-----	-----	68	-----	1	86.36	83.82	10.92	5.84	2.79					
87914-6821	-----	-----	-----	-----	68	-----	1	86.36	83.82	12.25	7.00	2.96					
87914-6812	-----	-----	-----	-----	68	-----	2	86.36	83.82	10.92	5.84	2.79					
87914-6822	-----	-----	-----	-----	68	-----	2	86.36	83.82	12.25	7.00	2.96					
87914-6813	-----	-----	-----	-----	68	-----	3	86.36	83.82	10.92	5.84	2.79					
87914-6823	-----	-----	-----	-----	68	-----	3	86.36	83.82	12.25	7.00	2.96					
87914-6814	-----	-----	-----	-----	68	-----	4	86.36	83.82	10.92	5.84	2.79					
87914-6824	-----	-----	-----	-----	68	-----	4	86.36	83.82	12.25	7.00	2.96					
87914-6815	-----	-----	-----	-----	68	-----	5	86.36	83.82	10.92	5.84	2.79					
87914-6825	-----	-----	-----	-----	68	-----	5	86.36	83.82	12.25	7.00	2.96					
87914-6816	-----	-----	-----	-----	68	-----	6	86.36	83.82	10.92	5.84	2.79					
87914-6826	-----	-----	-----	-----	68	-----	6	86.36	83.82	12.25	7.00	2.96					


THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

MIGRATED TO NX 2017/03/17 2017/05/09 EC NO: 114031 DRWN: FCSCC CHK'D: APP: KHLIM	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H						
			MM	INCH	MM	NTS							
	4 PLACES	±	±	DRWN BY	DATE	KCHO					2004/11/05		
	3 PLACES	±	±	CHK'D BY	DATE	PTLIM	2004/12/08						
	2 PLACES	±	0.2	±	APPR BY	DATE	MLONG	2010/09/06					
1 PLACES	±	±	±	DRAWING SIZE		THIRD ANGLE PROJECTION		SERIES		MATERIAL NUMBER		CUSTOMER	
0 PLACES	±	±	±	A3				87914	SEE TABLE	GENERAL MARKET			
ANGULAR TOL = 3.0			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS					DOCUMENT NUMBER		DOC TYPE	DOC PART	SHEET NUMBER	
								SD-87914-013		PSD	000	39 OF 45	

RELEASE STATUS	RELEASE DATE																
----------------	--------------	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--	--

PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-7011	-----	-----	-----	-----	70	-----	1	88.90	86.36	10.92	5.84	2.79
87914-7021	-----	-----	-----	-----	70	-----	1	88.90	86.36	12.25	7.00	2.96
87914-7012	-----	-----	-----	-----	70	-----	2	88.90	86.36	10.92	5.84	2.79
87914-7022	-----	-----	-----	-----	70	-----	2	88.90	86.36	12.25	7.00	2.96
87914-7013	-----	-----	-----	-----	70	-----	3	88.90	86.36	10.92	5.84	2.79
87914-7023	-----	-----	-----	-----	70	-----	3	88.90	86.36	12.25	7.00	2.96
87914-7014	-----	-----	-----	-----	70	-----	4	88.90	86.36	10.92	5.84	2.79
87914-7024	-----	-----	-----	-----	70	-----	4	88.90	86.36	12.25	7.00	2.96
87914-7015	-----	-----	-----	-----	70	-----	5	88.90	86.36	10.92	5.84	2.79
87914-7025	-----	-----	-----	-----	70	-----	5	88.90	86.36	12.25	7.00	2.96
87914-7016	-----	-----	-----	-----	70	-----	6	88.90	86.36	10.92	5.84	2.79
87914-7026	-----	-----	-----	-----	70	-----	6	88.90	86.36	12.25	7.00	2.96



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

MIGRATED TO NX EC NO: 114031 DRWN: FCSCC CHK'D: KHLIM REV APPR: 2017/03/17 2017/05/09	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		molex 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H	
			MM	INCH	MM	NTS		
	4 PLACES	±		±	DRWN BY	DATE		PRODUCT CUSTOMER DRAWING
	3 PLACES	±		±	KCHO	2004/11/05		
	2 PLACES	± 0.2		±	CHK'D BY	DATE		
1 PLACES	±		±	PTLIM	2004/12/08			
0 PLACES	±		±	APPR BY	DATE			
ANGULAR TOL = 3.0		DRAWING SIZE		THIRD ANGLE PROJECTION				
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		A3						

RELEASE STATUS	RELEASE DATE
----------------	--------------

PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-7211	-----	-----	-----	-----	72	-----	1	91.44	88.90	10.92	5.84	2.79
87914-7221	-----	-----	-----	-----	72	-----	1	91.44	88.90	12.25	7.00	2.96
87914-7212	-----	-----	-----	-----	72	-----	2	91.44	88.90	10.92	5.84	2.79
87914-7222	-----	-----	-----	-----	72	-----	2	91.44	88.90	12.25	7.00	2.96
87914-7213	-----	-----	-----	-----	72	-----	3	91.44	88.90	10.92	5.84	2.79
87914-7223	-----	-----	-----	-----	72	-----	3	91.44	88.90	12.25	7.00	2.96
87914-7214	-----	-----	-----	-----	72	-----	4	91.44	88.90	10.92	5.84	2.79
87914-7224	-----	-----	-----	-----	72	-----	4	91.44	88.90	12.25	7.00	2.96
87914-7215	-----	-----	-----	-----	72	-----	5	91.44	88.90	10.92	5.84	2.79
87914-7225	-----	-----	-----	-----	72	-----	5	91.44	88.90	12.25	7.00	2.96
87914-7216	-----	-----	-----	-----	72	-----	6	91.44	88.90	10.92	5.84	2.79
87914-7226	-----	-----	-----	-----	72	-----	6	91.44	88.90	12.25	7.00	2.96



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

MIGRATED TO NX 2017/03/17 2017/05/09 EC NO: 114031 DRWN: FCSCC CHK'D: APP: KHLIM	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H	
			MM	INCH	MM	NTS		
	4 PLACES	±		±	DRWN BY	DATE		KCHO 2004/11/05
	3 PLACES	±		±	CHK'D BY	DATE		
	2 PLACES	± 0.2		±	PTLIM	2004/12/08		
	1 PLACES	±		±	APPR BY	DATE		MLONG 2010/09/06
0 PLACES	±		±	DRAWING SIZE	THIRD ANGLE PROJECTION			
ANGULAR TOL = 3.0				A3				
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS							SERIES: 87914 MATERIAL NUMBER: SEE TABLE CUSTOMER: GENERAL MARKET	
DOCUMENT NUMBER: SD-87914-013		DOC TYPE: PSD		DOC PART: 000		SHEET NUMBER: 41 OF 45		

RELEASE STATUS	RELEASE DATE
----------------	--------------



	9	8	7	6	5	4	3	2	1				
	PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
									A	B	F	M	P
	87914-7411	-----	-----	-----	-----	74	-----	1	93.98	91.44	10.92	5.84	2.79
	87914-7421	-----	-----	-----	-----	74	-----	1	93.98	91.44	12.25	7.00	2.96
E	87914-7412	-----	-----	-----	-----	74	-----	2	93.98	91.44	10.92	5.84	2.79
	87914-7422	-----	-----	-----	-----	74	-----	2	93.98	91.44	12.25	7.00	2.96
	87914-7413	-----	-----	-----	-----	74	-----	3	93.98	91.44	10.92	5.84	2.79
	87914-7423	-----	-----	-----	-----	74	-----	3	93.98	91.44	12.25	7.00	2.96
	87914-7414	-----	-----	-----	-----	74	-----	4	93.98	91.44	10.92	5.84	2.79
	87914-7424	-----	-----	-----	-----	74	-----	4	93.98	91.44	12.25	7.00	2.96
	87914-7415	-----	-----	-----	-----	74	-----	5	93.98	91.44	10.92	5.84	2.79
	87914-7425	-----	-----	-----	-----	74	-----	5	93.98	91.44	12.25	7.00	2.96
	87914-7416	-----	-----	-----	-----	74	-----	6	93.98	91.44	10.92	5.84	2.79
	87914-7426	-----	-----	-----	-----	74	-----	6	93.98	91.44	12.25	7.00	2.96
D													
C													
B													
A													

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

MIGRATED TO NX EC NO: 114031 DRWN: FCSCC CHK'D: KHLIM APPR: KHLIM REV:	2017/03/17		2017/05/09		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H PRODUCT CUSTOMER DRAWING								
							MM INCH		MM NTS										
	4 PLACES ±		±				DRWN BY		DATE										
	3 PLACES ±		±				KCHO		2004/11/05										
	2 PLACES ± 0.2		±				CHK'D BY		DATE										
	1 PLACES ±		±				PTLIM		2004/12/08										
	0 PLACES ±		±				APPR BY		DATE										
							MLONG		2010/09/06										
					ANGULAR TOL = 3.0		DRAWING SIZE		THIRD ANGLE PROJECTION										
					DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		A3												
D18						87914			SEE TABLE			GENERAL MARKET							
RELEASE STATUS						RELEASE DATE						DOCUMENT NUMBER			DOC TYPE		DOC PART	SHEET NUMBER	
												SD-87914-013			PSD		000	42 OF 45	

PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-7611	-----	-----	-----	-----	76	-----	1	96.52	93.98	10.92	5.84	2.79
87914-7621	-----	-----	-----	-----	76	-----	1	96.52	93.98	12.25	7.00	2.96
87914-7612	-----	-----	-----	-----	76	-----	2	96.52	93.98	10.92	5.84	2.79
87914-7622	-----	-----	-----	-----	76	-----	2	96.52	93.98	12.25	7.00	2.96
87914-7613	-----	-----	-----	-----	76	-----	3	96.52	93.98	10.92	5.84	2.79
87914-7623	-----	-----	-----	-----	76	-----	3	96.52	93.98	12.25	7.00	2.96
87914-7614	-----	-----	-----	-----	76	-----	4	96.52	93.98	10.92	5.84	2.79
87914-7624	-----	-----	-----	-----	76	-----	4	96.52	93.98	12.25	7.00	2.96
87914-7615	-----	-----	-----	-----	76	-----	5	96.52	93.98	10.92	5.84	2.79
87914-7625	-----	-----	-----	-----	76	-----	5	96.52	93.98	12.25	7.00	2.96
87914-7616	-----	-----	-----	-----	76	-----	6	96.52	93.98	10.92	5.84	2.79
87914-7626	-----	-----	-----	-----	76	-----	6	96.52	93.98	12.25	7.00	2.96

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION


MIGRATED TO NX 2017/03/17 2017/05/09 EC NO: 114031 DRWN: FCSCC CHK'D: KHLIM REV APPR: KHLIM	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		 2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H PRODUCT CUSTOMER DRAWING
			MM	INCH	MM	NTS	
	4 PLACES	±			DRWN BY	DATE	
	3 PLACES	±			KCHO	2004/11/05	
	2 PLACES	± 0.2			CHK'D BY	DATE	
	1 PLACES	±			PTLIM	2004/12/08	
	0 PLACES	±			APPR BY	DATE	
					MLONG	2010/09/06	
	ANGULAR TOL = 3.0		DRAWING SIZE	THIRD ANGLE PROJECTION			
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		A3				

SERIES	MATERIAL NUMBER	CUSTOMER	
87914	SEE TABLE	GENERAL MARKET	
DOCUMENT NUMBER	DOC TYPE	DOC PART	SHEET NUMBER
SD-87914-013	PSD	000	43 OF 45

RELEASE STATUS	RELEASE DATE
----------------	--------------

PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-7811	-----	-----	-----	-----	78	-----	1	99.06	96.52	10.92	5.84	2.79
87914-7821	-----	-----	-----	-----	78	-----	1	99.06	96.52	12.25	7.00	2.96
87914-7812	-----	-----	-----	-----	78	-----	2	99.06	96.52	10.92	5.84	2.79
87914-7822	-----	-----	-----	-----	78	-----	2	99.06	96.52	12.25	7.00	2.96
87914-7813	-----	-----	-----	-----	78	-----	3	99.06	96.52	10.92	5.84	2.79
87914-7823	-----	-----	-----	-----	78	-----	3	99.06	96.52	12.25	7.00	2.96
87914-7814	-----	-----	-----	-----	78	-----	4	99.06	96.52	10.92	5.84	2.79
87914-7824	-----	-----	-----	-----	78	-----	4	99.06	96.52	12.25	7.00	2.96
87914-7815	-----	-----	-----	-----	78	-----	5	99.06	96.52	10.92	5.84	2.79
87914-7825	-----	-----	-----	-----	78	-----	5	99.06	96.52	12.25	7.00	2.96
87914-7816	-----	-----	-----	-----	78	-----	6	99.06	96.52	10.92	5.84	2.79
87914-7826	-----	-----	-----	-----	78	-----	6	99.06	96.52	12.25	7.00	2.96

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

MIGRATED TO NX EC NO: 114031 DRWN: FCSCC CHK'D: REV APPR: KHLIM	2017/03/17	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE				
	2017/05/09	MM	INCH	MM	NTS					
			4 PLACES ±		DRWN BY	DATE	2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H			
			3 PLACES ±		KCHO	2004/11/05				
			2 PLACES ± 0.2		CHK'D BY	DATE				
			1 PLACES ±		PTLIM	2004/12/08	PRODUCT CUSTOMER DRAWING			
			0 PLACES ±		APPR BY	DATE				
					MLONG	2010/09/06	SERIES	MATERIAL NUMBER	CUSTOMER	
					ANGULAR TOL = 3.0	DRAWING SIZE	THIRD ANGLE PROJECTION	87914	SEE TABLE	GENERAL MARKET
					DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	A3				
						DOCUMENT NUMBER	DOC TYPE	DOC PART	SHEET NUMBER	
						SD-87914-013	PSD	000	44 OF 45	

RELEASE STATUS	RELEASE DATE
----------------	--------------

PART NO FOR BULK PACKAGING	PART NO. FOR TUBE WITHOUT CAP PACKAGING	PART NO. FOR TUBE WITH CAP PACKAGING	PART NO. FOR TAPE & REEL WITHOUT CAP PACKAGING	PART NO. FOR TAPE & REEL WITH CAP PACKAGING	CKT SIZE	VOID POSITION	PLATING TYPE	DIMENSION				
								A	B	F	M	P
87914-8011	-----	-----	-----	-----	80	-----	1	101.60	99.06	10.92	5.84	2.79
87914-8021	-----	-----	-----	-----	80	-----	1	101.60	99.06	12.25	7.00	2.96
87914-8012	-----	-----	-----	-----	80	-----	2	101.60	99.06	10.92	5.84	2.79
87914-8022	-----	-----	-----	-----	80	-----	2	101.60	99.06	12.25	7.00	2.96
87914-8013	-----	-----	-----	-----	80	-----	3	101.60	99.06	10.92	5.84	2.79
87914-8023	-----	-----	-----	-----	80	-----	3	101.60	99.06	12.25	7.00	2.96
87914-8014	-----	-----	-----	-----	80	-----	4	101.60	99.06	10.92	5.84	2.79
87914-8024	-----	-----	-----	-----	80	-----	4	101.60	99.06	12.25	7.00	2.96
87914-8015	-----	-----	-----	-----	80	-----	5	101.60	99.06	10.92	5.84	2.79
87914-8025	-----	-----	-----	-----	80	-----	5	101.60	99.06	12.25	7.00	2.96
87914-8016	-----	-----	-----	-----	80	-----	6	101.60	99.06	10.92	5.84	2.79
87914-8026	-----	-----	-----	-----	80	-----	6	101.60	99.06	12.25	7.00	2.96

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

MIGRATED TO NX EC NO: 114031 DRWN: FCSCC CHK'D: REV APPR: KHLIM	2017/03/17	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		molex®				
	2017/05/09	MM	INCH	MM	INCH	MM	NTS					
	4 PLACES	±	±	DRWN BY		DATE		2.54MM PITCH DUAL ROW HEADER SINGLE WAFER, T/H				
	3 PLACES	±	±	KCHO		2004/11/05						
	2 PLACES	± 0.2	±	CHK'D BY		DATE						
	1 PLACES	±	±	PTLIM		2004/12/08		PRODUCT CUSTOMER DRAWING				
	0 PLACES	±	±	APPR BY		DATE						
	ANGULAR TOL = 3.0			MLONG		2010/09/06		SERIES	MATERIAL NUMBER	CUSTOMER		
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			DRAWING SIZE		THIRD ANGLE PROJECTION		87914	SEE TABLE	GENERAL MARKET		
				A3				DOCUMENT NUMBER		DOC TYPE	DOC PART	SHEET NUMBER
							SD-87914-013		PSD	000	45 OF 45	

RELEASE STATUS	RELEASE DATE
----------------	--------------