





宏聚电子五金制品有限公司

HONGJU ELECTRONIC & METAL PRODUCTS CO.,LTD

FH1



Fuse holder for overload protection



Rating: 10A 250VAC (UL,CUL)

Fuse: Ø5.0x20mm



Cap: Bayonet type

Operating Temperature: -10°C ~ +70°C



MATERIAL:


Housing: PC, UL rated 94V2 min

Bayonet: PC, UL rated 94V2 min

Terminal: Brass, silver or tin plated

CE  US E240653

P.C.B.LAYOUT



公差 TOLERANCES		.X±0.3	.XX±0.15	角度 ANGLE ±1°		单位 DIMENSION UNIT		mm.
版本 VERSION		A0	比例尺 SCALE		NONE	品名 TITLE		图号 DRAWING NO
核准 APPROVED BY		Xinchao_Lee	核对 CHECKED BY		Gokey_Guo	日期 DATE		2009.02.26
日期 DATE		2009.02.26	ECN NO.		N/A	绘图 DRAWN BY		Gokey_Guo
变更说明 CHANGE DESCRIPTION		New Issue						
版本 VER.		A0						

FH1-206Z

FH1-206Z_A0