

SPECIFICATIONS

Rated(额定参数): 300V,15A
 Dielectric strength(抗电强度): AC2000V/1 Minute
 Insulation Resistance(绝缘电阻):1000MΩ Min
 Contact Resistance(接触电阻):20mΩ Max
 Screw Torque(扭矩): 0.5Nm (4.4l.b.in)
 Wire Range(线径):1.4~2.2AWG
 Temp. range(操作温度): -40°C~+105°C
 MAX Soldering(瞬时温度):+250°C,5s




Housing Material(塑件): PA66 (UL94 V-0)
 Contact(端子): Brass, Tin plating(黄铜镀锡)
 Screw (螺丝): M3.0, Steel, Ni plating(钢, 镀锌)

| PITCH RANGE | | NOMINAL DIMENSION RANGE | | | | | |
|-------------|-------|-------------------------|-------|-------|-------|-------|-------|
| IN MM | | IN MM | | IN MM | | IN MM | |
| OVER | TO | OVER | TO | OVER | TO | OVER | TO |
| 6 | 10 | 30 | 60 | 100 | 150 | 150 | 150 |
| 10 | 24 | 60 | 100 | 150 | 150 | 150 | 150 |
| ±0.10 | ±0.15 | ±0.25 | ±0.30 | ±0.30 | ±0.50 | ±0.70 | ±1.00 |

Ordering Information

JL25C - 762 XX B X 1

Pitch 762=7.62PH
 No.of pins 2P~26P
 Housing Color
 B=Black
 G=Green
 U=Blue
 R=Red
 W=White
 Y=Yellow
 O=Orange
 F=Grey
 Packing
 O=Pe bog
 T=Tube
 A=Tray



1.25±0.1

| | | | | | | | | | | | | | |
|-----------|--|---------|--|-----|--|----------|--|--------|--|-----|--|--------------------------------|--|
| OPERATION | | DRAW | | BEN | | 17.01.04 | | SCALE | | FIT | | PART NO. | |
| ±0.30 | | CHECK | | | | | | mm | | A4 | | JL25C-762XXBX1 | |
| ±0.20 | | CHECK | | | | | | SIZE | | 1/1 | | 7.62mm Barrier Terminal Blocks | |
| ±0.10 | | APPROVE | | | | | | SHEET | | 1/1 | | | |
| ±3° | | | | | | | | PROU. | | 1/1 | | | |
| CHANGE | | | | | | | | TITLE: | | | | | |
| DIM | | | | | | | | PRU. | | | | | |
| TOL | | | | | | | | PRU. | | | | | |

JIN 深圳市锦凌电子有限公司
 SHENZHEN JINLING ELECTRONIC CO.,LTD
 Tel: 86-755-2997-5806/5802 Fax: 86-755-2997-5992