



Recommended P.C.B Layout

MATERIAL

Insulator : NYLON 6T or 9T
 Contact Pin : Brass

SPECIFICATION

Current Rate : 3 AMP
 Insulation Resistance : 5000MΩMin. at DC 500V
 Contact Resistance : 20mΩMax. at DC 100mA
 Dielectric Voltage : AC 500V for one minute
 Operation Temperature : -40°C to + 105°C

510-9 0- 14 G B 00
 1 2 3 4 5

1. 5: Normal Parts
- 7: Green Product
- 9: Green Product High Temp
2. No. of contacts
3. G: Gold flash
- S: Selective
- T: Tin plated
4. B: Black Insulator
5. Pinrex internal code.

				TOLERANCE .0 =±.30 .00 =±.20 .000 =±.XXX .0000=±. ANG.=±3'		 UNITS : mm		OLD PART NO. BH1S-14GB		TITLE BOX HEADER 2.54*2.54mm, STRAIGHT TYPE		頻銳科技股份有限公司 PINREX TECHNOLOGY CORP.	
				SCALE	SIZE	SHEET	REV.	APP'D	NEW PART NO.		DRAW NO.		
A	RELEASE	2005/06/17		NONE	A4	1 OF 1	A		510-90-14GB00		510-90-14GB00		
REV.	DESCRIPTION	DATE											